

Quarterly Reliability Monitoring Results

Quarters: Q1/2021 to Q4/2021

Based on structural similarity

Supplier Nexperia B.V. Name of Laboratory		User Part Number					
		PMEG2010EV					
		Part Description					
		Nexperia DHAM	Schottky				
Assembly reliability labs		SMD package					
Based on AEC-Q101 Test		Test Conditions	Duration	# Lots	# Quantity	# Rejects	
	TEST						
	Pre- and Post-Stress						
# E1	Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below	
		JESD22-A113					
		Bake Tamb = 125 °C	24 hours				
	PC	Soak Tamb = 85 °C, RH = 85%	168 hours				
# A1	Preconditioning	Reflow soldering	3 cycles	810	58300	0	
		MIL-STD-750-1					
	HTRB	M1038 Method A					
	High Temperature Reverse	Tj = Tjmax, Vr = 100% of max. datasheet					
# B1	Bias	reverse voltage ^[1]	1000 hours	116	9280	0	
	тс	JESD22-A104					
# 44	Temperature Cycling	-65 °C to Tjmax, not to exceed 150°C	1000 eveles	170	12600	0	
# A4	remperature cycling	• '	1000 cycles	170	13600	U	
	AC	JESD22-A102 Tamb = 121 °C, RH = 100 %					
# A3 alt	Autoclave	Pressure = 205 kPa (29.7 psia)	96 hours	170	13600	0	
AS all	Autociave	11e33dre = 203 ki d (23.7 p3id)	96 Hours	170	13600	U	
	H3TRB	JESD22-A101					
	High Humidity High	Tamb = 85 °C, RH = 85%, VR = 80 % of					
# A2 alt		rated reverse voltage ^{[1], [2]}	1000 hours	170	13600	0	
# AZ dil	Temperature Reverse Blas		1000 110015	170	13000	U	
	IOL	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔT_i =					
# A5	Intermittent Operating Life		1000 hours	170	13600	0	
+ A3	Intermittent Operating Life	100 0 101 15000 070105	1000 Hours	170	13000	U	
	RSH	JESD22-A111					
# C8	Resistance to Solder Heat	260 °C ± 5 °C	10 s	130	3900	0	
	SD		10.3	130	3300		

^[1] The physical limitations of Schottky diodes have to be considered (thermal runaway).

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia					
DHAM	Schottky	9280	0	0.46	2.19E+09

© 2022 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com

^[2] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.