

Quarterly Reliability Monitoring Results

Quarters: Q1/2022 to Q4/2023

Based on structural similarity

| Supplier | | User Part Number | | | | |
|---------------------------|--|-----------------------------------|-----------|------------|-----------|--|
| Nexperia B.V. | | PMEG3005EB-Q | | | | |
| Name of Laboratory | | Part Description | | | | |
| Assembly reliability labs | | Nexperia DHAM | | Schottky | | |
| | | SMD package | | | | |
| Based on AEC-Q101 Test | Test Conditions | Duration | # Lots | # Quantity | # Rejects | |
| # E1 | TEST Pre- and Post-Stress Electrical Test Tamb = 25 °C | N/A | see below | all parts | see below | |
| # A1 | PC Preconditioning JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering | 24 hours 168 hours 3 cycles | 1514 | 64430 | 0 | |
| # B1 | HTRB High Temperature Reverse Bias MIL-STD-750-1 M1038 Method A Tj = Tjmax, Vr = 100% of max. datasheet reverse voltage ^[1] | 1000 hours | 206 | 9320 | 0 | |
| # A4 | TC Temperature Cycling JESD22-A104 -65 °C to Tjmax, not to exceed 150°C | 1000 cycles | 311 | 14080 | 0 | |
| # A3 or | UHAST Unbiased HAST JESD22-A118 Tamb = 130 °C, RH = 85 % | 96 hours | 311 | 14080 | 0 | |
| # A3 alt | AC Autoclave JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia) | | | | | |
| # A2 alt | H3TRB High Humidity High Temperature Reverse Bias JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage ^{[1], [2]} | 1000 hours | 311 | 14080 | 0 | |
| # A5 | IOL Intermittent Operating Life MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C for 15000 cycles | 1000 hours | 312 | 14120 | 0 | |
| # C8 | RSH Resistance to Solder Heat JESD22-A111 260 °C ± 5 °C | 10 s | 269 | 8070 | 0 | |
| # C10 | SD Solderability J-STD-002 | | 222 | 6660 | 0 | |

[1] The physical limitations of Schottky diodes have to be considered (thermal runaway).

[2] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

| Wafer Fab | Technology | Quantity | Rejects | Failure Rate (FIT) | MTTF (hrs) |
|-----------|------------|----------|---------|--------------------|------------|
| Nexperia | Schottky | 9320 | 0 | 0,46 | 2,19E+09 |

© 2024 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com