

Reliability Results for Product Type PMEG2015EJ

Time period: Q1/2018 to Q4/2018

Test Results

AEC-Q101 Test	Conditions	Duration	Quantity	Rejects
TEST				
# 1 Pre- and Post-Stress Electrical Test	T _{amb} = 25 °C	N/A	all parts	see below
# 2 PC Preconditioning	JESD22-A113 Bake T _{amb} = 125 °C Soak T _{amb} = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	37120	0
# 5 HTRB High Temperature Reverse Bias	MIL-STD-750-1 M1038 Method A T _j = T _{jmax} , V _r = 100% of max. datasheet reverse voltage ^[1]	1000 hours	4400	0
# 7 TC Temperature Cycling	JESD22-A104 -55 °C to T _{jmax} , not to exceed 150°C	1000 cycles	9280	0
# 8 AC Autoclave	JESD22-A102 T _{amb} = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)	96 hours	9280	0
# 9 H3TRB High Humidity High Temperature Reverse Bias	JESD22-A101 T _{amb} = 85 °C, RH = 85%, V _R > 80 % of rated reverse voltage ^[1]	1000 hours	9280	0
# 10 IOL Intermittent Operating Life	MIL-STD-750 Method 1037 t _{on} = t _{off} , devices powered to insure ΔT _j = 100 °C for 15000 cycles	1000 hours	9280	0
# 20 RSH Resistance to Solder Heat	JESD22-A111 260 °C ± 5 °C	10 s	2340	0
# 21 SD Solderability	J-STD-002 Test method B and D		2280	0

[1] The physical limitations of Schottky diodes have to be considered (thermal runaway).

Calculation of FIT and MTBF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, AEC-Q101 Test # 5)
Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate	MTBF
Nexperia DHAM	Schottky	4400	0	0.97 FIT	118197 years