

## Quarterly Reliability Monitoring Results

Quarters: Q1/2023 to Q4/2024

Based on structural similarity

Supplier		User Part Number				
Nexperia B.V.		PMEG60T30ELP				
Name of Laboratory		Part Description				
Assembly reliability labs		Nexperia DHAM Schottky SMD package				
Test		Test Conditions	Duration	# Lots	# Quantity	# Rejects
# 1	<b>TEST</b> Pre- and Post-Stress Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below
# 2	<b>PC</b> Preconditioning	JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	1602	61540	0
# 5	<b>HTRB</b> High Temperature Reverse Bias	MIL-STD-750-1 M1038 Method A Tj = Tjmax, Vr = 100% of max. datasheet reverse voltage <sup>[1]</sup>	1000 hours	231	9240	0
# 7	<b>TC</b> Temperature Cycling	JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	500 cycles	337	13480	0
# 8 or	<b>UHAIST</b> Unbiased HAST	JESD22-A118 Tamb = 130 °C, RH = 85 %	96 hours	337	13480	0
# 8a	<b>AC</b> Autoclave	JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)				
# 9	<b>H3TRB</b> High Humidity High Temperature Reverse Bias	JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage <sup>[1], [2]</sup>	1000 hours	337	13480	0
# 10	<b>IOL</b> Intermittent Operating Life	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C	333 hours	337	13480	0
# 20	<b>RSH</b> Resistance to Solder Heat	JESD22-A111 260 °C ± 5 °C	10 s	254	7620	0
# 21	<b>SD</b> Solderability	J-STD-002		210	6300	0

[1] The physical limitations of Schottky diodes have to be considered (thermal runaway).

[2] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

### Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test # 5)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia DHAM	Schottky	9240	0	0,46	2,18E+09

© 2025 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

[nexperia.com](https://www.nexperia.com)