

Quarterly Reliability Monitoring Results

Quarters: Q1/2023 to Q4/2024

Based on structural similarity

Supplier		User Part Number				
Nexperia B.V.		PZU27BA				
Name of Laboratory		Part Description				
Assembly reliability labs		Nexperia DHAM SMD package				
Test		Test Conditions	Duration	# Lots	# Quantity	# Rejects
# 1	TEST Pre- and Post-Stress Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below
# 2	PC Preconditioning	JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	1602	61540	0
# 5	HTRB High Temperature Reverse Bias	MIL-STD-750-1 M1038 Method A Tj = Tjmax, VR = 80 % of rated reverse voltage	1000 hours	256	10240	0
# 5c	SSOP Steady State Operational	MIL-STD-750-1 M1038 Method B Tj = Tjmax, Iz = 100% of max. datasheet reverse current	1000 hours	51	2040	0
# 7	TC Temperature Cycling	JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	500 cycles	337	13480	0
# 8 or	UHAST Unbiased HAST	JESD22-A118 Tamb = 130 °C, RH = 85 %	96 hours	337	13480	0
# 8a	AC Autoclave	JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)				
# 9	H3TRB High Humidity High Temperature Reverse Bias	JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage ^[1]	1000 hours	337	13480	0
# 10	IOL Intermittent Operating Life	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔTj = 100 °C	333 hours	337	13480	0
# 20	RSH Resistance to Solder Heat	JESD22-A111 260 °C ± 5 °C	10 s	254	7620	0
# 21	SD Solderability	J-STD-002		210	6300	0

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test # 5)

Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia DHAM	Zener	10240	0	0,41	2,41E+09

© 2025 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.