

Product Quality Quick Reference Information

Quality information for product types

Quality and reliability data provided by Nexperia is intended to be a non-binding estimate of product performance only. It does not imply that any performance levels reflected in such data can be met if the product is operated outside the conditions expressly stated in the latest published datasheet for a device or in your application.

Quick reference

Information	Content
Device type	PSMN1R0-80CSE
Orderable part number (12NC)	934666613118
Package	SOT8005A
Waferfab sites	Nexperia, Manchester
Assembly sites	Nexperia, Phillipines
ESD HBM	> 8000V (3B)
ESD CDM	> 1000V

The ESD values shown are typical representative numbers from a sample of devices tested during qualification and not guaranteed. Measurements have been conducted in accordance with JS-001-2017.

Stress	Conditions	Duration	Quantity	Rejects
Stress Pre and Post stress electrical test	$T_{amb} = 25^{\circ}\text{C}$	N/A	All parts	See below
PC Preconditioning	JESD22-A113 Bake $T_{amb} = 125^{\circ}\text{C}$ Soak $T_{amb} = 85^{\circ}\text{C}$, RH = 85% reflow	24 hours 168 hours 3 cycles	924	0
HTRB High temperature reverse bias	MIL-STD-750-1 $T_j = T_j \text{ max}$, $V_{DS} = 80\%$ of rated Voltage M1039 Method A	1000 hours	231	0
HTGB High temperature gate bias	JESD22-A108 $T_j = T_j \text{ max}$, $V_{GS} = 20\text{V(SL)}$, 16V(LL)	1000 hours	231	0
TC Temperature Cycling	JESD22-A104 -55°C to 150°C	500 cycles	231	0
UHAST Unbiased highly accelerated stress test	JESD22-A118 $T_{amb} = 130^{\circ}\text{C}$, RH = 85% Pressure = +2.27atm	96 hours	231	0
HAST* Highly accelerated stress test	JESD22-A110 $T_{amb} = 130^{\circ}\text{C}$, RH = 85% $V_{DS} = 80\%$ of rated voltage	96 hours	231	0
H3TRB* Temperature Humidity bias	JESD22-A101 $T_{amb} = 85^{\circ}\text{C}$, RH = 85% $V_{DS} = 80\%$ of rated voltage	1000 hours		
IOL Intermittent operating life	MIL-STD-750 method 1037 $\Delta T_j = 80^{\circ}\text{C}$	5000 cycles	231	0
RSH Resistance to solder heat	JESD22-A111 (SMD) $260^{\circ}\text{C} \pm 5^{\circ}\text{C}$	10s	30	0
SD Solderability	IPC/ECA J-STD-002 Method A dip and look No aging, solder $T_a = 245^{\circ}\text{C}$	3 sec dip	66	0
	IPC/ECA J-STD-002 Method B dip and look No aging, Solder $T_a = 245^{\circ}\text{C}$ >95% lead coverage required Steam Aging: condition C Steam $T_a = 93^{\circ}\text{C}$, 8 hours Solder $T_a = 245^{\circ}\text{C}$, 3 sec dip	8 hours 3 sec dip	66	0
	Dry Bake: $T_a = 150^{\circ}\text{C}$ Solder $T_a = 245^{\circ}\text{C}$ >95% lead coverage required	16 hours 3 sec dip	22	0

*Either HAST or HT3RB are tested for a set of devices.

© 2022 Nexperia B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent – or other industrial or intellectual property rights

Calculation of FIT and MTBF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB) and High temperature Gate Bias (HTGB). Confidence level 60%, derated to 55°C, activation energy 0.7eV test time 168 to 1000 hours.

Technology	Quantity	Failure rate	MTBF
T12	462	2.61	3.83E+08

Structural Similarity Grouping

For qualification testing Nexperia uses the Qualification Family approach, also referred to as 'Structural Similarity Grouping' (SSG), meaning the products in the family share the same major process and material elements.