

Product Quality Quick Reference Information

Quality information for product types

Quality and reliability data provided by Nexperia is intended to be a non-binding estimate of product performance only. It does not imply that any performance levels reflected in such data can be met if the product is operated outside the conditions expressly stated in the latest published datasheet for a device or in your application.

Quick reference

| Information | Content |
|------------------------------|--------------------|
| Device type | PXN011-60QLA |
| Orderable part number (12NC) | 934668047118 |
| Package | SOT8002-1 |
| Waferfab sites | Wingskysemi, China |
| Assembly sites | Nexperia, China |
| ESD HBM | 500-1000 (1B) |
| ESD CDM | N/A |

The ESD values shown are typical representative numbers from a sample of devices tested during qualification and not guaranteed. Measurements have been conducted in accordance with JS-001-2017.

| Stress | Conditions | Duration | Quantity | Rejects |
|---|---|-----------------------------------|-----------|-----------|
| Stress Pre and Post stress electrical test | $T_{amb} = 25^{\circ}\text{C}$ | N/A | All parts | See below |
| PC Preconditioning | JESD22-A113 Bake $T_{amb} = 125^{\circ}\text{C}$ Soak $T_{amb} = 85^{\circ}\text{C}$, RH = 85% reflow | 24 hours 168 hours 3 cycles | 693 | 0 |
| HTRB High temperature reverse bias | MIL-STD-750-1 $T_j = 150^{\circ}\text{C}$, $V_{DS} = 80\%$ of rated Voltage M1039 Method A | 504 hours | 231 | 0 |
| HTGB High temperature gate bias | JESD22-A108 $T_j = 150^{\circ}\text{C}$, $V_{GS} = 20\text{V}(\text{SL})$, 16V (LL) | 504 hours | 231 | 0 |
| TC Temperature Cycling | JESD22-A104 -40°C to 125°C | 850 cycles | 231 | 0 |
| H3TRB Temperature Humidity bias | JESD22-A101 $T_{amb} = 85^{\circ}\text{C}$, RH = 85% $V_{DS} = 80\%$ of rated voltage | 1000 hours | 231 | 0 |
| IOL Intermittent operating life | MIL-STD-750 method 1037 $\Delta T_j = 80^{\circ}\text{C}$ | 5000 cycles | 231 | 0 |
| RSH Resistance to solder heat | JESD22-A111 (SMD) $260^{\circ}\text{C} \pm 5^{\circ}\text{C}$ | 10s | 30 | 0 |
| SD Solderability | IPC/ECA J-STD-002 Method A dip and look No aging, solder $T_a = 245^{\circ}\text{C}$ | 3 sec dip | 66 | 0 |
| | IPC/ECA J-STD-002 Method B dip and look No aging, Solder $T_a = 245^{\circ}\text{C}$ >95% lead coverage required Steam Aging: condition C Steam $T_a = 93^{\circ}\text{C}$, 8 hours Solder $T_a = 245^{\circ}\text{C}$, 3 sec dip | 8 hours 3 sec dip | 66 | 0 |
| | Dry Bake: $T_a = 150^{\circ}\text{C}$ Solder $T_a = 245^{\circ}\text{C}$ >95% lead coverage required | 16 hours 3 sec dip | 22 | 0 |

Calculation of FIT and MTBF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB) and High temperature Gate Bias (HTGB). Confidence level 60%, derated to 55°C, activation energy 0.7eV test time 168 to 1000 hours.

| Technology | Quantity | Failure rate | MTBF |
|------------|----------|--------------|----------|
| UNT_SGT_G1 | 462 | 2.61 | 3.83E+08 |

Structural Similarity Grouping

For qualification testing Nexperia uses the Qualification Family approach, also referred to as 'Structural Similarity Grouping' (SSG), meaning the products in the family share the same major process and material elements.