


SPICE thermal model

PSMN0R9-25YLD

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$R_{th(j-mb)}$	thermal resistance from junction to mounting base		-	-	0.56	K/W

C_{th1}	7.318E-05 F
C_{th2}	4.791E-04 F
C_{th3}	6.083E-04 F
C_{th4}	3.238E-03 F
C_{th5}	2.142E-02 F
C_{th6}	1.258E-02 F
C_{th7}	1.016E+03 F
R_{th1}	1.132E-03 Ω
R_{th2}	2.293E-03 Ω
R_{th3}	1.651E-02 Ω
R_{th4}	2.490E-02 Ω
R_{th5}	5.886E-02 Ω
R_{th6}	4.562E-01 Ω
R_{th7}	6.222E-05 Ω



Part: PSMN0R9-25YLD
 Date: 17/3/2016
 Model Rth 0.56 K/W