

PSMN011-60HL

### SPICE thermal model

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Rth(j-mb)	thermal resistance from junction to mounting base		-	-	2.21	K/W

Cth1	3.735480E-2	F	Rth1	1.062760E+0	$\Omega$
Cth2	3.377690E-3	F	Rth2	1.045490E+0	$\Omega$
Cth3	7.036820E-4	F	Rth3	7.439690E-2	$\Omega$
Cth4	1.049820E-4	F	Rth4	2.285360E-2	$\Omega$

Part Name: PSMN011-60HL  
 Date: 19 August 2022

