Low-power dual supply buffer/line driver; 3-state Rev. 2.1 — 23 July 2018 Pro

Product data sheet

1 General description

The 74AUP1T1326 is a high-performance, low-power, low-voltage, single-bit, dual supply buffer/line driver with output enable circuitry.

The 74AUP1T1326 is designed for logic-level translation applications and combines the functions of the 74AUP1G32 and 74AUP1G126. The buffer/line driver is controlled by two output enable Schmitt trigger inputs (1OE and 2OE) through an OR-gate. The output enable inputs accept standard input signals and are capable of transforming slowly changing input signals into sharply defined, jitter-free output signals. The output of the OR-gate is also available at output 1Y.

The output enable inputs (1OE and 2OE) switch at different points for positive and negative-going signals. The difference between the positive voltage V_{T+} and the negative voltage V_{T-} is defined as the input hysteresis voltage V_{H} .

Both V_{CC(A)} and V_{CC(B)} can be supplied at any voltage between 1.1 V and 3.6 V making the device suitable for interfacing between any of the low voltage nodes (1.2 V, 1.5 V, 1.8 V, 2.5 V and 3.3 V) with compatible input levels. Pins 1OE, 2OE and 1Y are referenced to V_{CC(A)} and pins A and 2Y are referenced to V_{CC(B)}. A logic LOW on both output enable pins causes the output 2Y to assume a high-impedance OFF-state.

The device ensures low static and dynamic power consumption and is fully specified for partial power down applications using I_{OFF} . The I_{OFF} circuitry disables the outputs, preventing any damaging backflow current through the device when it is powered down.

2 Features and benefits

- Wide supply voltage range:
 - V_{CC(A)}: 1.1 V to 3.6 V; V_{CC(B)}: 1.1 V to 3.6 V.
- · High noise immunity
- · Complies with JEDEC standards:
 - JESD8-7 (1.2 V to 1.95 V)
 - JESD8-5 (1.8 V to 2.7 V)
 - JESD8-B (2.7 V to 3.6 V)
- ESD protection:
 - HBM JESD22-A114E Class 2A exceeds 2000 V
 - MM JESD22-A115-A exceeds 200 V
 - CDM JESD22-C101C exceeds 1000 V
- Low static power consumption; I_{CC} = 0.9 μA (maximum)
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Inputs accept voltages up to 3.6 V
- Low noise overshoot and undershoot < 10 % of V_{CC}
- I_{OFF} circuitry provides partial Power-down mode operation

ne<mark>x</mark>peria

Low-power dual supply buffer/line driver; 3-state

- Multiple package options
- Specified from -40 °C to +85 °C


3 Ordering information

Table 1. Ordering information								
Type number	Package							
	Temperature range	Name	Description	Version				
74AUP1T1326GT	-40 °C to +85 °C	XSON8	plastic extremely thin small outline package; no leads; 8 terminals; body 1 × 1.95 × 0.5 mm	SOT833-1				

4 Marking

Table 2. Marking	
Type number	Marking code
74AUP1T1326GT	p31


5 Functional diagram



Low-power dual supply buffer/line driver; 3-state

6 Pinning information

6.1 Pinning



6.2 Pin description

Table 3. Pin de	Table 3. Pin description						
Symbol	Pin	Description					
V _{CC(B)}	1	supply voltage B					
A	2	data input					
V _{CC(A)}	3	supply voltage A					
GND	4	ground (0 V)					
10E	5	output enable input (Schmitt trigger input)					
20E	6	output enable input (Schmitt trigger input)					
1Y	7	data output					
2Y	8	data output					

7 Functional description

Table 4. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

Input		Output		
10E	20E	Α	1Y	2Y
L	L	Х	L	Z
Х	Н	L	Н	L
Х	Н	Н	Н	Н
Н	Х	L	Н	L
Н	Х	Н	Н	Н

74AUP1T1326 Product data sheet

Low-power dual supply buffer/line driver; 3-state

Limiting values 8

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC(A)}	supply voltage A		-0.5	+4.6	V
V _{CC(B)}	supply voltage B		-0.5	+4.6	V
I _{IK}	input clamping current	V _I < 0 V	-50	-	mA
VI	input voltage	[1]	-0.5	+4.6	V
I _{ОК}	output clamping current	$V_{\rm O}$ > $V_{\rm CCO}$ or $V_{\rm O}$ < 0 V ^[2]	-	-50	mA
Vo	output voltage	Active mode and Power-down mode ^[1]	-0.5	+4.6	V
I _O	output current	$V_{\rm O} = 0 \ V \ to \ V_{\rm CCO} $ ^[2]	-	±20	mA
I _{CC}	supply current		-	50	mA
I _{GND}	ground current		-50	-	mA
T _{stg}	storage temperature		-65	+150	°C
P _{tot}	total power dissipation	$T_{amb} = -40 \ ^{\circ}C \ to \ +85 \ ^{\circ}C $ ^[3]	-	250	mW

[1] The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.

V_{CCO} is the supply voltage associated with an output pin.
 For XSON8 package: above 45 °C the value of P_{tot} derates linearly with 2.4 mW/K.

Recommended operating conditions 9

Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Мах	Unit
V _{CC(A)}	supply voltage A		1.1	3.6	V
V _{CC(B)}	supply voltage B		1.1	3.6	V
VI	input voltage		0	3.6	V
Vo	output voltage	[1]	0	V _{CCO}	V
T _{amb}	ambient temperature		-40	+85	°C
Δt/ΔV	input transition rise and fall rate	input A; V_{CCI} = 1.1 V to 3.6 V ^[2]	-	200	ns/V
		input nOE; V_{CCI} = 1.1 V to 3.6 V ^[2]	-	30	ms/V

Low-power dual supply buffer/line driver; 3-state

10 Static characteristics

Table 7. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		T _{am}	_b = 25	°C	T _{am} -40 °C to	, = +85 ℃	Unit
				Min	Тур	Мах	Min	Мах	1
V _{IH}	HIGH-level	input A;	[1] [2]						
	input voltage	V _{CCI} = 1.1 V to 1.95 V		0.65V _{CCI}	-	-	0.65V _{CCI}	-	V
		V_{CCI} = 2.3 V to 2.7 V		1.6	-	-	1.6	-	V
		V _{CCI} = 3.0 V to 3.6 V		2.0	-	-	2.0	-	V
V _{IL}	LOW-level	input A;	[1] [2]						
	input voltage	V _{CCI} = 1.1 V to 1.95 V		-	-	0.35V _{CCI}	-	0.35V _{CCI}	V
		V _{CCI} = 2.3 V to 2.7 V		-	-	0.7	-	0.7	V
		V _{CCI} = 3.0 V to 3.6 V		-	-	0.9	-	0.9	V
V _{OH}	HIGH-level	$V_{I} = V_{IL}$ or V_{I} or $V_{I} = V_{T+}$ or V_{T-}	[3]						
	output voltage	I _O = -20 μA; V _{CCO} = 1.1 V to 3.6 V		V _{CCO} - 0.1	-	-	V _{CCO} - 0.1	-	V
		I _O = -1.1 mA; V _{CCO} = 1.1 V	1.1 mA; V _{CCO} = 1.1 V		-	-	0.825	-	V
		I _O = -1.7 mA; V _{CCO} = 1.4 V		1.05	-	-	1.05	-	V
		I _O = -3 mA; V _{CCO} = 1.65 V		1.2	-	-	1.2	-	V
		I _O = -2.3 mA; V _{CCO} = 2.3 V		1.97	-	-	1.97	-	V
	-	$I_{\rm O}$ = -4.0 mA; $V_{\rm CCO}$ = 2.3 V		2.0	-	-	2.0	-	V
		I _O = -2.7 mA; V _{CCO} = 3.0 V		2.67	-	-	2.67	-	V
		I_{O} = -6.0 mA; V_{CCO} = 3.0 V		2.48	-	-	2.48	-	V
V _{OL}	LOW-level	$V_{I} = V_{IL} \text{ or } V_{I} \text{ or } V_{I} = V_{T+} \text{ or } V_{T-}$	[3]						
	output voltage	I _O = 20 μA; V _{CCO} = 1.1 V to 3.6 V		-	-	0.10	-	0.10	V
		I _O = 1.1 mA; V _{CCO} = 1.1 V		-	-	0.275	-	0.275	V
		I _O = 1.7 mA; V _{CCO} = 1.4 V		-	-	0.35	-	0.35	V
		I _O = 3.0 mA; V _{CCO} = 1.65 V		-	-	0.45	-	0.45	V
		I _O = 2.3 mA; V _{CCO} = 2.3 V		-	-	0.33	-	0.33	V
		I _O = 4.0 mA; V _{CCO} = 2.3 V		-	-	0.40	-	0.40	V
		I _O = 2.7 mA; V _{CCO} = 3.0 V		-	-	0.33	-	0.33	V
		I _O = 6.0 mA; V _{CCO} = 3.0 V		-	-	0.40	-	0.40	V
lı	input leakage current	input A; $V_I = 0 V$ to 3.6 V; $V_{CCI} = 1.1 V$ to 3.6 V	[1]	-	-	±0.1	-	±0.5	μA
I _{OZ}	OFF-state output current	$\begin{array}{l} \text{output 2Y; } V_{\text{I}} = V_{\text{IH}} \text{ or } V_{\text{IL}}; \\ V_{\text{O}} = 0 \ \text{V to } 3.6 \ \text{V}; \\ V_{\text{CC}(\text{A})} = 1.1 \ \text{V to } 3.6 \ \text{V}; \\ V_{\text{CC}(\text{B})} = 1.1 \ \text{V to } 3.6 \ \text{V} \end{array}$		-	-	±0.1	-	±0.5	μA

Nexperia

74AUP1T1326

Low-power dual supply buffer/line driver; 3-state

Symbol	Parameter	Conditions		T _{am}	_{ib} = 25 °	с	T _{amt} -40 °C to	, = +85 ℃	Unit
				Min	Тур	Max	Min	Max	
I _{OFF}	power-off leakage current	$\begin{array}{l} 1 \text{Y}; \ \text{V}_{\text{CC}(\text{A})} = 0 \ \text{V}; \\ \text{V}_{\text{O}} = 0 \ \text{V} \ \text{to} \ 3.6 \ \text{V}; \\ \text{V}_{\text{CC}(\text{B})} = 1.1 \ \text{V} \ \text{to} \ 3.6 \ \text{V} \end{array}$		-	-	±0.2	-	±0.5	μA
		A, 2Y; $V_{CC(B)} = 0$ V; V ₁ or V ₀ = 0 V to 3.6 V; V _{CC(A)} = 1.1 V to 3.6 V		-	-	±0.2	-	±0.5	μA
ΔI _{OFF}	additional power-off leakage	$\begin{array}{l} 1 \text{Y}; \ \text{V}_{\text{CC}(\text{A})} = 0 \ \text{V} \ \text{to} \ 0.2 \ \text{V}; \\ \text{V}_{\text{O}} = 0 \ \text{V} \ \text{to} \ 3.6 \ \text{V}; \\ \text{V}_{\text{CC}(\text{B})} = 1.1 \ \text{V} \ \text{to} \ 3.6 \ \text{V} \end{array}$		-	-	±0.2	-	±0.6	μA
	current	A, 2Y; $V_{CC(B)} = 0$ V to 0.2 V; V _I or V _O = 0 V to 3.6 V; $V_{CC(A)} = 1.1$ V to 3.6 V		-	-	±0.2	-	±0.6	μA
I _{CC(A)}	supply current A			-	-	0.5	-	0.9	μA
I _{CC(B)}	supply	$V_{I} = 0 V \text{ or } V_{CC(B)}; I_{O} = 0 A$						0.9	
	current B	$V_{CC(A)} = V_{CC(B)} = 1.1 \text{ V to } 3.6 \text{ V}$		-	-	0.5	-		μA
		V _{CC(A)} = 1.71 V; V _{CC(B)} = 2.6 V		-	-	350	-	500	μA
ΔI _{CC}	additional supply current	nOE; V _{CC(A)} = V _{CC(B)} = 3.3 V; V _I = V _{CC(A)} - 0.6 V		-	-	40	-	50	μA
		A; $V_{CC(A)} = V_{CC(B)} = 3.3 \text{ V};$ $V_I = V_{CC(B)} - 0.6 \text{ V}$		-	-	40	-	50	μA
		A; $V_1 = GND$ to 3.6 V; nOE = GND; $V_{CC(A)} = V_{CC(B)} = 1.1$ V to 3.6 V	4]	-	-	-	-	1	μA
R _{pd}	pull-down resistance			151	281	428	150	435	kΩ
CI	input capacitance	input A; $V_I = 0 V \text{ or } V_{CCI}$; $V_{CCI} = 1.1 V \text{ to } 3.6 V$	1]	-	0.9	-	-	-	pF
		input nOE; V_I = 0 V or V_{CCI} ; [V_{CCI} = 1.1 V to 3.6 V	1]	-	0.8	-	-	-	pF
Co	output	$1Y; V_0 = GND; V_{CCO} = 0 V$	3]	-	1.7	-	-	-	pF
	capacitance	2Y enabled; V_0 = GND; V_{CCO} = 0 V	3]	-	1.7	-	-	-	pF
		2Y disabled; $V_{CCO} = 0 V \text{ to } 3.6 V;$ $V_{O} = GND \text{ or } V_{CCO}$	3]	-	1.5	-	-	-	pF

Low-power dual supply buffer/line driver; 3-state


11 Transfer characteristics

Table 8. Transfer characteristics

Voltages are referenced to GND (ground = 0 V; for test circuit see Figure 9.

Symbol	Parameter	Conditions	1	Γ _{amb} = 25 °	С	T _{an} -40 °C t	_{nb} = o +85 °C	Unit
			Min	Тур	Max	Min	Max	
V _{T+}	positive-going threshold voltage	nOE inputs; see <u>Figure 3</u> and <u>Figure 4</u>						
		V _{CC(A)} = 1.1 V	0.53	-	0.90	0.53	0.90	V
		V _{CC(A)} = 1.4 V	0.74	-	1.11	0.74	1.11	V
		V _{CC(A)} = 1.65 V	0.91	-	1.29	0.91	1.29	V
		V _{CC(A)} = 2.3 V	1.37	-	1.77	1.37	1.77	V
		V _{CC(A)} = 3.0 V	1.88	-	2.29	1.88	2.29	V
V _{T-}	negative-going threshold voltage	nOE inputs; see <u>Figure 3</u> and <u>Figure 4</u>						
		V _{CC(A)} = 1.1 V	0.26	-	0.65	0.26	0.65	V
		V _{CC(A)} = 1.4 V	0.39	-	0.75	0.39	0.75	V
		V _{CC(A)} = 1.65 V	0.47	-	0.84	0.47	0.84	V
		V _{CC(A)} = 2.3 V	0.69	-	1.04	0.69	1.04	V
		V _{CC(A)} = 3.0 V	0.88	-	1.24	0.88	1.24	V
V _H	hysteresis voltage	nOE inputs; $(V_{T+} - V_{T-})$; see Figure 3, Figure 4, Figure 5 and Figure 6						
		V _{CC(A)} = 1.1 V	0.08	-	0.46	0.08	0.46	V
		V _{CC(A)} = 1.4 V	0.18	-	0.56	0.18	0.56	V
		V _{CC(A)} = 1.65 V	0.27	-	0.66	0.27	0.66	V
		V _{CC(A)} = 2.3 V	0.53	-	0.92	0.53	0.92	V
		V _{CC(A)} = 3.0 V	0.79	-	1.31	0.79	1.31	V

Low-power dual supply buffer/line driver; 3-state



11.1 Waveforms transfer characteristics

Low-power dual supply buffer/line driver; 3-state

12 Dynamic characteristics

Table 9. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 9.

Symbol	Parameter	Conditions		amb = 25 '	°C	T _{an} -40 °C te	_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Max	Min	Max	
C _L = 5 p	F							
t _{pd}	propagation delay	A to 2Y; see <u>Figure 7</u> ^[2]						
		V _{CC(B)} = 1.1 V to 1.3 V	3.0	5.4	9.5	2.7	9.7	ns
		V _{CC(B)} = 1.4 V to 1.6 V	2.4	3.8	5.7	2.1	6.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V	1.9	3.1	4.5	1.7	5.0	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	1.5	2.3	3.4	1.3	3.8	ns
		V _{CC(B)} = 3.0 V to 3.6 V	1.2	2.1	3.0	1.0	3.3	ns
		nOE to 1Y; see Figure 7						
		V _{CC(A)} = 1.1 V to 1.3 V	3.4	5.6	9.3	3.2	9.5	ns
		V _{CC(A)} = 1.4 V to 1.6 V	2.8	4.2	5.9	2.6	6.3	ns
		V _{CC(A)} = 1.65 V to 1.95 V	2.4	3.5	4.9	2.2	5.3	ns
		V _{CC(A)} = 2.3 V to 2.7 V	2.2	2.9	3.9	2.0	4.1	ns
		V _{CC(A)} = 3.0 V to 3.6 V	1.9	2.6	3.4	1.8	3.7	ns
C _L = 10	pF							
t _{pd}	propagation delay	A to 2Y; see <u>Figure 7</u> ^[2]						
		V _{CC(B)} = 1.1 V to 1.3 V	3.4	6.2	11.0	3.0	11.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V	2.7	4.4	6.6	2.4	7.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V	2.3	3.6	5.3	2.0	5.8	ns
		V _{CC(B)} = 2.3 V to 2.7 V	1.8	2.8	4.1	1.5	4.5	ns
		V _{CC(B)} = 3.0 V to 3.6 V	1.6	2.6	3.8	1.3	4.2	ns
		nOE to 1Y; see Figure 7						
		V _{CC(A)} = 1.1 V to 1.3 V	3.7	6.4	10.8	3.4	11.1	ns
		V _{CC(A)} = 1.4 V to 1.6 V	3.1	4.7	6.8	2.8	7.2	ns
		V _{CC(A)} = 1.65 V to 1.95 V	2.9	4.0	5.6	2.5	6.1	ns
		V _{CC(A)} = 2.3 V to 2.7 V	2.5	3.4	4.6	2.2	4.9	ns
		V _{CC(A)} = 3.0 V to 3.6 V	2.3	3.1	4.1	2.1	4.5	ns

Nexperia

Symbol	Parameter	Conditions	T,	_{amb} = 25 °	°C	T _{ar} -40 °C t	_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Мах	Min	Max	
C _L = 15	pF							
t _{pd}	propagation delay	A to 2Y; see Figure 7 ^[2]						
		V _{CC(B)} = 1.1 V to 1.3 V	3.8	6.9	12.5	3.4	12.9	ns
		V _{CC(B)} = 1.4 V to 1.6 V	3.2	4.9	7.5	2.8	8.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V	2.7	4.0	6.0	2.3	6.5	ns
		V _{CC(B)} = 2.3 V to 2.7 V	2.2	3.2	4.8	1.8	5.3	ns
		V _{CC(B)} = 3.0 V to 3.6 V	1.8	2.9	4.4	1.6	4.8	ns
		nOE to 1Y; see Figure 7						
		V _{CC(A)} = 1.1 V to 1.3 V	4.2	7.2	12.4	3.8	12.7	ns
		V _{CC(A)} = 1.4 V to 1.6 V	3.6	5.2	7.6	3.3	8.2	ns
		V _{CC(A)} = 1.65 V to 1.95 V	3.1	4.5	6.3	2.7	6.9	ns
		V _{CC(A)} = 2.3 V to 2.7 V	2.8	3.8	5.3	2.5	5.6	ns
		V _{CC(A)} = 3.0 V to 3.6 V	2.5	3.5	4.8	2.3	5.2	ns
C _L = 30	pF				<u> </u>			
t _{pd}	propagation delay	A to 2Y; see Figure 7 ^[2]						
		V _{CC(B)} = 1.1 V to 1.3 V	4.8	9.0	16.6	4.2	17.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.0	6.3	9.8	3.4	10.6	ns
		V _{CC(B)} = 1.65 V to 1.95 V	3.5	5.1	7.8	3.0	8.6	ns
		V _{CC(B)} = 2.3 V to 2.7 V	2.7	4.2	6.2	2.4	6.8	ns
		V _{CC(B)} = 3.0 V to 3.6 V	2.5	3.9	5.9	2.3	6.4	ns
		nOE to 1Y; see Figure 7						
		V _{CC(A)} = 1.1 V to 1.3 V	5.1	9.2	16.4	4.6	17.1	ns
		V _{CC(A)} = 1.4 V to 1.6 V	4.3	6.6	9.9	3.8	10.8	ns
		V _{CC(A)} = 1.65 V to 1.95 V	4.0	5.6	8.1	3.5	8.9	ns
		V _{CC(A)} = 2.3 V to 2.7 V	3.4	4.7	6.7	3.0	7.2	ns
		V _{CC(A)} = 3.0 V to 3.6 V	3.3	4.4	6.2	3.0	6.7	ns
C _L = 5 p	F; V _{CC(A)} = 1.1 V to							
t _{en}	enable time	nOE to 2Y; see <u>Figure 8</u> ^[3]						
		V _{CC(B)} = 1.1 V to 1.3 V	3.4	8.7	20.0	3.2	20.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V	2.8	7.0	15.6	2.5	15.8	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8 [4]						
		V _{CC(B)} = 1.1 V to 1.3 V	3.4	7.1	15.2	3.2	15.5	ns
		V _{CC(B)} = 1.4 V to 1.6 V	2.8	6.1	13.5	2.5	13.9	ns

Nexperia

Symbol	Parameter	Conditions		T,	amb = 25 °	°C	T _{ar} -40 °C t	_{nb} = o +85 °C	Unit
			-	Min	Тур ^[1]	Max	Min	Мах	
C _L = 5 p	F; V _{CC(A)} = 1.4 V	to 1.6 V	l			1			
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	7.8	16.6	3.1	17.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		2.8	6.1	12.2	2.5	12.6	ns
		$V_{CC(B)}$ = 1.65 V to 1.95 V		2.4	5.4	10.7	2.1	11.1	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	6.3	11.8	3.1	12.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V		2.8	5.3	10.1	2.5	10.7	ns
		$V_{CC(B)}$ = 1.65 V to 1.95 V		2.4	5.4	9.9	2.1	10.5	ns
C _L = 5 p	F; V _{CC(A)} = 1.65 V	/ to 1.95 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	7.4	15.6	3.1	16.0	ns
		V _{CC(B)} = 1.4 V to 1.6 V		2.8	5.6	11.2	2.5	11.5	ns
		$V_{CC(B)}$ = 1.65 V to 1.95 V		2.4	4.9	9.7	2.1	10.1	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.2	4.4	8.2	1.9	8.8	ns
t _{dis}	disable time	nOE to 2Y; see <u>Figure 8</u>	[4]						
		$V_{CC(B)}$ = 1.1 V to 1.3 V		3.4	6.0	10.8	3.1	11.2	ns
		$V_{CC(B)}$ = 1.4 V to 1.6 V		2.8	5.0	9.1	2.5	9.6	ns
		$V_{CC(B)}$ = 1.65 V to 1.95 V		2.4	5.1	8.9	2.1	9.4	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.2	4.3	7.8	1.9	8.4	ns
C _L = 5 p	F; V _{CC(A)} = 2.3 V	to 2.7 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		$V_{CC(B)}$ = 1.1 V to 1.3 V		3.4	6.8	14.6	3.1	14.9	ns
		$V_{CC(B)}$ = 1.4 V to 1.6 V		2.8	5.0	10.1	2.5	10.4	ns
		$V_{CC(B)}$ = 1.65 V to 1.95 V		2.4	4.3	8.7	2.1	9.0	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.2	3.7	7.2	1.9	7.7	ns
		$V_{CC(B)}$ = 3.0 V to 3.6 V		1.9	3.6	6.8	1.6	7.3	ns
t _{dis}	disable time	nOE to 2Y; see <u>Figure 8</u>	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	5.5	9.8	3.1	10.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		2.8	4.5	8.1	2.5	8.5	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.4	4.6	7.9	2.1	8.3	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.2	3.9	6.8	1.9	7.3	ns
		V _{CC(B)} = 3.0 V to 3.6 V		1.9	4.4	7.3	1.6	7.7	ns

Nexperia

74AUP1T1326

Symbol	Parameter	Conditions	Conditions		_{amb} = 25	°C	T _{an} -40 °C t	_{nb} = o +85 °C	Unit
				Min	Тур ^[1]	Мах	Min	Max	
C _L = 5 p	F; V _{CC(A)} = 3.0 V	to 3.6 V						-	
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	6.5	14.2	3.1	14.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V		2.8	4.8	9.7	2.5	9.9	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.4	4.1	8.2	2.1	8.5	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	V _{CC(B)} = 2.3 V to 2.7 V		3.4	6.7	1.9	7.2	ns
		$V_{CC(B)}$ = 3.0 V to 3.6 V		1.9	3.2	6.3	1.6	6.8	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.4	5.3	9.3	3.1	9.7	ns
		V _{CC(B)} = 1.4 V to 1.6 V			4.3	7.7	2.5	8.0	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.4	4.4	7.4	2.1	7.9	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.2	3.7	6.4	1.9	6.8	ns
		V _{CC(B)} = 3.0 V to 3.6 V		1.9	4.2	6.9	1.6	7.2	ns
C _L = 10	pF; V _{CC(A)} = 1.1 V	/ to 1.3 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	9.9	22.9	3.3	23.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.1	8.0	17.8	2.8	18.1	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	8.5	18.0	3.3	18.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.1	7.3	16.0	2.8	16.4	ns
C _L = 10	pF; V _{CC(A)} = 1.4 V	/ to 1.6 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	8.8	18.8	3.3	19.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.1	6.9	13.8	2.8	14.2	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.9	6.1	12.2	2.5	12.9	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	7.6	14.0	3.3	14.5	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.1	6.4	11.9	2.8	12.5	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.9	6.7	12.0	2.5	12.6	ns

Nexperia

Symbol	Parameter	Conditions	т	T _{amb} = 25 °C			_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Мах	Min	Max	
C _L = 10	pF; V _{CC(A)} = 1.65	V to 1.95 V			<u> </u>			
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]					
		V _{CC(B)} = 1.1 V to 1.3 V	3.7	8.3	17.6	3.3	18.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		6.4	12.6	2.8	13.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V		5.6	11.0	2.5	11.7	ns
	$V_{CC(B)}$ = 2.3 V to 2.7 V	2.5	5.1	9.7	2.2	10.5	ns	
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]					
		V _{CC(B)} = 1.1 V to 1.3 V	3.7	7.2	12.8	3.3	13.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V	3.1	6.0	10.8	2.8	11.4	ns
		V _{CC(B)} = 1.65 V to 1.95 V	2.9	6.3	10.8	2.5	11.5	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.5	5.2	9.5	2.2	10.1	ns
C _L = 10	pF; V _{CC(A)} = 2.3 \	/ to 2.7 V						
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]					
		V _{CC(B)} = 1.1 V to 1.3 V	3.7	7.7	16.6	3.3	16.9	ns
		V _{CC(B)} = 1.4 V to 1.6 V	3.1	5.8	11.6	2.8	11.9	ns
		V _{CC(B)} = 1.65 V to 1.95 V	2.9	5.0	10.0	2.5	10.5	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.5	4.4	8.7	2.2	9.3	ns
		V _{CC(B)} = 3.0 V to 3.6 V	2.3	4.3	8.3	2.1	8.8	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]					
		V _{CC(B)} = 1.1 V to 1.3 V	3.7	6.8	11.8	3.3	12.2	ns
		$V_{CC(B)}$ = 1.4 V to 1.6 V	3.1	5.6	9.7	2.8	10.2	ns
		V _{CC(B)} = 1.65 V to 1.95 V	2.9	5.9	9.8	2.5	10.3	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.5	4.8	8.4	2.2	8.9	ns
		V _{CC(B)} = 3.0 V to 3.6 V	2.3	5.8	9.4	2.1	9.8	ns

Nexperia

Symbol	Parameter	Conditions	Conditions		amb = 25	°C	T _{an} -40 °C t	_{nb} = o +85 °C	Unit
				Min	Тур ^[1]	Мах	Min	Max	
C _L = 10	pF; V _{CC(A)} = 3.0 V	/ to 3.6 V						-	
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	7.4	16.1	3.3	16.5	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.1	5.5	11.1	2.8	11.5	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.9	4.7	9.5	2.5	10.1	ns
		V _{CC(B)} = 2.3 V to 2.7 V	$V_{CC(B)} = 2.3 V \text{ to } 2.7 V$ 2		4.1	8.3	2.2	8.8	ns
		V _{CC(B)} = 3.0 V to 3.6 V		2.3	3.9	7.8	2.1	8.3	ns
t _{dis} disable time		nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		3.7	6.6	11.3	3.3	11.7	ns
		V _{CC(B)} = 1.4 V to 1.6 V	V _{CC(B)} = 1.4 V to 1.6 V		5.4	9.3	2.8	9.7	ns
		V _{CC(B)} = 1.65 V to 1.95 V		2.9	5.7	9.4	2.5	9.8	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V		2.5	4.6	8.0	2.2	8.5	ns
	V _{CC(B)} = 3.0 V to 3.6 V		2.3	5.6	9.0	2.1	9.4	ns	
C _L = 15	pF; V _{CC(A)} = 1.1 V	/ to 1.3 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	10.9	25.5	3.8	25.9	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	8.9	20.1	3.2	20.6	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	9.9	20.8	3.8	21.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	8.4	18.4	3.2	18.9	ns
C _L = 15	pF; V _{CC(A)} = 1.4 V	/ to 1.6 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	9.7	20.8	3.8	21.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	7.6	15.3	3.2	16.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V		3.1	6.8	13.6	2.7	14.5	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	8.9	16.0	3.8	16.6	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	7.4	13.7	3.2	14.4	ns
		V _{CC(B)} = 1.65 V to 1.95 V		3.1	8.0	14.1	2.7	14.8	ns

Nexperia

Symbol	Parameter	Conditions	т	amb = 25 '	°C	T _{ar} -40 °C t	_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Мах	Min	Max	
C _L = 15	pF; V _{CC(A)} = 1.65	V to 1.95 V						
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]					
		V _{CC(B)} = 1.1 V to 1.3 V	4.2	9.1	19.5	3.8	20.1	ns
		V _{CC(B)} = 1.4 V to 1.6 V		7.0	14.0	3.1	14.7	ns
		V _{CC(B)} = 1.65 V to 1.95 V		6.2	12.2	2.7	13.2	ns
		V _{CC(B)} = 2.3 V to 2.7 V		5.6	11.0	2.4	11.8	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]					
		V _{CC(B)} = 1.1 V to 1.3 V	4.2	8.5	14.7	3.8	15.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V	3.6	7.0	12.4	3.1	13.1	ns
		V _{CC(B)} = 1.65 V to 1.95 V	3.1	7.5	12.7	2.7	13.5	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.8	6.1	11.0	2.4	11.8	ns
C _L = 15	pF; V _{CC(A)} = 2.3 \	/ to 2.7 V		-		1	-1	
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]					
		V _{CC(B)} = 1.1 V to 1.3 V	4.2	8.5	18.4	3.8	18.8	ns
		V _{CC(B)} = 1.4 V to 1.6 V	3.6	6.4	13.0	3.2	13.5	ns
		V _{CC(B)} = 1.65 V to 1.95 V	3.1	5.6	11.2	2.7	11.9	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.8	4.9	10.0	2.5	10.6	ns
		V _{CC(B)} = 3.0 V to 3.6 V	2.5	4.8	9.6	2.3	10.1	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]					
		V _{CC(B)} = 1.1 V to 1.3 V	4.2	8.0	13.6	3.8	14.0	ns
		$V_{CC(B)}$ = 1.4 V to 1.6 V	3.6	6.6	11.3	3.2	11.8	ns
		V _{CC(B)} = 1.65 V to 1.95 V	3.1	7.1	11.7	2.7	12.3	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	2.8	5.7	10.0	2.5	10.5	ns
		V _{CC(B)} = 3.0 V to 3.6 V	2.5	7.1	11.5	2.3	11.9	ns

Nexperia

Symbol	Parameter	Conditions		T,	amb = 25	°C	T _{an} -40 °C t	_{nb} = o +85 °C	Unit
				Min	Тур ^[1]	Мах	Min	Max	
C _L = 15	pF; V _{CC(A)} = 3.0 V	' to 3.6 V							
t _{en}	enable time	nOE to 2Y; see <u>Figure 8</u>	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	8.2	18.0	3.8	18.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	6.1	12.5	3.2	13.0	ns
		V _{CC(B)} = 1.65 V to 1.95 V		3.1	5.2	10.7	2.7	11.5	ns
		V _{CC(B)} = 2.3 V to 2.7 V		2.8	4.6	9.5	2.5	10.1	ns
		V _{CC(B)} = 3.0 V to 3.6 V		2.5	4.4	9.1	2.3	9.6	ns
t _{dis} disable time		nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		4.2	7.8	13.2	3.8	13.6	ns
		V _{CC(B)} = 1.4 V to 1.6 V		3.6	6.3	10.9	3.2	11.4	ns
		V _{CC(B)} = 1.65 V to 1.95 V		3.1	6.9	11.3	2.7	11.8	ns
		V _{CC(B)} = 2.3 V to 2.7 V		2.8	5.5	9.5	2.5	10.0	ns
		V _{CC(B)} = 3.0 V to 3.6 V		2.5	6.8	11.0	2.3	11.5	ns
C _L = 30	pF; V _{CC(A)} = 1.1 V	' to 1.3 V			-				
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		5.1	13.8	33.1	4.6	33.8	ns
		V _{CC(B)} = 1.4 V to 1.6 V		4.3	11.2	26.1	3.8	27.7	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		5.1	13.9	28.5	4.6	29.2	ns
		V _{CC(B)} = 1.4 V to 1.6 V		4.3	11.7	25.4	3.8	26.2	ns
C _L = 30	pF; V _{CC(A)} = 1.4 V	to 1.6 V							
t _{en}	enable time	nOE to 2Y; see Figure 8	[3]						
		V _{CC(B)} = 1.1 V to 1.3 V		5.1	12.1	26.6	4.6	27.5	ns
		V _{CC(B)} = 1.4 V to 1.6 V		4.3	9.5	19.6	3.8	21.4	ns
		V _{CC(B)} = 1.65 V to 1.95 V		4.0	8.5	17.7	3.5	19.2	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	[4]						
		V _{CC(B)} = 1.1 V to 1.3 V		5.1	12.6	22.0	4.6	22.9	ns
		V _{CC(B)} = 1.4 V to 1.6 V		4.3	10.4	18.9	3.8	19.9	ns
		V _{CC(B)} = 1.65 V to 1.95 V		4.0	11.6	20.1	3.5	21.2	ns

Nexperia

Symbol	Parameter	Conditions	т	amb = 25	°C	T _{ar} -40 °C t	_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Мах	Min	Max	
C _L = 30	pF; V _{CC(A)} = 1.65	V to 1.95 V						
t _{en}	enable time	nOE to 2Y; see Figure 8	3]					
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	11.4	24.8	4.6	25.6	ns
		V _{CC(B)} = 1.4 V to 1.6 V		8.7	17.8	3.8	19.5	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	7.7	15.9	3.5	17.3	ns
	V _{CC(B)} = 2.3 V to 2.7 V		7.1	14.3	3.1	15.3	ns	
t _{dis}	disable time	nOE to 2Y; see Figure 8	4]					
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	12.0	20.2	4.6	21.0	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.3	9.9	17.1	3.8	18.0	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	11.1	18.3	3.5	19.3	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	3.4	8.7	15.5	3.2	16.4	ns
C _L = 30	pF; V _{CC(A)} = 2.3 \	/ to 2.7 V			I			
t _{en}	enable time	nOE to 2Y; see Figure 8	3]					
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	10.6	23.3	4.6	23.9	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.3	7.9	16.4	3.8	17.8	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	6.9	14.4	3.5	15.6	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	3.4	6.2	12.8	3.2	13.6	ns
		V _{CC(B)} = 3.0 V to 3.6 V	3.3	6.1	12.4	3.1	13.0	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8	4]					
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	11.5	18.7	4.6	19.3	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.3	9.3	15.6	3.8	16.3	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	10.5	16.8	3.5	17.5	ns
		$V_{CC(B)}$ = 2.3 V to 2.7 V	3.4	8.2	14.0	3.2	14.7	ns
		V _{CC(B)} = 3.0 V to 3.6 V	3.3	10.7	17.0	3.1	17.6	ns

Nexperia

74AUP1T1326

Low-power dual supply buffer/line driver; 3-state

Symbol	Parameter	Conditions	T _{amb} = 25 °C			T _{ar} -40 °C t	_{nb} = o +85 °C	Unit
			Min	Тур ^[1]	Max	Min	Max	
C _L = 30	pF; V _{CC(A)} = 3.0 V to	9 3.6 V			1	1		
t _{en}	enable time	nOE to 2Y; see <u>Figure 8</u> ^[3]						
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	10.2	22.9	4.6	23.4	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.3	7.6	15.9	3.8	17.2	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	6.6	14.0	3.5	15.1	ns
		V _{CC(B)} = 2.3 V to 2.7 V	3.4	5.8	12.4	3.2	13.1	ns
		V _{CC(B)} = 3.0 V to 3.6 V	3.3	5.6	12.0	3.1	12.5	ns
t _{dis}	disable time	nOE to 2Y; see Figure 8 [4]						
		V _{CC(B)} = 1.1 V to 1.3 V	5.1	11.2	18.3	4.6	18.8	ns
		V _{CC(B)} = 1.4 V to 1.6 V	4.3	9.1	15.2	3.8	15.8	ns
		V _{CC(B)} = 1.65 V to 1.95 V	4.0	10.2	16.4	3.5	17.0	ns
		V _{CC(B)} = 2.3 V to 2.7 V	3.4	7.9	13.6	3.2	14.2	ns
		V _{CC(B)} = 3.0 V to 3.6 V	3.3	10.5	16.5	3.1	17.1	ns
C _L = 5 p	F, 10 pF, 15 pF and	30 pF		-		1		
C _{PD}	power dissipation capacitance	output 2Y; $f_i = 1 \text{ MHz}$; V _I = 0 V to V _{CC} ^[5]						
		V _{CC(A)} = V _{CC(B)} = 1.2 V	-	2.8	-	-	-	pF
		V _{CC(A)} = V _{CC(B)} = 1.5 V	-	3.0	-	-	-	pF
		V _{CC(A)} = V _{CC(B)} = 1.8 V	-	3.0	-	-	-	pF
		$V_{CC(A)} = V_{CC(B)} = 2.5 V$	-	3.6	-	-	-	pF
		$V_{CC(A)} = V_{CC(B)} = 3.3 V$	-	4.1	-	-	-	pF

[1] All typical values are measured at nominal $V_{CC(A)}$ and $V_{CC(B)}$.

An typical setting for the same as t_{PLH} and t_{PHL}.
 t_{pd} is the same as t_{PZH} and t_{PZL}.
 t_{dis} is the same as t_{PHZ} and t_{PLZ}.
 t_{dis} is the same as t_{PHZ} and t_{PLZ}.
 C_{PD} is used to determine the dynamic power dissipation (P_D in µW).
 P_D = C_{PD} × V_{CC}² × f_i × N + Σ(C_L × V_{CC}² × f₀) where: f_i = input frequency in MHz;
 f = output frequency in MHz;


 C_L = load capacitance in pF;

 V_{CC} = supply voltage in V;

N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$ = sum of the outputs.

Low-power dual supply buffer/line driver; 3-state



12.1 Waveforms and test circuit

 V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.







Figure 8. Enable and disable times

Low-power dual supply buffer/line driver; 3-state

Table 10. Measurement	Table 10. Measurement points					
Supply voltage	Input ^[1]	Output ^[2]				
V _{CC(A)} , V _{CC(B)}	V _M	V _M	V _X	V _Y		
1.1 V to 1.6 V	0.5V _{CCI}	0.5V _{CCO}	V _{OL} + 0.1 V	V _{OH} - 0.1 V		
1.65 V to 2.7 V	0.5V _{CCI}	0.5V _{CCO}	V _{OL} + 0.15 V	V _{OH} - 0.15 V		
3.0 V to 3.6 V	0.5V _{CCI}	0.5V _{CCO}	V _{OL} + 0.3 V	V _{OH} - 0.3 V		



Test data is given in Table 11.

Definitions for test circuit:

R_L = Load resistance.

 C_L = Load capacitance including jig and probe capacitance.

 R_T = Termination resistance should be equal to the output impedance Z_0 of the pulse generator.

V_{EXT} = External voltage for measuring switching times.

Figure 9. Test circuit for measuring switching times


Table 11. Test data

Supply voltage			Load ^[1]	V _{EXT}			
$V_{CC(A)}, V_{CC(B)}$	V _I ^[2]	t _r = t _f	CL	R _L ^[3]	t _{PLH} , t _{PHL}	t _{PZH} , t _{PHZ}	t _{PZL} , t _{PLZ} ^[4]
1.1 V to 3.6 V	V _{CCI}	≤ 3.0 ns	5 pF, 10 pF, 15 pF and 30 pF	5 k Ω or 1 M Ω	open	GND	2V _{CCO}

[1] For measuring enable and disable times, C_L and R_L are connected to pin 2Y. Pin 1Y has no load. [2] V_{CCI} is the supply voltage associated with the data input port. [3] For measuring enable and disable times $R_L = 5 k\Omega$, for measuring propagation delays $R_L = 1 M\Omega$. [4] V_{CCO} is the supply voltage associated with the output port.

Low-power dual supply buffer/line driver; 3-state

13 Package outline



Low-power dual supply buffer/line driver; 3-state

14 Abbreviations

Table 12. Abbreviations					
Acronym	Description				
CDM	Charged Device Model				
DUT	Device Under Test				
ESD	ElectroStatic Discharge				
НВМ	Human Body Model				
MM	Machine Model				

15 Revision history

Table 13. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes			
74AUP1T1326 v.2.1	20180723	Product data sheet	-	74AUP1T1326 v.1			
Modifications:	Nexperia.	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. 					
74AUP1T1326 v.1	20090120	Product data sheet	-	-			

Low-power dual supply buffer/line driver; 3-state

16 Legal information

16.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

16.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

16.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Low-power dual supply buffer/line driver; 3-state

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Nexperia

74AUP1T1326

Low-power dual supply buffer/line driver; 3-state

Contents

1	General description	1
2	Features and benefits	1
3	Ordering information	2
4	Marking	2
5	Functional diagram	2
6	Pinning information	3
6.1	Pinning	3
6.2	Pin description	3
7	Functional description	
8	Limiting values	4
9	Recommended operating conditions	4
10	Static characteristics	5
11	Transfer characteristics	7
11.1	Waveforms transfer characteristics	
12	Dynamic characteristics	9
12.1	Waveforms and test circuit	19
13	Package outline	21
14	Abbreviations	22
15	Revision history	
16	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2018.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 23 July 2018 Document identifier: 74AUP1T1326