74AUP1T57

Low-power configurable gate with voltage-level translator
Rev. 8 — 26 January 2022 Product data sheet

1. General description

The 74AUP1T57 is a configurable multiple function gate with level translating, Schmitt-trigger inputs. The device can be configured as any of the following logic functions AND, OR, NAND, NOR, XNOR, inverter and buffer; using the 3-bit input. All inputs can be connected directly to V_{CC} or GND. Low threshold Schmitt trigger inputs allow these devices to be driven by 1.8 V logic levels in 3.3 V applications.

This device ensures very low static and dynamic power consumption across the entire V_{CC} range from 2.3 V to 3.6 V. This device is fully specified for partial power down applications using I_{OFF} . The I_{OFF} circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

2. Features and benefits

- Wide supply voltage range from 2.3 V to 3.6 V
- · High noise immunity
- Low static power consumption; I_{CC} = 1.5 μA (maximum)
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
- Overvoltage tolerant inputs to 3.6 V
- Low noise overshoot and undershoot < 10 % of V_{CC}
- I_{OFF} circuitry provides partial power-down mode operation
- ESD protection:
 - HBM: ANSI/ESDA/JEDEC JS-001 class 3A exceeds 5000 V
 - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- · Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

3. Ordering information

Table 1. Ordering information

Type number	Package								
	Temperature range	Name	Description	Version					
74AUP1T57GW	-40 °C to +125 °C	TSSOP6	plastic thin shrink small outline package; 6 leads; body width 1.25 mm	SOT363-2					
74AUP1T57GM	-40 °C to +125 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 × 1.45 × 0.5 mm	SOT886					
74AUP1T57GN	-40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 0.9 × 1.0 × 0.35 mm	SOT1115					
74AUP1T57GS	-40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 1.0 × 1.0 × 0.35 mm	SOT1202					



Low-power configurable gate with voltage-level translator


4. Marking

Table 2. Marking

Type number	Marking code [1]
74AUP1T57GW	a7
74AUP1T57GM	a7
74AUP1T57GN	a7
74AUP1T57GS	a7


^[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

5. Functional diagram



6. Pinning information

6.1. Pinning



6.2. Pin description

Table 3. Pin description

Symbol	Pin	Description
В	1	data input
GND	2	ground (0 V)
A	3	data input
Υ	4	data output
V _{CC}	5	supply voltage
С	6	data input

Low-power configurable gate with voltage-level translator

7. Functional description

Table 4. Function table


 $H = HIGH \ voltage \ level; \ L = LOW \ voltage \ level.$

Input			Output
С	В	A	Υ
L	L	L	Н
L	L	Н	L
L	Н	L	Н
L	Н	Н	L
Н	L	L	L
Н	L	Н	L
Н	Н	L	Н
Н	Н	Н	Н

7.1. Logic configurations

Table 5. Function selection table

Logic function	Figure
2-input AND	see Fig. 2
2-input AND with both inputs inverted	see Fig. 5
2-input NAND with inverted input	see Fig. 3 and Fig. 4
2-input OR with inverted input	see Fig. 3 and Fig. 4
2-input NOR	see Fig. 5
2-input NOR with both inputs inverted	see Fig. 2
2-input XNOR	see Fig. 6
Inverter	see Fig. 7
Buffer	see Fig. 8



2-input NOR gate with both inputs inverted




Fig. 3. 2-input NAND gate with input B inverted or 2-input OR gate with inverted C input




Fig. 4. 2-input NAND gate with input C inverted or 2-input OR gate with inverted A input





Fig. 5. 2-input NOR gate or 2-input AND gate with both inputs inverted

Low-power configurable gate with voltage-level translator



8. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC}	supply voltage		-0.5	+4.6	V
I _{IK}	input clamping current	V _I < 0 V	-50	-	mA
VI	input voltage	[1]	-0.5	+4.6	V
I _{OK}	output clamping current	V _O < 0 V	-50	-	mA
Vo	output voltage	Active mode and Power-down mode [1]	-0.5	+4.6	٧
Io	output current	$V_O = 0 V \text{ to } V_{CC}$	-	±20	mA
I _{CC}	supply current		-	50	mA
I_{GND}	ground current		-50	-	mA
T _{stg}	storage temperature		-65	+150	°C
P _{tot}	total power dissipation	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$ [2]	-	250	mW

- [1] The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.
- [2] For SOT363-2 (TSSOP6) package: P_{tot} derates linearly with 3.7 mW/K above 83 °C.

For SOT886 (XSON6) package: P_{tot} derates linearly with 3.3 mW/K above 74 °C.

For SOT1115 (XSON6) package: P_{tot} derates linearly with 3.2 mW/K above 71 °C.

For SOT1202 (XSON6) package: P_{tot} derates linearly with 3.3 mW/K above 74 °C.

9. Recommended operating conditions

Table 7. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC}	supply voltage		2.3	3.6	V
VI	input voltage		0	3.6	V
Vo	output voltage	Active mode	0	V _{CC}	V
		Power-down mode; V _{CC} = 0 V	0	3.6	V
T _{amb}	ambient temperature		-40	+125	°C

Low-power configurable gate with voltage-level translator

10. Static characteristics

Table 8. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T _{amb} = 2	5 °C		•		-	'
V _{T+}	positive-going threshold	V _{CC} = 2.3 V to 2.7 V	0.60	-	1.10	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.75	-	1.16	V
V _{T-}	negative-going threshold	V _{CC} = 2.3 V to 2.7 V	0.35	-	0.60	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.50	-	0.85	V
V _H	hysteresis voltage	$(V_H = V_{T+} - V_{T-})$				
		V _{CC} = 2.3 V to 2.7 V	0.23	-	0.60	V
		V _{CC} = 3.0 V to 3.6 V	0.25	-	0.56	V
V _{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_{O} = -20 μ A; V_{CC} = 2.3 V to 3.6 V	V _{CC} - 0.1	-	-	V
		I _O = -2.3 mA; V _{CC} = 2.3 V	2.05	-	-	V
		I _O = -3.1 mA; V _{CC} = 2.3 V	1.9	-	-	V
		I _O = -2.7 mA; V _{CC} = 3.0 V	2.72	-	-	V
		I _O = -4.0 mA; V _{CC} = 3.0 V	2.6	-	-	V
V _{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I _O = 20 μA; V _{CC} = 2.3 V to 3.6 V	-	-	0.10	V
		I _O = 2.3 mA; V _{CC} = 2.3 V	-	-	0.31	V
		I _O = 3.1 mA; V _{CC} = 2.3 V	-	-	0.44	V
		I _O = 2.7 mA; V _{CC} = 3.0 V	-	-	0.31	V
		I _O = 4.0 mA; V _{CC} = 3.0 V	-	-	0.44	V
l _l	input leakage current	$V_I = GND \text{ to } 3.6 \text{ V}; V_{CC} = 0 \text{ V to } 3.6 \text{ V}$	-	-	±0.1	μA
I _{OFF}	power-off leakage current	V_{I} or $V_{O} = 0 V$ to 3.6 V; $V_{CC} = 0 V$	-	-	±0.1	μA
Δl _{OFF}	additional power-off leakage current	V _I or V _O = 0 V to 3.6 V; V _{CC} = 0 V to 0.2 V	-	-	±0.2	μA
I _{CC}	supply current	V _I = GND or V _{CC} ; I _O = 0 A; V _{CC} = 2.3 V to 3.6 V	-	-	1.2	μΑ
ΔI _{CC}	additional supply current	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V; } I_{O} = 0 \text{ A}$ [1]	-	-	-	μA
		$V_{CC} = 3.0 \text{ V to } 3.6 \text{ V; } I_{O} = 0 \text{ A}$ [2]	-	-	-	μA
Cı	input capacitance	V_{CC} = 0 V to 3.6 V; V_I = GND or V_{CC}	-	0.8	-	pF
Co	output capacitance	$V_O = GND; V_{CC} = 0 V$	-	1.7	-	pF

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T _{amb} = -	40 °C to +85 °C					
V _{T+}	positive-going threshold	V _{CC} = 2.3 V to 2.7 V	0.60	-	1.10	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.75	-	1.19	V
V _{T-}	negative-going threshold	V _{CC} = 2.3 V to 2.7 V	0.35	-	0.60	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.50	-	0.85	V
V _H	hysteresis voltage	$(V_H = V_{T+} - V_{T-})$				
		V _{CC} = 2.3 V to 2.7 V	0.10	-	0.60	V
		V _{CC} = 3.0 V to 3.6 V	0.15	-	0.56	V
V _{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_{O} = -20 μ A; V_{CC} = 2.3 V to 3.6 V	V _{CC} - 0.1	-	-	V
		I_{O} = -2.3 mA; V_{CC} = 2.3 V	1.97	-	-	V
		I _O = -3.1 mA; V _{CC} = 2.3 V	1.85	-	-	V
		I_{O} = -2.7 mA; V_{CC} = 3.0 V	2.67	-	-	V
		I_{O} = -4.0 mA; V_{CC} = 3.0 V	2.55	-	-	V
V _{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_{O} = 20 μ A; V_{CC} = 2.3 V to 3.6 V		-	0.1	V
		I _O = 2.3 mA; V _{CC} = 2.3 V	-	-	0.33	V
		I _O = 3.1 mA; V _{CC} = 2.3 V	-	-	0.45	V
		I _O = 2.7 mA; V _{CC} = 3.0 V	-	-	0.33	V
		I _O = 4.0 mA; V _{CC} = 3.0 V	-	-	0.45	V
l _l	input leakage current	V_{I} = GND to 3.6 V; V_{CC} = 0 V to 3.6 V	-	-	±0.5	μΑ
I _{OFF}	power-off leakage current	V_{I} or V_{O} = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±0.5	μΑ
ΔI _{OFF}	additional power-off leakage current	V _I or V _O = 0 V to 3.6 V; V _{CC} = 0 V to 0.2 V	-	-	±0.5	μA
I _{CC}	supply current	V _I = GND or V _{CC} ; I _O = 0 A; V _{CC} = 2.3 V to 3.6 V	-	-	1.5	μA
ΔI _{CC}	additional supply current	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V; } I_{O} = 0 \text{ A}$ [1]	-	-	4	μΑ
		$V_{CC} = 3.0 \text{ V to } 3.6 \text{ V; } I_O = 0 \text{ A}$ [2]	-	-	12	μA

Low-power configurable gate with voltage-level translator

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T _{amb} = -	40 °C to +125 °C					
V _{T+}	positive-going threshold	V _{CC} = 2.3 V to 2.7 V	0.60	-	1.10	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.75	-	1.19	V
V _{T-}	negative-going threshold	V _{CC} = 2.3 V to 2.7 V	0.33	-	0.64	V
	voltage	V _{CC} = 3.0 V to 3.6 V	0.46	-	0.85	V
V _H	hysteresis voltage	$(V_{H} = V_{T+} - V_{T-})$				
		V _{CC} = 2.3 V to 2.7 V	0.10	-	0.60	V
		V _{CC} = 3.0 V to 3.6 V	0.15	-	0.56	V
V _{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_{O} = -20 μ A; V_{CC} = 2.3 V to 3.6 V	V _{CC} - 0.11	-	-	V
		I _O = -2.3 mA; V _{CC} = 2.3 V	1.77	-	-	V
		I _O = -3.1 mA; V _{CC} = 2.3 V	1.67	-	-	V
		I _O = -2.7 mA; V _{CC} = 3.0 V	2.40	-	-	V
		I _O = -4.0 mA; V _{CC} = 3.0 V	2.30	-	-	V
V _{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I _O = 20 μA; V _{CC} = 2.3 V to 3.6 V	-	-	0.11	V
		I _O = 2.3 mA; V _{CC} = 2.3 V	-	-	0.36	V
		I _O = 3.1 mA; V _{CC} = 2.3 V	-	-	0.50	V
		I _O = 2.7 mA; V _{CC} = 3.0 V	-	-	0.36	V
		I _O = 4.0 mA; V _{CC} = 3.0 V	-	-	0.50	V
l _l	input leakage current	V_{I} = GND to 3.6 V; V_{CC} = 0 V to 3.6 V	-	-	±0.75	μΑ
I _{OFF}	power-off leakage current	V_{I} or $V_{O} = 0 V$ to 3.6 V; $V_{CC} = 0 V$	-	-	±0.75	μA
Δl _{OFF}	additional power-off leakage current	V _I or V _O = 0 V to 3.6 V; V _{CC} = 0 V to 0.2 V	-	-	±0.75	μA
I _{CC}	supply current	V _I = GND or V _{CC} ; I _O = 0 A; V _{CC} = 2.3 V to 3.6 V	-	-	3.5	μA
ΔI _{CC}	additional supply current	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V; } I_O = 0 \text{ A}$ [1]	-	-	7	μΑ
		$V_{CC} = 3.0 \text{ V to } 3.6 \text{ V; } I_{O} = 0 \text{ A}$ [2]	-	-	22	μΑ

11. Dynamic characteristics

Table 9. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 10.

Symbol	Parameter	Conditions	25 °C		25 °C -40 °C to +85 °C			_	°C to 5 °C	Unit
			Min	Typ[1]	Max	Min	Max	Min	Max	
V _{CC} = 2.3 V to 2.7 V; V _I = 1.65 V to 1.95 V										
t _{pd}	propagation delay	A, B, C to Y; see <u>Fig. 9</u> [2]								
		C _L = 5 pF	2.1	3.6	5.5	0.5	6.8	0.5	7.5	ns
		C _L = 10 pF	2.6	4.1	6.2	1.0	7.9	1.0	8.7	ns
		C _L = 15 pF	2.9	4.6	6.8	1.0	8.7	1.0	9.6	ns
		C _L = 30 pF	3.8	5.8	8.2	1.5	10.8	1.5	11.9	ns

One input at 0.3 V or 1.1 V, other input at V_{CC} or GND. One input at 0.45 V or 1.2 V, other input at V_{CC} or GND.

Low-power configurable gate with voltage-level translator

Symbol	Parameter Conditions				25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit
				Min	Typ[1]	Max	Min	Max	Min	Max	
V _{CC} = 2.	3 V to 2.7 V; V _I =	2.3 V to 2.7 V					•				
t _{pd}	propagation	A, B, C to Y; see Fig. 9	[2]								
	delay	C _L = 5 pF		1.7	3.4	5.4	0.5	6.0	0.5	6.6	ns
		C _L = 10 pF		2.1	4.0	6.2	1.0	7.1	1.0	7.9	ns
		C _L = 15 pF		2.5	4.5	6.7	1.0	7.9	1.0	8.7	ns
		C _L = 30 pF		3.3	5.6	8.2	1.5	10.0	1.5	11.0	ns
V _{CC} = 2.	3 V to 2.7 V; V _I =	3.0 V to 3.6 V									
t _{pd}	propagation	A, B, C to Y; see Fig. 9	[2]								
	delay	C _L = 5 pF		1.4	3.2	4.9	0.5	5.5	0.5	6.1	ns
		C _L = 10 pF		1.8	3.7	5.7	1.0	6.5	1.0	7.2	ns
		C _L = 15 pF		2.2	4.2	6.3	1.0	7.4	1.0	8.2	ns
		C _L = 30 pF		3.0	5.4	7.8	1.5	9.5	1.5	10.5	ns
V _{CC} = 3.	0 V to 3.6 V; V _I =	1.65 V to 1.95 V									
t _{pd}	propagation delay	A, B, C to Y; see Fig. 9	[2]								
		C _L = 5 pF		2.0	2.9	3.9	0.5	8.0	0.5	8.8	ns
		C _L = 10 pF		2.5	3.5	4.6	1.0	8.5	1.0	9.4	ns
		C _L = 15 pF		2.8	3.9	5.2	1.0	9.1	1.0	10.1	ns
		C _L = 30 pF		3.6	5.1	6.6	1.5	9.8	1.5	10.8	ns
$V_{CC} = 3$.	0 V to 3.6 V; V _I =	2.3 V to 2.7 V									
t _{pd}	propagation	A, B, C to Y; see Fig. 9	[2]								
	delay	C _L = 5 pF		1.6	2.8	4.2	0.5	5.3	0.5	5.9	ns
		C _L = 10 pF		2.0	3.4	4.9	1.0	6.1	1.0	6.8	ns
		C _L = 15 pF		2.3	3.9	5.5	1.0	6.8	1.0	7.5	ns
		C _L = 30 pF		3.1	5.0	6.9	1.5	8.5	1.5	9.4	ns
$V_{CC} = 3.$	0 V to 3.6 V; V _I =	3.0 V to 3.6 V									
t _{pd}	propagation	A, B, C to Y; see Fig. 9	[2]								
	delay	C _L = 5 pF		1.3	2.8	4.2	0.5	4.7	0.5	5.2	ns
		C _L = 10 pF		1.7	3.3	4.9	1.0	5.7	1.0	6.3	ns
		C _L = 15 pF		2.0	3.8	5.5	1.0	6.2	1.0	6.9	ns
		C _L = 30 pF		2.8	4.9	7.0	1.5	7.8	1.5	8.6	ns
T _{amb} = 2	25 °C										
C _{PD}	power	f_i = 1 MHz; V_I = GND to V_{CC}	[3]								
	dissipation capacitance	V _{CC} = 2.3 V to 2.7 V		-	3.6	-	-	-	-	-	pF
	Sapaonanoo	V _{CC} = 3.0 V to 3.6 V		-	4.3	-	-	-	-	-	pF

^[1] All typical values are measured at nominal V_{CC}.

f_i = input frequency in MHz;

f_o = output frequency in MHz;

C_L = output load capacitance in pF;

V_{CC} = supply voltage in V;

N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$ = sum of the outputs.

 ^[2] t_{pd} is the same as t_{PLH} and t_{PHL}.
 [3] C_{PD} is used to determine the dynamic power dissipation (P_D in μW).
 P_D = C_{PD} × V_{CC}² × f_i × N + Σ(C_L × V_{CC}² × f_o) where:

Low-power configurable gate with voltage-level translator

11.1. Waveforms and test circuit





Fig. 9. Input A, B and C to output Y propagation delay times

Table 10. Measurement points

Supply voltage	Output	Input		
V _{CC}	V _M	V _M	VI	$t_r = t_f$
2.3 V to 3.6 V	0.5 × V _{CC}	0.5 × V _I	1.65 V to 3.6 V	≤ 3.0 ns



Test data is given in Table 11.

Definitions for test circuit:

R_L = Load resistance;

C_L = Load capacitance including jig and probe capacitance;

 R_T = Termination resistance should be equal to the output impedance Z_o of the pulse generator;

V_{EXT} = External voltage for measuring switching times.

Fig. 10. Test circuit for measuring switching times

Table 11. Test data

Supply voltage	Load		V _{EXT}		
V _{CC}	CL	R _L [1]	t _{PLH} , t _{PHL}	t _{PZH} , t _{PHZ}	t _{PZL} , t _{PLZ}
2.3 V to 3.6 V	5 pF, 10 pF, 15 pF and 30 pF	5 k Ω or 1 M Ω	open	GND	2 × V _{CC}

^[1] For measuring enable and disable times R_L = 5 $k\Omega.$

For measuring propagation delays, setup and hold times and pulse width R_L = 1 $M\Omega$.

Low-power configurable gate with voltage-level translator

12. Package outline




Fig. 11. Package outline SOT363-2 (TSSOP6)




Fig. 12. Package outline SOT886 (XSON6)




Fig. 13. Package outline SOT1115 (XSON6)




Fig. 14. Package outline SOT1202 (XSON6)

Low-power configurable gate with voltage-level translator

13. Abbreviations

Table 12. Abbreviations

Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model

14. Revision history

Table 13. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74AUP1T57 v.8	20230726	Product data sheet	-	74AUP1T57 v.7	
Modifications:	Section 2:	<u>Section 2</u> : ESD specification updated according to the latest JEDEC standard.			
74AUP1T57 v.7	20220126	Product data sheet	-	74AUP1T57 v.6	
Modifications:	Package S	Package SOT363 (SC-88) changed to SOT363-2 (TSSOP6).			
74AUP1T57 v.6	20210526	Product data sheet	-	74AUP1T57 v.5	
Modifications:	guidelines Legal texts Type numl <u>Section 1</u> :	 The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. Type number 74AUP1T57GF (SOT891 / XSON6) removed. Section 1 and Section 2 updated. Section 8: Derating values for P_{tot} total power dissipation updated. 			
74AUP1T57 v.5	20120815	Product data sheet	-	74AUP1T57 v.4	
Modifications:	a Dookogo o	Package outline drawing of SOT886 (<u>Fig. 12</u>) modified.			
	• Fackage C	outline drawing of SOT886	(Fig. 12) modified.		
74AUP1T57 v.4	20111201	Product data sheet	(Fig. 12) modified.	74AUP1T57 v.3	
74AUP1T57 v.4 74AUP1T57 v.3			5 (<u>Fig. 12</u>) modified.	74AUP1T57 v.3 74AUP1T57 v.2	
	20111201	Product data sheet	- - -		

Low-power configurable gate with voltage-level translator

15. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at https://www.nexperia.com.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

74AUP1T57

All information provided in this document is subject to legal disclaimers

© Nexperia B.V. 2023. All rights reserved

Low-power configurable gate with voltage-level translator

Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Marking	2
5. Functional diagram	2
6. Pinning information	2
6.1. Pinning	2
6.2. Pin description	2
7. Functional description	3
7.1. Logic configurations	3
8. Limiting values	4
9. Recommended operating conditions	4
10. Static characteristics	5
11. Dynamic characteristics	7
11.1. Waveforms and test circuit	g
12. Package outline	10
13. Abbreviations	
14. Revision history	14
15. Legal information	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 26 January 2022

[©] Nexperia B.V. 2023. All rights reserved