# 74AVC4T245

4-bit dual supply translating transceiver with configurable voltage translation; 3-state

Rev. 8 — 11 April 2024

**Product data sheet** 

### 1. General description

The 74AVC4T245 is an 4-bit, dual supply transceiver that enables bidirectional level translation. The device can be used as two 2-bit transceivers or as a 4-bit transceiver. It features four 2-bit input-output ports (nAn and nBn), a direction control input (nDIR), an output enable input (n $\overline{OE}$ ) and dual supply pins (V<sub>CC(A)</sub> and V<sub>CC(B)</sub>). Both V<sub>CC(A)</sub> and V<sub>CC(B)</sub> can be supplied at any voltage between 0.8 V and 3.6 V making the device suitable for translating between any of the low voltage nodes (0.8 V, 1.2 V, 1.5 V, 1.8 V, 2.5 V and 3.3 V). Pins nAn, n $\overline{OE}$  and nDIR are referenced to V<sub>CC(A)</sub> and pins nBn are referenced to V<sub>CC(B)</sub>. A HIGH on nDIR allows transmission from nAn to nBn and a LOW on nDIR allows transmission from nBn to nAn. The output enable input (n $\overline{OE}$ ) can be used to disable the outputs so the buses are effectively isolated.

The device is fully specified for partial power-down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing any damaging backflow current through the device when it is powered down. In suspend mode when either  $V_{CC(A)}$  or  $V_{CC(B)}$  are at GND level, both nAn and nBn are in the high-impedance OFF-state.

### 2. Features and benefits

- Wide supply voltage range:
  - V<sub>CC(A)</sub>: 0.8 V to 3.6 V
  - V<sub>CC(B)</sub>: 0.8 V to 3.6 V
- Complies with JEDEC standards:
  - JESD8-12 (0.8 V to 1.3 V)
  - JESD8-11 (0.9 V to 1.65 V)
  - JESD8-7 (1.2 V to 1.95 V)
  - JESD8-5 (1.8 V to 2.7 V)
  - JESD8-B (2.7 V to 3.6 V)
- Maximum data rates:
  - 380 Mbit/s (≥ 1.8 V to 3.3 V translation)
  - 200 Mbit/s (≥ 1.1 V to 3.3 V translation)
  - 200 Mbit/s (≥ 1.1 V to 2.5 V translation)
  - 200 Mbit/s (≥ 1.1 V to 1.8 V translation)
  - 150 Mbit/s (≥ 1.1 V to 1.5 V translation)
  - 100 Mbit/s (≥ 1.1 V to 1.2 V translation)
- Suspend mode
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Inputs accept voltages up to 3.6 V
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 3B exceeds 8000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

# ne<mark>x</mark>peria


# 3. Ordering information


Type number	Package				
	Temperature range	Name	Description	Version	
74AVC4T245D	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads; body width 3.9 mm	<u>SOT109-1</u>	
74AVC4T245PW	-40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads; body width 4.4 mm	<u>SOT403-1</u>	
74AVC4T245BQ	-40 °C to +125 °C	DHVQFN16	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 × 3.5 × 0.85 mm	<u>SOT763-1</u>	
74AVC4T245GU	-40 °C to +125 °C	XQFN16	plastic, extremely thin quad flat package; no leads; 16 terminals; body 1.80 × 2.60 × 0.50 mm	<u>SOT1161-1</u>	
74AVC4T245BZ	-40 °C to +125 °C	DHXQFN16	plastic, leadless dual in-line compatible thermal enhanced extreme thin quad flat package; no leads; 16 terminals; 0.4 mm pitch; body 2 mm × 2.4 mm × 0.48 mm	<u>SOT8016-1</u>	

### 4. Marking


Table 2. Marking codes	
Type number	Marking code
74AVC4T245D	74AVC4T245D
74AVC4T245PW	VC4T245
74AVC4T245BQ	C4T245
74AVC4T245GU	BT5
74AVC4T245BZ	T245

### 5. Functional diagram






### 6. Pinning information



### 6.1. Pinning

# 74AVC4T245

#### 4-bit dual supply translating transceiver with configurable voltage translation; 3-state



. . -

#### 4-bit dual supply translating transceiver with configurable voltage translation; 3-state

### 6.2. Pin description

Symbol	Pin		Description
	SOT109-1, SOT403-1, SOT763-1 and SOT8016-1	SOT1161-1	
V <sub>CC(A)</sub>	1	3	supply voltage A (nAn, n $\overline{\text{OE}}$ and nDIR inputs are referenced to $V_{\text{CC(A)}}$
1DIR, 2DIR	2, 3	4, 5	direction control
1A1, 1A2	4, 5	6, 7	data input or output
2A1, 2A2	6, 7	8, 9	data input or output
GND[1]	8, 9	10, 11	ground (0 V)
2B2, 2B1	10, 11	12, 13	data input or output
1B2, 1B1	12, 13	14, 15	data input or output
2 <u>0E</u> , 1 <u>0E</u>	14, 15	16, 1	output enable input (active LOW)
V <sub>CC(B)</sub>	16	2	supply voltage B (nBn inputs are referenced to V <sub>CC(B)</sub> )

[1] All GND pins must be connected to ground (0 V).

### 7. Functional description

.... .

#### **Table 4. Function table**

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

Supply voltage	Input		Input/output[1]		
V <sub>CC(A)</sub> , V <sub>CC(B)</sub>	nOE [2] nDIR[2]		nAn[2]	nBn[2]	
0.8 V to 3.6 V	L	L	nAn = nBn	input	
0.8 V to 3.6 V	L	Н	input	nBn = nAn	
0.8 V to 3.6 V	Н	Х	Z	Z	
GND[1]	Х	Х	Z	Z	

[1]

If at least one of  $V_{CC(A)}$  or  $V_{CC(B)}$  is at GND level, the device goes into suspend mode. The nAn, nDIR and nOE input circuit is referenced to  $V_{CC(A)}$ ; The nBn input circuit is referenced to  $V_{CC(B)}$ . [2]

### 8. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC(A)</sub>	supply voltage A			-0.5	+4.6	V
V <sub>CC(B)</sub>	supply voltage B			-0.5	+4.6	V
I <sub>IK</sub>	input clamping current	V <sub>1</sub> < 0 V		-50	-	mA
VI	input voltage		[1]	-0.5	+4.6	V
I <sub>ОК</sub>	output clamping current	V <sub>O</sub> < 0 V		-50	-	mA
Vo	output voltage	Active mode	[1] [2] [3]	-0.5	V <sub>CCO</sub> + 0.5	V
		Suspend or 3-state mode	[1]	-0.5	+4.6	V
lo	output current	$V_{O} = 0 V$ to $V_{CCO}$	[2]	-	±50	mA
I <sub>CC</sub>	supply current	per $V_{CC(A)}$ or $V_{CC(B)}$ pin		-	100	mA
I <sub>GND</sub>	ground current	per GND pin		-100	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C				
		SOT109-1; SOT403-1; SOT763-1	[4]	-	500	mW
		SOT1161-1; SOT8016-1		-	250	mW

[1] The minimum input voltage ratings and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2]  $V_{CCO}$  is the supply voltage associated with the output port.

[3]  $V_{CCO}$  + 0.5 V should not exceed 4.6 V.

[4] For SOT109-1 (SO16) package: P<sub>tot</sub> derates linearly with 12.4 mW/K above 110 °C.
 For SOT403-1 (TSSOP16) package: P<sub>tot</sub> derates linearly with 8.5 mW/K above 91 °C.
 For SOT763-1 (DHVQFN16) package: P<sub>tot</sub> derates linearly with 11.2 mW/K above 106 °C.

### 9. Recommended operating conditions

#### Table 6. Recommended operating conditions

Symbol	Parameter	Conditions		Min	Мах	Unit
V <sub>CC(A)</sub>	supply voltage A			0.8	3.6	V
V <sub>CC(B)</sub>	supply voltage B			0.8	3.6	V
VI	input voltage			0	3.6	V
Vo	output voltage	Active mode	[1]	0	V <sub>cco</sub>	V
		Suspend or 3-state mode		0	3.6	V
T <sub>amb</sub>	ambient temperature			-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CCI</sub> = 0.8 V to 3.6 V	[2]	-	5	ns/V

[1]  $V_{CCO}$  is the supply voltage associated with the output port.

[2]  $V_{CCI}$  is the supply voltage associated with the input port.

### **10. Static characteristics**

#### Table 7. Typical static characteristics at T<sub>amb</sub> = 25 °C

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).[1]

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>OH</sub>	HIGH-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>				
		I <sub>O</sub> = -1.5 mA; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V	-	0.69	-	V
V <sub>OL</sub>	LOW-level output voltage	$V_{I} = V_{IH} \text{ or } V_{IL}$				
		I <sub>O</sub> = 1.5 mA; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V	-	0.07	-	V
lı	input leakage current	nDIR, n $\overline{OE}$ input; V <sub>1</sub> = 0 V or 3.6 V; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V to 3.6 V	-	±0.025	±0.25	μA
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_O = 0 V$ or $V_{CCO}$ ; [2] $V_{CC(A)} = V_{CC(B)} = 3.6 V$		±0.5	±2.5	μA
		suspend mode A port; $V_O = 0 V \text{ or } V_{CCO}$ ; [2 $V_{CC(A)} = 3.6 V$ ; $V_{CC(B)} = 0 V$	] -	±0.5	±2.5	μA
		suspend mode B port; $V_0 = 0 V \text{ or } V_{CCO}$ ; [2 $V_{CC(A)} = 0 V$ ; $V_{CC(B)} = 3.6 V$	] -	±0.5	±2.5	μA
I <sub>OFF</sub>	power-off leakage current	A port; V <sub>1</sub> or V <sub>O</sub> = 0 V to 3.6 V; V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 0.8 V to 3.6 V	-	±0.1	±1	μA
		B port; V <sub>1</sub> or V <sub>O</sub> = 0 V to 3.6 V; V <sub>CC(B)</sub> = 0 V; V <sub>CC(A)</sub> = 0.8 V to 3.6 V	-	±0.1	±1	μA
Cı	input capacitance	nDIR, n $\overline{OE}$ input; V <sub>I</sub> = 0 V or 3.3 V; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 3.3 V	-	1.0	-	pF
C <sub>I/O</sub>	input/output capacitance	A and B port; $V_0 = 3.3 \text{ V}$ or 0 V; $V_{CC(A)} = V_{CC(B)} = 3.3 \text{ V}$	-	4.0	-	pF

#### **Table 8. Static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).[1]

Symbol	Parameter	Conditions	-40 °C to	+85 °C	-40 °C to	Unit	
			Min	Max	Min	Мах	7
V <sub>IH</sub>	H HIGH-level input voltage	data input					
		V <sub>CCI</sub> = 0.8 V	0.70V <sub>CCI</sub>	-	0.70V <sub>CCI</sub>	-	V
		V <sub>CCI</sub> = 1.1 V to 1.95 V	0.65V <sub>CCI</sub>	-	0.65V <sub>CCI</sub>	-	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V	1.6	-	1.6	-	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V	2	-	2	-	V
		nDIR, nOE input					
		V <sub>CC(A)</sub> = 0.8 V	0.70V <sub>CC(A)</sub>	-	0.70V <sub>CC(A)</sub>	-	V
		V <sub>CC(A)</sub> = 1.1 V to 1.95 V	0.65V <sub>CC(A)</sub>	-	0.65V <sub>CC(A)</sub>	-	V
		V <sub>CC(A)</sub> = 2.3 V to 2.7 V	1.6	-	1.6	-	V
		V <sub>CC(A)</sub> = 3.0 V to 3.6 V	2	-	2	-	V

Symbol	Parameter	Conditions		-40 °C t	o +85 °C	-40 °C to	Unit	
				Min	Max	Min Max		
VIL	LOW-level	data input						
	input voltage	V <sub>CCI</sub> = 0.8 V		-	0.30V <sub>CCI</sub>	-	0.30V <sub>CCI</sub>	V
		V <sub>CCI</sub> = 1.1 V to 1.95 V		-	0.35V <sub>CCI</sub>	-	0.35V <sub>CCI</sub>	V
		V <sub>CCI</sub> = 2.3 V to 2.7 V		-	0.7	-	0.7	V
		V <sub>CCI</sub> = 3.0 V to 3.6 V		-	0.8	-	0.8	V
		nDIR, nOE input						
		V <sub>CC(A)</sub> = 0.8 V		-	0.30V <sub>CC(A)</sub>	-	0.30V <sub>CC(A)</sub>	V
		V <sub>CC(A)</sub> = 1.1 V to 1.95 V		-	0.35V <sub>CC(A)</sub>	-	0.35V <sub>CC(A)</sub>	
		V <sub>CC(A)</sub> = 2.3 V to 2.7 V		_	0.7	_	0.7	V
		V <sub>CC(A)</sub> = 3.0 V to 3.6 V		_	0.8	_	0.8	V
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{IH}$ or $V_{IL}$						
	output voltage	I <sub>O</sub> = -100 μA; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V to 3.6 V		V <sub>CCO</sub> - 0.1	-	V <sub>CCO</sub> - 0.1	-	V
		$I_{O} = -3 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.1 \text{ V}$		0.85	-	0.85	-	V
		$I_{O} = -6 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.4 \text{ V}$		1.05	-	1.05	-	V
		$I_{O} = -8 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.65 \text{ V}$		1.2	-	1.2	-	V
		$I_{O} = -9 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 2.3 \text{ V}$		1.75	-	1.75	-	V
		$I_{O}$ = -12 mA; $V_{CC(A)}$ = $V_{CC(B)}$ = 3.0 V		2.3	-	2.3	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{IH} \text{ or } V_{IL}$						
	output voltage	I <sub>O</sub> = 100 μA; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V to 3.6 V		-	0.1	-	0.1	V
		$I_{O} = 3 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.1 \text{ V}$		-	0.25	-	0.25	V
		$I_{O} = 6 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.4 \text{ V}$		-	0.35	-	0.35	V
		$I_{O} = 8 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 1.65 \text{ V}$		-	0.45	-	0.45	V
		$I_{O} = 9 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 2.3 \text{ V}$		-	0.55	-	0.55	V
		$I_{O} = 12 \text{ mA}; V_{CC(A)} = V_{CC(B)} = 3.0 \text{ V}$		-	0.7	-	0.7	V
lı	input leakage current	nDIR, n $\overline{OE}$ input; V <sub>I</sub> = 0 V or 3.6 V; V <sub>CC(A)</sub> = V <sub>CC(B)</sub> = 0.8 V to 3.6 V		-	±1	-	±5	μA
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_O = 0 V$ or $V_{CCO}$ ; $V_{CC(A)} = V_{CC(B)} = 3.6 V$	[2]	-	±5	-	±30	μA
		suspend mode A port; $V_O = 0 V \text{ or } V_{CCO}; V_{CC(A)} = 3.6 V;$ $V_{CC(B)} = 0 V$	[2]	-	±5	-	±30	μA
		suspend mode B port; $V_O = 0 V \text{ or } V_{CCO}; V_{CC(A)} = 0 V;$ $V_{CC(B)} = 3.6 V$	[2]	-	±5	-	±30	μA
I <sub>OFF</sub>	power-off leakage	A port; V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V; V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 0.8 V to 3.6 V		-	±5	-	±30	μA
	current	B port; V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V; V <sub>CC(B)</sub> = 0 V; V <sub>CC(A)</sub> = 0.8 V to 3.6 V		-	±5	-	±30	μA

Symbol	Parameter	Conditions	-40 °C t	o +85 °C	-40 °C to +125 °C		Unit
			Min	Max	Min	Max	
I <sub>CC</sub>	supply current	A port; $V_I = 0$ V or $V_{CCI}$ ; $I_O = 0$ A					
		$V_{CC(A)} = 0.8 V \text{ to } 3.6 V;$ $V_{CC(B)} = 0.8 V \text{ to } 3.6 V$	-	10	-	55	μA
		V <sub>CC(A)</sub> = 1.1 V to 3.6 V; V <sub>CC(B)</sub> = 1.1 V to 3.6 V	-	8	-	50	μA
		V <sub>CC(A)</sub> = 3.6 V; V <sub>CC(B)</sub> = 0 V	-	8	-	50	μA
		V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 3.6 V	-2	-	-12	-	μA
		B port; $V_1 = 0$ V or $V_{CCI}$ ; $I_0 = 0$ A					
		$V_{CC(A)} = 0.8 V \text{ to } 3.6 V;$ $V_{CC(B)} = 0.8 V \text{ to } 3.6 V$	-	10	-	55	μA
		V <sub>CC(A)</sub> = 1.1 V to 3.6 V; V <sub>CC(B)</sub> = 1.1 V to 3.6 V	-	8	-	50	μA
		V <sub>CC(A)</sub> = 3.6 V; V <sub>CC(B)</sub> = 0 V	-2	-	-12	-	μA
		V <sub>CC(A)</sub> = 0 V; V <sub>CC(B)</sub> = 3.6 V	-	8	-	50	μA
		A plus B port $(I_{CC(A)} + I_{CC(B)})$ ; $I_{O} = 0$ A; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; V <sub>CC(A)</sub> = 0.8 V to 3.6 V; V <sub>CC(B)</sub> = 0.8 V to 3.6 V	-	20	-	70	μA
		A plus B port $(I_{CC(A)} + I_{CC(B)})$ ; $I_0 = 0 A$ ; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; V <sub>CC(A)</sub> = 1.1 V to 3.6 V; V <sub>CC(B)</sub> = 1.1 V to 3.6 V	-	16	-	65	μA

[1]  $V_{CCO}$  is the supply voltage associated with the output port;  $V_{CCI}$  is the supply voltage associated with the data input port.

[2] For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.

#### Table 9. Typical total supply current (I<sub>CC(A)</sub> + I<sub>CC(B)</sub>)

V <sub>CC(A)</sub>	V <sub>CC(B)</sub>	V <sub>CC(B)</sub>									
	0 V	0.8 V	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V				
0 V	0	0.1	0.1	0.1	0.1	0.1	0.1	μA			
0.8 V	0.1	0.1	0.1	0.1	0.1	0.3	1.6	μA			
1.2 V	0.1	0.1	0.1	0.1	0.1	0.1	0.8	μA			
1.5 V	0.1	0.1	0.1	0.1	0.1	0.1	0.4	μA			
1.8 V	0.1	0.1	0.1	0.1	0.1	0.1	0.2	μA			
2.5 V	0.1	0.3	0.1	0.1	0.1	0.1	0.1	μA			
3.3 V	0.1	1.6	0.8	0.4	0.2	0.1	0.1	μA			

### **11. Dynamic characteristics**

#### Table 10. Typical power dissipation capacitance at $V_{CC(A)} = V_{CC(B)}$ and $T_{amb} = 25 \degree C$ Voltages are referenced to GND (ground = 0 V).[1] [2]

Symbol	Parameter	Conditions			V <sub>CC(A)</sub> =	= V <sub>CC(B)</sub>			Unit
			0.8 V	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	
C <sub>PD</sub>	power dissipation	A port: (direction nAn to nBn); output enabled	0.2	0.2	0.2	0.2	0.3	0.4	pF
	capacitance	A port: (direction nAn to nBn); output disabled	0.2	0.2	0.2	0.2	0.3	0.4	pF
		A port: (direction nBn to nAn); output enabled	9.5	9.7	9.8	9.9	10.7	11.9	pF
		A port: (direction nBn to nAn); output disabled	0.6	0.6	0.6	0.6	0.7	0.7	pF
		B port: (direction nAn to nBn); output enabled	9.5	9.7	9.8	9.9	10.7	11.9	pF
		B port: (direction nAn to nBn); output disabled	0.6	0.6	0.6	0.6	0.7	0.7	pF
	B port: (direction nBn to nAn); output enabled	0.2	0.2	0.2	0.2	0.3	0.4	pF	
		B port: (direction nBn to nAn); output disabled	0.2	0.2	0.2	0.2	0.3	0.4	pF

[1]  $C_{PD}$  is used to determine the dynamic power dissipation (P<sub>D</sub> in  $\mu$ W).

 $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} \times N + \Sigma (C_{L} \times V_{CC}^{2} \times f_{o}) \text{ where:}$ 

f<sub>i</sub> = input frequency in MHz;

 $f_o$  = output frequency in MHz;

 $C_L$  = load capacitance in pF;

V<sub>CC</sub> = supply voltage in V;

N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_o) = \text{sum of the outputs.}$ [2]  $f_i = 10 \text{ MHz}; V_I = \text{GND to } V_{CC}; t_r = t_f = 1 \text{ ns}; C_L = 0 \text{ pF}; R_L = \infty \Omega.$ 

#### Table 11. Typical dynamic characteristics at $V_{CC(A)}$ = 0.8 V and $T_{amb}$ = 25 $^{\circ}C$

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 10; for waveforms see Fig. 8 and Fig. 9.[1]

Symbol	Parameter	Conditions	Conditions V <sub>CC(B)</sub>						
			0.8 V	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	
t <sub>pd</sub>	propagation delay	nAn to nBn	14.5	7.3	6.5	6.2	5.9	6.0	ns
		nBn to nAn	14.5	12.7	12.4	12.3	12.1	12.0	ns
t <sub>dis</sub> disable time	disable time	n <del>OE</del> to nAn	14.3	14.3	14.3	14.3	14.3	14.3	ns
		n <del>OE</del> to nBn	17.0	9.9	9.0	9.4	9.0	9.7	ns
t <sub>en</sub>	enable time	nOE to nAn	18.2	18.2	18.2	18.2	18.2	18.2	ns
		n <del>OE</del> to nBn	19.2	10.7	9.8	9.6	9.7	10.2	ns

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .

#### Table 12. Typical dynamic characteristics at $V_{CC(B)}$ = 0.8 V and $T_{amb}$ = 25 $^{\circ}C$

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 10; for waveforms see Fig. 8 and Fig. 9.[1]

Symbol	Parameter	Conditions	V <sub>CC(A)</sub>						Unit
			0.8 V	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	
t <sub>pd</sub>	propagation delay	nAn to nBn	14.5	12.7	12.4	12.3	12.1	12.0	ns
		nBn to nAn	14.5	7.3	6.5	6.2	5.9	6.0	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	14.3	5.5	4.1	4.0	3.0	3.5	ns
		n <del>OE</del> to nBn	17.0	13.8	13.4	13.1	12.9	12.7	ns
t <sub>en</sub> e	enable time	n <del>OE</del> to nAn	18.2	5.6	4.0	3.2	2.4	2.2	ns
		n <del>OE</del> to nBn	19.2	14.6	14.1	13.9	13.7	13.6	ns

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .

#### Table 13. Dynamic characteristics for temperature range -40 °C to +85 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 10; for waveforms see Fig. 8 and Fig. 9.[1]

Symbol	Parameter	Conditions	V <sub>CC(B)</sub>									Unit	
			1.2 V ± 0.1 V		1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	1
V <sub>CC(A)</sub> =	1.1 V to 1.3 V			1	1	1	1			1			
t <sub>pd</sub>	propagation	nAn to nBn	0.5	9.4	0.5	7.1	0.5	6.2	0.5	5.2	0.5	5.1	ns
	delay	nBn to nAn	0.5	9.4	0.5	8.9	0.5	8.7	0.5	8.4	0.5	8.2	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	10.9	1.8	10.9	1.8	10.9	1.8	10.9	1.8	10.9	ns
		n <del>OE</del> to nBn	1.9	12.4	1.9	9.6	1.9	9.5	1.4	8.1	1.2	9.1	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.4	12.8	1.4	12.8	1.4	12.8	1.4	12.8	1.4	12.8	ns
		n <del>OE</del> to nBn	1.1	13.3	1.1	10.0	1.1	8.9	1.0	7.9	1.0	7.7	ns
V <sub>CC(A)</sub> =	1.4 V to 1.6 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.3	8.9	0.3	6.3	0.3	5.2	0.3	4.2	0.3	4.2	ns
	delay	nBn to nAn	0.7	7.1	0.7	6.3	0.5	6.0	0.4	5.7	0.3	5.6	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	10.2	1.8	10.2	1.5	10.2	1.3	10.2	1.6	10.2	ns
		n <del>OE</del> to nBn	1.9	11.3	1.9	10.3	1.9	9.1	1.4	7.4	1.2	7.6	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.1	9.4	1.4	9.4	1.1	9.4	0.7	9.4	0.4	9.4	ns
		n <del>OE</del> to nBn	1.4	12.1	1.4	9.6	1.1	7.7	0.9	5.8	0.9	5.6	ns
V <sub>CC(A)</sub> =	1.65 V to 1.95	V											
t <sub>pd</sub>	propagation delay	nAn to nBn	0.1	8.7	0.1	6.0	0.1	4.9	0.1	3.9	0.3	3.9	ns
		nBn to nAn	0.6	6.2	0.6	5.3	0.5	4.9	0.3	4.6	0.3	4.5	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	8.6	1.6	8.6	1.8	8.6	1.3	8.6	1.6	8.6	ns
		n <del>OE</del> to nBn	1.7	10.9	1.7	9.9	1.6	8.7	1.2	6.9	1.0	6.9	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.0	7.2	1.0	7.2	1.0	7.2	0.6	7.2	0.4	7.2	ns
		n <del>OE</del> to nBn	1.2	11.7	1.2	9.2	1.0	7.4	0.8	5.3	0.8	4.6	ns
V <sub>CC(A)</sub> =	2.3 V to 2.7 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.1	8.4	0.1	5.7	0.1	4.6	0.2	3.5	0.1	3.6	ns
	delay	nBn to nAn	0.6	5.2	0.6	4.2	0.4	3.9	0.2	3.4	0.2	3.3	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.0	6.2	1.0	6.2	1.0	6.2	1.0	6.2	1.0	6.2	ns
		n <del>OE</del> to nBn	1.5	10.4	1.5	8.8	1.3	8.2	1.1	6.2	0.9	5.2	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	0.7	4.8	0.7	4.8	0.7	4.8	0.6	4.8	0.4	4.8	ns
		n <del>OE</del> to nBn	0.9	11.3	0.9	8.8	0.8	7.0	0.6	4.8	0.6	4.0	ns
V <sub>CC(A)</sub> =	3.0 V to 3.6 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.1	8.2	0.1	5.6	0.1	4.5	0.1	3.3	0.1	2.9	ns
	delay	nBn to nAn	0.6	5.1	0.6	4.2	0.4	3.4	0.2	3.0	0.1	2.8	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	0.7	5.6	0.7	5.6	0.7	5.6	0.7	5.6	0.7	5.6	ns
		n <del>OE</del> to nBn	1.4	10.2	1.4	9.3	1.2	8.1	1.0	6.4	0.8	6.2	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	0.6	3.8	0.6	3.8	0.6	3.8	0.6	3.8	0.4	3.8	ns
		nOE to nBn	0.8	11.3	0.8	8.7	0.6	6.8	0.5	4.7	0.5	3.8	ns

 $[1] \quad t_{pd} \text{ is the same as } t_{PLH} \text{ and } t_{PHL}; \ t_{dis} \text{ is the same as } t_{PLZ} \text{ and } t_{PHZ}; \ t_{en} \text{ is the same as } t_{PZL} \text{ and } t_{PZH}.$ 


#### Table 14. Dynamic characteristics for temperature range -40 °C to +125 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 10; for waveforms see Fig. 8 and Fig. 9.[1]

Symbol	Parameter	Conditions	V <sub>CC(B)</sub>									Unit	
			1.2 V ± 0.1 V		1.5 V ± 0.1 V		1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		
			Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	1
V <sub>CC(A)</sub> =	1.1 V to 1.3 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.5	10.4	0.5	7.9	0.5	6.9	0.5	5.8	0.5	5.7	ns
	delay	nBn to nAn	0.5	10.4	0.5	9.8	0.5	9.6	0.5	9.3	0.5	9.1	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	12.0	1.8	12.0	1.8	12.0	1.8	12.0	1.8	12.0	ns
		n <del>OE</del> to nBn	1.9	13.7	1.9	10.6	1.9	10.5	1.4	9.0	1.2	10.1	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.4	14.1	1.4	14.1	1.4	14.1	1.4	14.1	1.4	14.1	ns
		n <del>OE</del> to nBn	1.1	14.7	1.1	11.0	1.1	9.8	1.0	8.7	1.0	8.5	ns
V <sub>CC(A)</sub> =	1.4 V to 1.6 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.3	9.8	0.3	7.0	0.3	5.8	0.3	4.7	0.3	4.7	ns
	delay	nBn to nAn	0.7	7.9	0.7	7.0	0.5	6.6	0.4	6.3	0.3	6.2	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	11.3	1.8	11.3	1.5	11.3	1.3	11.3	1.6	11.3	ns
		n <del>OE</del> to nBn	1.9	12.5	1.9	11.4	1.9	10.1	1.4	8.2	1.2	8.4	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.1	10.4	1.4	10.4	1.1	10.4	0.7	10.4	0.4	10.4	ns
		n <del>OE</del> to nBn	1.4	13.3	1.4	10.6	1.1	8.5	0.9	6.4	0.9	6.2	ns
V <sub>CC(A)</sub> =	1.65 V to 1.95	V											
t <sub>pd</sub>	propagation delay	nAn to nBn	0.1	9.6	0.1	6.6	0.1	5.4	0.1	4.3	0.3	4.3	ns
		nBn to nAn	0.6	6.9	0.6	5.9	0.5	5.4	0.3	5.1	0.3	5.0	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.8	9.5	1.6	9.5	1.8	9.5	1.3	9.5	1.6	9.5	ns
		n <del>OE</del> to nBn	1.7	12.0	1.7	10.9	1.6	9.6	1.2	7.6	1.0	7.6	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	1.0	8.0	1.0	8.0	1.0	8.0	0.6	8.0	0.4	8.0	ns
		n <del>OE</del> to nBn	1.2	12.9	1.2	10.2	1.0	8.2	0.8	5.9	0.8	5.1	ns
V <sub>CC(A)</sub> =	2.3 V to 2.7 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.1	9.3	0.1	6.3	0.1	5.1	0.2	4.0	0.1	4.0	ns
	delay	nBn to nAn	0.6	5.8	0.6	4.7	0.4	4.3	0.2	3.9	0.2	3.8	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	1.0	6.9	1.0	6.9	1.0	6.9	1.0	6.9	1.0	6.9	ns
		n <del>OE</del> to nBn	1.5	11.5	1.5	10.4	1.3	9.1	1.1	6.9	0.9	5.8	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	0.7	5.3	0.7	5.3	0.7	5.3	0.6	5.3	0.4	5.3	ns
		n <del>OE</del> to nBn	0.9	12.4	0.9	9.7	0.8	7.7	0.6	5.3	0.6	4.4	ns
V <sub>CC(A)</sub> =	3.0 V to 3.6 V												
t <sub>pd</sub>	propagation	nAn to nBn	0.1	9.1	0.1	6.2	0.1	5.0	0.1	3.8	0.1	3.3	ns
	delay	nBn to nAn	0.6	5.7	0.6	4.7	0.4	3.9	0.2	3.4	0.1	3.3	ns
t <sub>dis</sub>	disable time	n <del>OE</del> to nAn	0.7	6.2	0.7	6.2	0.7	6.2	0.7	6.2	0.7	6.2	ns
		n <del>OE</del> to nBn	1.4	11.3	1.4	10.3	1.2	9.0	1.0	7.1	0.8	6.9	ns
t <sub>en</sub>	enable time	n <del>OE</del> to nAn	0.6	4.2	0.6	4.2	0.6	4.2	0.6	4.2	0.4	4.2	ns
		nOE to nBn	0.8	12.4	0.8	9.6	0.6	7.5	0.5	5.2	0.5	4.2	ns

 $[1] \quad t_{pd} \text{ is the same as } t_{PLH} \text{ and } t_{PHL}; \ t_{dis} \text{ is the same as } t_{PLZ} \text{ and } t_{PHZ}; \ t_{en} \text{ is the same as } t_{PZL} \text{ and } t_{PZH}.$ 

### 11.1. Waveforms and test circuit



#### Table 15. Measurement points


Supply voltage	Input[1]	Output[2]	Output[2]					
V <sub>CC(A)</sub> , V <sub>CC(B)</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>				
0.8 V to 1.6 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.1 V	V <sub>OH</sub> - 0.1 V				
1.65 V to 2.7 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V				
3.0 V to 3.6 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V				

[1]  $V_{CCI}$  is the supply voltage associated with the data input port.

[2]  $V_{CCO}$  is the supply voltage associated with the output port.

# 74AVC4T245

#### 4-bit dual supply translating transceiver with configurable voltage translation; 3-state




#### Table 16. Test data

Supply voltage	ltage Input		Load		V <sub>EXT</sub>			
$V_{CC(A)}, V_{CC(B)}$	V <sub>I</sub> [1]	Δt/ΔV [2]	CL	RL	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>PZH</sub> , t <sub>PHZ</sub>	t <sub>PZL</sub> , t <sub>PLZ</sub> [3]	
0.8 V to 1.6 V	V <sub>CCI</sub>	≤ 1.0 ns/V	15 pF	2 kΩ	open	GND	2V <sub>CCO</sub>	
1.65 V to 2.7 V	V <sub>CCI</sub>	≤ 1.0 ns/V	15 pF	2 kΩ	open	GND	2V <sub>CCO</sub>	
3.0 V to 3.6 V	V <sub>CCI</sub>	≤ 1.0 ns/V	15 pF	2 kΩ	open	GND	2V <sub>CCO</sub>	


[1]  $V_{CCI}$  is the supply voltage associated with the data input port.


[2] dV/dt ≥ 1.0 V/ns

[3]  $V_{CCO}$  is the supply voltage associated with the output port.



### 12. Typical propagation delay characteristics






c. LOW to HIGH propagation delay (A to B);  $V_{CC(A)}$  = 1.5 V

 $\begin{array}{l} (1) \ V_{CC(B)} = 1.2 \ V \\ (2) \ V_{CC(B)} = 1.5 \ V \\ (3) \ V_{CC(B)} = 1.8 \ V \\ (4) \ V_{CC(B)} = 2.5 \ V \\ (5) \ V_{CC(B)} = 3.3 \ V \end{array}$ 


7 tPHL (ns) 5 4 4 1 0 20 40 CL (pF) 001aai491 (1) (1) (2) (3) (4) (5) 60

b. HIGH to LOW propagation delay (A to B);  $V_{CC(A)}$  = 1.2 V




d. HIGH to LOW propagation delay (A to B);  $V_{CC(A)}$  = 1.5 V

Fig. 12. Typical propagation delay versus load capacitance; T<sub>amb</sub> = 25 °C



a. LOW to HIGH propagation delay (A to B);  $V_{CC(A)}$  = 1.8 V




c. LOW to HIGH propagation delay (A to B);  $V_{CC(A)}$  = 2.5 V

 $\begin{array}{l} (1) \ V_{CC(B)} = 1.2 \ V \\ (2) \ V_{CC(B)} = 1.5 \ V \\ (3) \ V_{CC(B)} = 1.8 \ V \\ (4) \ V_{CC(B)} = 2.5 \ V \\ (5) \ V_{CC(B)} = 3.3 \ V \end{array}$ 


7 tPHL (ns) 5 6 1 0 20 40 CL (pF) 001ai/482 (1) (1) (2) (3) (4) (5) 60 CL (pF)

b. HIGH to LOW propagation delay (A to B);  $V_{CC(A)}$  = 1.8 V



d. HIGH to LOW propagation delay (A to B);  $V_{CC(A)} = 2.5 V$ 

Fig. 13. Typical propagation delay versus load capacitance; T<sub>amb</sub> = 25 °C



© Nexperia B.V. 2024. All rights reserved

### 13. Package outline




Fig. 15. Package outline SOT109-1 (SO16)



SOT403-1




Fig. 16. Package outline SOT403-1 (TSSOP16)

#### DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; SOT763-1 16 terminals; body 2.5 x 3.5 x 0.85 mm B A A<sub>1</sub> F С detail X terminal 1 index area С terminal 1 e<sub>1</sub> index area // y1 C -> • [] У е b-0 w w 2 7 L. Ā 1 E<sub>h</sub> е 16 10 15 Dh Х 0 2.5 5 mm scale DIMENSIONS (mm are the original dimensions) A<sup>(1)</sup> D<sup>(1)</sup> E<sup>(1)</sup> UNIT A<sub>1</sub> b с Dh Eh е e1 L v w у У1 max. 2.15 1.85 0.05 0.30 2.6 1.15 3.6 0.5 mm 1 0.2 0.5 2.5 0.1 0.05 0.05 0.1 0.18 3.4 2.4 0.3 0.00 0.85 Note 1. Plastic or metal protrusions of 0.075 mm maximum per side are not included. REFERENCES EUROPEAN OUTLINE **ISSUE DATE** VERSION PROJECTION IEC JEDEC JEITA 02-10-17 $\blacksquare$ SOT763-1 - - -MO-241 - - -03-01-27

Fig. 17. Package outline SOT763-1 (DHVQFN16)

<sup>74</sup>AVC4T245

# 74AVC4T245

#### 4-bit dual supply translating transceiver with configurable voltage translation; 3-state

XQFN16: plastic, extremely thin quad flat package; no leads; 16 terminals; body 1.80 x 2.60 x 0.50 mm





Fig. 18. Package outline SOT1161-1 (XQFN16)

DHXQFN16: plastic, leadless dual in-line compatible thermal enhanced extreme thin quad flat package; no leads; 16 terminals; 0.4 mm pitch; body 2 mm x 2.4 mm x 0.48 mm





### 14. Abbreviations

Table 17. Abbreviati	ons
Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model

# 15. Revision history

#### Table 18. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74AVC4T245 v.8	20240411	Product data sheet	-	74AVC4T245 v.7
Modifications:	and MO-15			e drawings to JEDEC MS-012 atest JEDEC standard.
74AVC4T245 v.7	20210429	Product data sheet	-	74AVC4T245 v.6
Modifications:	• •	per 74AVC4T245BZ (SOT8 erating values for P <sub>tot</sub> total		,
74AVC4T245 v.6	20190320	Product data sheet	-	74AVC4T245 v.5
Modifications:	guidelines	t of this data sheet has bee of Nexperia. have been adapted to the	C C	
74AVC4T245 v.5	20151207	Product data sheet	-	74AVC4T245 v.4
Modifications:	• <u>Table 5</u> : co	onditions I <sub>CC</sub> and I <sub>GND</sub> chan	iged (errata).	J
74AVC4T245 v.4	20111207	Product data sheet	-	74AVC4T245 v.3
Modifications:	Legal page	es updated.	l	
74AVC4T245 v.3	20110922	Product data sheet	-	74AVC4T245 v.2
74AVC4T245 v.2	20101209	Product data sheet	-	74AVC4T245 v.1
74AVC4T245 v.1	20090720	Product data sheet	-	-

### 16. Legal information

#### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# Contents

2. Features and benefits.         3. Ordering information.         4. Marking.         5. Functional diagram.         6. Pinning information.         6.1. Pinning.         6.2. Pin description.         7. Functional description.         8. Limiting values.         9. Recommended operating conditions.         10. Static characteristics.         11. Dynamic characteristics.         12. Typical propagation delay characteristics.         13. Package outline.         14. Abbreviations.         15. Revision history.	1. General description	1
<ol> <li>Marking</li></ol>	2. Features and benefits	1
5. Functional diagram	3. Ordering information	2
6. Pinning information	4. Marking	2
6.1. Pinning	5. Functional diagram	2
<ul> <li>6.2. Pin description</li></ul>	6. Pinning information	3
<ol> <li>Functional description</li></ol>	6.1. Pinning	3
<ol> <li>8. Limiting values</li></ol>	6.2. Pin description	5
9. Recommended operating conditions	7. Functional description	5
10. Static characteristics	8. Limiting values	6
11. Dynamic characteristics	9. Recommended operating conditions	6
11.1. Waveforms and test circuit	10. Static characteristics	7
12. Typical propagation delay characteristics	11. Dynamic characteristics	10
<ul> <li>13. Package outline</li></ul>	11.1. Waveforms and test circuit	14
14. Abbreviations2 15. Revision history	12. Typical propagation delay characteristics	16
15. Revision history	13. Package outline	20
-	14. Abbreviations	25
16. Legal information	15. Revision history	25
	16. Legal information	26

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 11 April 2024