74CBTLV3257 Quad 1-of-2 multiplexer/demultiplexer Rev. 9 — 1 February 2024

1. General description

Х.

The 74CBTLV3257 provides a guad 1-of-2 high-speed multiplexer/demultiplexer with common select (S) and output enable (OE) inputs. The low ON resistance of the switch allows inputs to be connected to outputs without adding propagation delay or generating additional ground bounce noise. When pin OE = LOW, one of the two switches is selected (low-impedance ON-state) with pin S. When pin \overline{OE} = HIGH, all switches are in the high-impedance OFF-state, independent of pin S.

Schmitt trigger action at control input makes the circuit tolerant to slower input rise and fall times across the entire V_{CC} range from 2.3 V to 3.6 V.

To ensure the high-impedance OFF-state during power-up or power-down, OE should be tied to the V_{CC} through a pull-up resistor. The minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial power-down applications using I_{OFF}. The I_{OFF} circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

2. Features and benefits

- Supply voltage range from 2.3 V to 3.6 V
- High noise immunity
- Complies with JEDEC standard:
 - JESD8-5 (2.3 V to 2.7 V)
 - JESD8-B/JESD36 (2.7 V to 3.6 V)
- 5Ω switch connection between two ports
- Rail to rail switching on data I/O ports
- CMOS low power consumption
- Latch-up performance exceeds 250 mA per JESD78B Class I level A
- I_{OFF} circuitry provides partial Power-down mode operation
- ESD protection:
 - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V •
 - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Multiple package options
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

ne<mark>x</mark>peria

3. Ordering information

Type number	Package								
	Temperature range	Name	Description	Version					
74CBTLV3257D	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads; body width 3.9 mm	<u>SOT109-1</u>					
74CBTLV3257DS	-40 °C to +125 °C	SSOP16 [1]	plastic shrink small outline package; 16 leads; body width 3.9 mm; lead pitch 0.635 mm	<u>SOT519-1</u>					
74CBTLV3257PW	-40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads; body width 4.4 mm	<u>SOT403-1</u>					
74CBTLV3257BQ	-40 °C to +125 °C	+125 °C DHVQFN16 plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 × 3.5 × 0.85 mm		<u>SOT763-1</u>					
74CBTLV3257GU	-40 °C to +125 °C	XQFN16	plastic, extremely thin quad flat package; no leads; 16 terminals; body 1.80 × 2.60 × 0.50 mm	<u>SOT1161-1</u>					

[1] Also known as QSOP16.


4. Marking

Type number	Marking code[1]
74CBTLV3257D	74CBTLV3257D
74CBTLV3257DS	TLV3257
74CBTLV3257PW	TLV3257
74CBTLV3257BQ	TV3257
74CBTLV3257GU	b57


[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

74CBTLV3257

5. Functional diagram



6. Pinning information



6.1. Pinning

6.2. Pin description

Symbol	Pin		Description		
	SO16, (T)SSOP16 and DHVQFN16	XQFN16			
S	1	15	select input		
1B1 to 4B1	2, 5, 11, 14	16, 3, 9, 12	B1 input/output		
1B2 to 4B2	3, 6, 10, 13	1, 4, 8, 11	B2 input/output		
1A to 4A	4, 7, 9, 12	2, 5, 7, 10	A input/output		
GND	8	6	ground (0 V)		
ŌĒ	15	13	output enable input (active LOW)		
V _{CC}	16	14	supply voltage		

7. Functional description

Table 4. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care.

Inputs	Function switch		
OE	S		
L	L	nA = nB1	
L	Н	nA = nB2	
Н	X	disconnect nA and nBn	

74CBTLV3257

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			-0.5	+4.6	V
VI	input voltage	control inputs	[1]	-0.5	+4.6	V
V _{SW}	switch voltage	enable and disable mode	[2]	-0.5	V _{CC} + 0.5	V
I _{IK}	input clamping current	V _I < -0.5 V		-50	-	mA
I _{SK}	switch clamping current	V _I < -0.5 V		-50	-	mA
I _{SW}	switch current	$V_{SW} = 0 V \text{ to } V_{CC}$		-	±128	mA
I _{CC}	supply current			-	+100	mA
I _{GND}	ground current			-100	-	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C				
		SOT109-1 (SO16) SOT519-1 (SSOP16) SOT403-1 (TSSOP16) SOT763-1 (DHVQFN16)	[3]	-	500	mW
		SOT1161-1 (XQFN16)		-	250	mW

[1] The minimum input voltage rating may be exceeded if the input clamping current ratings are observed.

[2] The switch voltage ratings may be exceeded if switch clamping current ratings are observed

For SOT109-1 (SO16) package: P_{tot} derates linearly with 12.4 mW/K above 110 °C.
 For SOT519-1 (SSOP16) packages: P_{tot} derates linearly with 8.5 mW/K above 91 °C.

For SOT403-1 (TSSOP16) package: P_{tot} derates linearly with 8.5 mW/K above 91 °C.

For SOT763-1 (DHVQFN16) package: P_{tot} derates linearly with 11.2 mW/K above 106 °C.

9. Recommended operating conditions

Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Мах	Unit				
V _{CC}	supply voltage		2.3	3.6	V				
VI	input voltage		0	3.6	V				
V _{SW}	switch voltage	enable and disable mode	0	V _{CC}	V				
T _{amb}	ambient temperature		-40	+125	°C				
Δt/ΔV	input transition rise and fall rate	V _{CC} = 2.3 V to 3.6 V [1]	0	200	ns/V				

[1] Applies to control signal levels.

10. Static characteristics

Table 7. Static characteristics


At recommended operating conditions voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	T _{amb} :	T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		
			Min	Typ[1]	Max	Min	Max	-	
VIH	HIGH-level input	V _{CC} = 2.3 V to 2.7 V	1.7	-	-	1.7	-	V	
	voltage	V _{CC} = 3.0 V to 3.6 V	2.0	-	-	2.0	-	V	
VIL	LOW-level input	V _{CC} = 2.3 V to 2.7 V	-	-	0.7	-	0.7	V	
	voltage	V _{CC} = 3.0 V to 3.6 V	-	-	0.9	-	0.9	V	
lı	input leakage current	pin \overline{OE} , S; V _{CC} = 3.6 V; V _I = GND to V _{CC}	-	-	±1	-	±20	μA	
I _{S(OFF)}	OFF-state leakage current	V _{CC} = 3.6 V; see <u>Fig. 2</u>	-	-	±1	-	±20	μA	
I _{S(ON)}	ON-state leakage current	V _{CC} = 3.6 V; see <u>Fig. 3</u>	-	-	±1	-	±20	μA	
I _{OFF}	power-off leakage current	V_1 or $V_0 = 0$ V to 3.6 V; $V_{CC} = 0$ V	-	-	±10	-	±50	μA	
I _{CC}	supply current	$V_{I} = GND \text{ or } V_{CC};$ $V_{SW} = GND \text{ or } V_{CC};$ $V_{CC} = 3.6 \text{ V}; I_{O} = 0 \text{ A}$	-	-	10	-	50	μA	
ΔI _{CC}	additional supply current	$ \begin{array}{l} \mbox{pin } \overline{OE}, \ S; \ V_{CC} = 3.6 \ V; \\ V_1 = V_{CC} - 0.6 \ V; \\ V_{SW} = GND \ or \ V_{CC} \end{array} $	-	-	300	-	2000	μA	
CI	input capacitance	pin \overline{OE} , S; V _{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	0.9	-	-	-	pF	
C _{S(OFF)}	OFF-state capacitance	V_{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	5.2	-	-	-	pF	
C _{S(ON)}	ON-state capacitance	V_{CC} = 3.3 V; V _I = 0 V to 3.3 V	-	14.3	-	-	-	pF	

[1] All typical values are measured at T_{amb} = 25 °C.

[2] One input at 3 V, other inputs at V_{CC} or GND.

10.1. Test circuits



10.2. ON resistance


Table 8. Resistance R_{ON}

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 4.

Symbol	Parameter	Conditions	T _{amb} = -40 °C to +85 °C			T _{arr} -40 °C to	Unit	
			Min	Typ[1]	Max	Min	Мах	
R _{ON} ON resistance		V _{CC} = 2.3 V to 2.7 V; [2] see <u>Fig. 5</u> to <u>Fig. 7</u>						
		I _{SW} = 64 mA; V _I = 0 V	-	4.2	8.0	-	15.0	Ω
		I _{SW} = 24 mA; V _I = 0 V	-	4.2	8.0	-	15.0	Ω
		I _{SW} = 15 mA; V _I = 1.7 V	-	8.4	40.0	-	60.0	Ω
		V _{CC} = 3.0 V to 3.6 V; see <u>Fig. 8</u> to <u>Fig. 10</u>						
		I _{SW} = 64 mA; V _I = 0 V	-	4.0	7.0	-	11.0	Ω
		I _{SW} = 24 mA; V _I = 0 V	-	4.0	7.0	-	11.0	Ω
		I _{SW} = 15 mA; V _I = 2.4 V	-	6.2	15.0	-	25.5	Ω


[1] Typical values are measured at T_{amb} = 25 °C and nominal $V_{CC}.$

[2] Measured by the voltage drop between the A and B terminals at the indicated current through the switch. ON-state resistance is determined by the lower of the voltages of the two (A or B) terminals.




10.3. ON resistance test circuit and graphs

Quad 1-of-2 multiplexer/demultiplexer



74CBTLV3257

Quad 1-of-2 multiplexer/demultiplexer



11. Dynamic characteristics

Table 9. Dynamic characteristics

GND = 0 V; for test circuit see Fig. 13.

Symbol	Parameter	Conditions	T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
t _{pd}	propagation	nA to nBn or nBn to nA; see Fig. 11 [2] [3]						
	delay	V _{CC} = 2.3 V to 2.7 V	-	-	0.15	-	0.25	ns
		V _{CC} = 3.0 V to 3.6 V	-	-	0.15	-	0.25	ns
		S to nA; see <u>Fig. 11</u> [3]						
		V _{CC} = 2.3 V to 2.7 V	1.0	3.8	6.1	1.0	6.7	ns
		V _{CC} = 3.0 V to 3.6 V	1.0	3.2	5.3	1.0	5.8	ns
t _{en}	enable time	OE to nA or nBn; see Fig. 12[4]						
		V _{CC} = 2.3 V to 2.7 V	1.0	2.2	5.6	1.0	6.2	ns
		V _{CC} = 3.0 V to 3.6 V	1.0	2.0	5.0	1.0	5.5	ns
		S to nBn; see <u>Fig. 12</u> [4]						
		V _{CC} = 2.3 V to 2.7 V	1.0	3.5	6.1	1.0	6.7	ns
		V _{CC} = 3.0 V to 3.6 V	1.0	3.0	5.3	1.0	5.8	ns

Quad 1-of-2 multiplexer/demultiplexer

Symbol	Parameter	Conditions		T _{amb} = -40 °C to +85 °C			T _{amb} = -40 °C to +125 °C		
			Min	Typ[1]	Мах	Min	Max	1	
t _{dis} disa	disable time	OE to nA or nBn; see Fig. 12 [5]							
		V _{CC} = 2.3 V to 2.7 V	1.0	2.6	5.5	1.0	6.1	ns	
		V _{CC} = 3.0 V to 3.6 V	1.0	3.1	5.5	1.0	6.1	ns	
		S to nBn; see <u>Fig. 12</u> [5]							
		V _{CC} = 2.3 V to 2.7 V	1.0	2.6	4.8	1.0	5.3	ns	
		V _{CC} = 3.0 V to 3.6 V	1.0	3.2	4.5	1.0	5.0	ns	

[1]


All typical values are measured at T_{amb} = 25 °C and at nominal V_{CC} . The propagation delay is the calculated RC time constant of the typical on-state resistance of the switch and the load capacitance, [2] when driven by an ideal voltage source (zero output impedance).

 t_{pd} is the same as t_{PLH} and t_{PHL} . [3]

[4] t_{en} is the same as t_{PZH} and t_{PZL} .

 t_{dis} is the same as t_{PHZ} and t_{PLZ} . [5]


11.1. Waveforms and test circuit



Measurement points are given in Table 10.

Logic levels: V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.


Fig. 11. The data input (nA or nBn) to output (nBn or nA) propagation delays



Quad 1-of-2 multiplexer/demultiplexer

Table 10. Measurement points

Supply voltage	Input			Output	Output			
V _{cc}	V _M	VI	$t_r = t_f$	V _M	V _X	V _Y		
2.3 V to 2.7 V	$0.5 \times V_{CC}$	V _{CC}	≤ 2.0 ns	$0.5 \times V_{CC}$	V _{OL} + 0.15 V	V _{OH} - 0.15 V		
3.0 V to 3.6 V	$0.5 \times V_{CC}$	V _{CC}	≤ 2.0 ns	$0.5 \times V_{CC}$	V _{OL} + 0.3 V	V _{OH} - 0.3 V		



				́с П
т			= c_∟	RL
				Ŷ
	r h i	h,	h	r h i
				001aae331

Test data is given in Table 11.

Definitions for test circuit:

R_L = Load resistance;

 C_L = Load capacitance including jig and probe capacitance;

 R_T = Termination resistance should be equal to the output impedance Z_o of the pulse generator;

∐ R ///

 V_{EXT} = External voltage for measuring switching times.

Fig. 13. Test circuit for measuring switching times

Table 11. Test data	Tab	le 11.	Test	data
---------------------	-----	--------	------	------

Supply voltage	Load		V _{EXT}		
V _{cc}	CL	RL	t _{PLH} , t _{PHL}	t _{PZH} , t _{PHZ}	t _{PZL} , t _{PLZ}
2.3 V to 2.7 V	30 pF	500 Ω	open	GND	$2 \times V_{CC}$
3.0 V to 3.6 V	50 pF	500 Ω	open	GND	$2 \times V_{CC}$


11.2. Additional dynamic characteristics

Table 12. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); $V_I = GND$ or V_{CC} (unless otherwise specified); $t_r = t_f \le 2.5$ ns.

Symbol	Parameter	Conditions		T _{amb} = 25 °C		Unit	
				Min	Тур	Max	
f _(-3dB)	-3 dB frequency response	V_{CC} = 3.3 V; R _L = 50 Ω; see <u>Fig. 14</u>	[1]	-	398	-	MHz

[1] f_i is biased at 0.5 × V_{CC}.



74CBTLV3257

12. Package outline




Fig. 15. Package outline SOT109-1 (SO16)

Quad 1-of-2 multiplexer/demultiplexer




Fig. 16. Package outline SOT519-1 (SSOP16)

⁷⁴CBTLV3257

Quad 1-of-2 multiplexer/demultiplexer




Fig. 17. Package outline SOT403-1 (TSSOP16)




Fig. 18. Package outline SOT763-1 (DHVQFN16)

Quad 1-of-2 multiplexer/demultiplexer




Fig. 19. Package outline SOT1161-1 (XQFN16)

13. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model

14. Revision history

Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes			
74CBTLV3257 v.9	20240201	Product data sheet	-	74CBTLV3257 v.8			
Modifications:	• <u>Fig. 15, Fig</u>	 <u>Section 2</u>: ESD specification updated according to the latest JEDEC standard. <u>Fig. 15</u>, <u>Fig. 17</u>: Aligned SO and TSSOP package outline drawings to JEDEC MS-012 and MO-153 					
74CBTLV3257 v.8	20230321	Product data sheet	-	74CBTLV3257 v.7			
Modifications:	• <u>Table 5</u> : De	erating values for P _{tot} total p	ower dissipation u	updated.			
74CBTLV3257 v.7	20190409	Product data sheet	-	74CBTLV3257 v.6			
Modifications:	guidelines Legal texts 	 uidelines of Nexperia. Legal texts have been adapted to the new company name where appropriate. 					
74CBTLV3257 v.6	20171211	Product data sheet	-	74CBTLV3257 v.5			
Modifications:	Type numb	Type number 74CBTLV3257GU (SOT1161-1 / XQFN16) added.					
74CBTLV3257 v.5	20161111	Product data sheet	-	74CBTLV3257 v.4			
Modifications:	Section 11	• <u>Section 11.2</u> added.					
74CBTLV3257 v.4	20111216	Product data sheet	-	74CBTLV3257 v.3			
Modifications:	Legal page	Legal pages updated.					
74CBTLV3257 v.3	20110106	Product data sheet	-	74CBTLV3257 v.2			
74CBTLV3257 v.2	20101126	Product data sheet	-	74CBTLV3257 v.1			
74CBTLV3257 v.1	20100112	Product data sheet	-	-			

15. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

Quad 1-of-2 multiplexer/demultiplexer

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Marking	2
5. Functional diagram	3
6. Pinning information	4
6.1. Pinning	4
6.2. Pin description	5
7. Functional description	5
8. Limiting values	6
9. Recommended operating conditions	6
10. Static characteristics	7
10.1. Test circuits	7
10.2. ON resistance	8
10.3. ON resistance test circuit and graphs	8
11. Dynamic characteristics	10
11.1. Waveforms and test circuit	11
11.2. Additional dynamic characteristics	13
12. Package outline	14
13. Abbreviations	19
14. Revision history	19
15. Legal information	

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 1 February 2024