Quad single-pole single-throw analog switch Rev. 1 — 18 October 2023

**Product data sheet** 

## 1. General description

The 74HCT4316-Q100 is a quad single pole, single throw analog switch (SPST). Each switch features two input/output terminals (nY and nZ) and an active HIGH enable input (nS). When nS is LOW, the analog switch is turned off. When  $\overline{E}$  is HIGH all four analog switches are turned off. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of  $V_{CC}$ .

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

#### 2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
  - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- · High noise immunity
- Input levels \overline{E} and nS inputs: TTL level
- Low ON resistance:
  - 160 Ω (typical) at V<sub>CC</sub> V<sub>EE</sub> = 4.5 V
  - 120  $\Omega$  (typical) at  $V_{CC}$   $V_{EE}$  = 6.0 V
  - 80  $\Omega$  (typical) at  $V_{CC}$   $V_{EE}$  = 9.0 V
- Logic level translation:
  - To enable 5 V logic to communicate with ±5 V analog signals
- Typical break-before-make built in
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V

# 3. Applications

- Signal gating
- Modulation
- Demodulation
- Chopper


# 4. Ordering information


#### Table 1. Ordering information


Type number	Package			
	Temperature range	Name	Description	Version
74HCT4316D-Q100	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads; body width 3.9 mm	SOT109-1



# 5. Functional diagram








# 6. Pinning information

## 6.1. Pinning



## 6.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
1Z, 2Z, 3Z, 4Z	1, 4, 10, 13	independent input or output
1Y, 2Y, 3Y, 4Y	2, 3, 11, 12	independent input or output
Ē	7	enable input (active LOW)
GND	8	ground (0 V)
V <sub>EE</sub>	9	negative supply voltage
1S, 2S, 3S, 4S	15, 5, 6, 14	select input (active HIGH)
V <sub>CC</sub>	14	positive supply voltage

# 7. Functional description

#### Table 3. Function table

 $H = HIGH \ voltage \ level; \ L = LOW \ voltage \ level; \ X = don't \ care.$ 

Input					
Ē	nS				
L	L	OFF			
L	Н	ON			
Н	X	OFF			

## 8. Limiting values

#### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
$V_{CC}$	supply voltage		-0.5	+11.0	V
I <sub>IK</sub>	input clamping current	$V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$	-	±20	mA
I <sub>SK</sub>	switch clamping current	$V_{SW}$ < -0.5 V or $V_{SW}$ > $V_{CC}$ + 0.5 V	-	±20	mA
I <sub>SW</sub>	switch current	$V_{SW} = -0.5 \text{ V to } V_{CC} + 0.5 \text{ V}$ [1]	-	±25	mA
I <sub>EE</sub>	supply current		-	20	mA
I <sub>CC</sub>	supply current		-	50	mA
$I_{GND}$	ground current		-50	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb} = -40  ^{\circ}\text{C to } +125  ^{\circ}\text{C}$ [2]	-	500	mW
Р	power dissipation	per switch	-	100	mW

<sup>[1]</sup> To avoid drawing V<sub>CC</sub> current out of terminal nZ, when switch current flows in terminals nY, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal nZ, no V<sub>CC</sub> current will flow out of terminals nY. In this case there is no limit for the voltage drop across the switch, but the voltages at nY and nZ may not exceed V<sub>CC</sub> or V<sub>EE</sub>.

# 9. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage	see Fig. 5				
		V <sub>CC</sub> - GND	4.5	5.0	5.5	V
		V <sub>EE</sub> - GND	2.0	5.0	10.0	V
VI	input voltage		GND	-	V <sub>CC</sub>	V
V <sub>SW</sub>	switch voltage		V <sub>EE</sub>	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 4.5 V	-	1.67	139	ns/V




Fig. 5. Guaranteed operating area as a function of the supply voltages

<sup>[2]</sup> For SOT109-1 (SO16) package: Ptot derates linearly with 12.4 mW/K above 110 °C.

# 10. Static characteristics

#### Table 6. R<sub>ON</sub> resistance per switch

 $V_I = V_{IH}$  or  $V_{IL}$ ; for test circuit see Fig. 6.


 $V_{is}$  is the input voltage at a nY or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nY or nZ terminal, whichever is assigned as an output.

 $V_{\rm CC}$  - GND = 4.5 V and 5.5 V;  $V_{\rm CC}$  -  $V_{\rm EE}$  = 2.0 V, 4.5 V, 6.0 V and 9.0 V.

Symbol	Parameter	Conditions		25	°C	-40 °C to	o +85 °C	-40 °C to	+125 °C	Unit
			7	Тур	Max	Min	Max	Min	Max	
R <sub>ON(peak)</sub>	ON resistance	V <sub>is</sub> = V <sub>CC</sub> to V <sub>EE</sub>	[1]							
	(peak)	$V_{CC}$ = 2.0 V; $V_{EE}$ = 0 V; $I_{SW}$ = 100 $\mu A$		-	-	-	-	-	-	Ω
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V; I <sub>SW</sub> = 1000 μA	1	160	320	-	400	-	480	Ω
		$V_{CC} = 6.0 \text{ V}; V_{EE} = 0 \text{ V};$ $I_{SW} = 1000  \mu\text{A}$	1	120	240	-	300	-	360	Ω
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V; I <sub>SW</sub> = 1000 μA		85	170	-	215	-	255	Ω
R <sub>ON(rail)</sub>	ON resistance	$V_{is} = V_{EE}$	[1]							
	(rail)	$V_{CC}$ = 2.0 V; $V_{EE}$ = 0 V; $I_{SW}$ = 100 $\mu$ A	1	160	-	-	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V};$ $I_{SW} = 1000  \mu\text{A}$		80	160	-	200	-	240	Ω
		$V_{CC}$ = 6.0 V; $V_{EE}$ = 0 V; $I_{SW}$ = 1000 $\mu$ A		70	140	-	175	-	210	Ω
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V; I <sub>SW</sub> = 1000 μA		60	120	-	150	-	180	Ω
		$V_{is} = V_{CC}$	[1]							
		$V_{CC}$ = 2.0 V; $V_{EE}$ = 0 V; $I_{SW}$ = 100 $\mu$ A	1	170	-	-	-	-	-	Ω
		$V_{CC} = 4.5 \text{ V}; V_{EE} = 0 \text{ V};$ $I_{SW} = 1000  \mu\text{A}$		90	180	-	225	-	270	Ω
		$V_{CC}$ = 6.0 V; $V_{EE}$ = 0 V; $I_{SW}$ = 1000 $\mu$ A		80	160	-	200	-	240	Ω
		$V_{CC}$ = 4.5 V; $V_{EE}$ = -4.5 V; $I_{SW}$ = 1000 $\mu$ A		65	135	-	170	-	205	Ω
$\Delta R_{ON}$	ON resistance	$V_{is} = V_{CC}$ to $V_{EE}$	[1]							
	mismatch between	V <sub>CC</sub> = 2.0 V; V <sub>EE</sub> = 0 V		-	-	-	-	-	-	Ω
	channels	V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V		16	-	-	-	-	-	Ω
		V <sub>CC</sub> = 6.0 V; V <sub>EE</sub> = 0 V		9	-	-	-	-	-	Ω
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V		6	-	-	-	-	-	Ω

<sup>[1]</sup> When supply voltages ( $V_{CC}$  -  $V_{EE}$ ) near 2.0 V the analog switch ON resistance becomes extremely non-linear. When using a supply of 2 V, it is recommended to use these devices only for transmitting digital signals.



#### Table 7. Static characteristics 74HCT4316


At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

 $V_{is}$  is the input voltage at a nY or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nY or nZ terminal, whichever is assigned as an output.


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T <sub>amb</sub> = 2	5 °C		<u> </u>			'
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	1.6	-	V
V <sub>IL</sub>	LOW-level input voltage	oltage V <sub>CC</sub> = 4.5 V to 5.5 V		1.2	0.8	V
I <sub>I</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5 \text{ V}$ ; $V_{EE} = 0 \text{ V}$	-	-	±0.1	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Fig. 8$	-	-	±0.1	μΑ
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};$ $ V_{SW}  = V_{CC} - V_{EE}; \text{ see } Fig. 9$	-	-	±0.1	μΑ
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		V <sub>CC</sub> = 5.5 V; V <sub>EE</sub> = 0 V	-	-	8.0	μΑ
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = -5.0 V	-	-	16.0	μΑ
ΔI <sub>CC</sub>	additional supply current	nS and $\overline{E}$ ; per input pin; $V_I = V_{CC} - 2.1 \text{ V}$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 \text{ V}$ to 5.5 V; $V_{EE} = 0 \text{ V}$	-	50	180	μΑ
Cı	input capacitance		-	3.5	-	pF
C <sub>sw</sub>	switch capacitance		-	5	-	pF

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
T <sub>amb</sub> = -	40 °C to +85 °C				1	
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	-	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.8	V
l <sub>l</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5 \text{ V}$ ; $V_{EE} = 0 \text{ V}$	-	-	±1.0	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};  V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Fig. 8}}{2}$	-	-	±1.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};  V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Fig. 9}}{\text{ or } V_{IL}}$	-	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		V <sub>CC</sub> = 5.5 V; V <sub>EE</sub> = 0 V	-	-	80	μΑ
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = -5.0 V	-	-	160	μΑ
ΔI <sub>CC</sub>			-	-	225	μA
T <sub>amb</sub> = -	40 °C to +125 °C		<u> </u>	'	'	
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	-	-	V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.8	V
l <sub>l</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 5.5$ V; $V_{EE} = 0$ V	-	-	±1.0	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};  V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Fig. 8}}{2}$	-	-	±1.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	$V_{CC} = 10 \text{ V}; V_{EE} = 0 \text{ V}; V_{I} = V_{IH} \text{ or } V_{IL};  V_{SW}  = V_{CC} - V_{EE}; \text{ see } \frac{\text{Fig. 9}}{\text{CC}}$	-	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $V_{is} = V_{EE}$ or $V_{CC}$ ; $V_{os} = V_{CC}$ or $V_{EE}$				
		V <sub>CC</sub> = 5.5 V; V <sub>EE</sub> = 0 V	-	-	160	μΑ
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = -5.0 V	-	-	320	μΑ
ΔI <sub>CC</sub>	additional supply current	nS and $\overline{E}$ ; per input pin; $V_I = V_{CC} - 2.1 \text{ V}$ ; other inputs at $V_{CC}$ or GND; $V_{CC} = 4.5 \text{ V}$ to 5.5 V; $V_{EE} = 0 \text{ V}$	-	-	245	μA



 $V_{is}$  =  $V_{CC}$  and  $V_{os}$  =  $V_{EE}$  $V_{is}$  =  $V_{EE}$  and  $V_{os}$  =  $V_{CC}$ 

Fig. 8. Test circuit for measuring OFF-state leakage current



aaa-024856

 $V_{is} = V_{CC}$  and  $V_{os} =$  open  $V_{is} = V_{EE}$  and  $V_{os} =$  open

Fig. 9. Test circuit for measuring ON-state leakage current

# 11. Dynamic characteristics

#### **Table 8. Dynamic characteristics**

GND = 0 V;  $t_r = t_f = 6$  ns;  $C_L = 50$  pF unless specified otherwise; for test circuit see Fig. 12.

 $V_{is}$  is the input voltage at a nY or nZ terminal, whichever is assigned as an input.

 $V_{os}$  is the output voltage at a nY or nZ terminal, whichever is assigned as an output.

Symbol	Parameter	Conditions	25	°C	-40 °C to	o +85 °C	-40 °C to	+125 °C	Unit
			Тур	Max	Min	Max	Min	Max	
t <sub>pd</sub>	propagation delay	nY to nZ or nZ to nY; $R_L = \infty \Omega$ ; [1] see Fig. 10							
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	6	12	-	15	-	18	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	4	8	-	10	-	12	ns
t <sub>PZH</sub>	OFF-state	E to nY or nZ; see Fig. 11							
	to HIGH	V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	22	44	-	55	-	66	ns
	propagation delay	V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	19	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	21	42	-	53	-	63	ns
		nS to nY or nZ; see Fig. 11							
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	20	40	-	53	-	60	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	17	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	17	34	-	43	-	51	ns
t <sub>PZL</sub> OFF-state	E to nY or nZ; see Fig. 11								
	to LOW propagation	V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	28	56	-	70	-	84	ns
	delay	V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	24	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	21	42	-	53	-	63	ns
		nS to nY or nZ; see Fig. 11							
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	25	50	-	63	-	75	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	21	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	17	34	-	43	-	51	ns
t <sub>off</sub>	turn-off time	E to nY or nZ; see Fig. 11 [2]							
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	25	50	-	63	-	75	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	21	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	23	46	-	58	-	69	ns
		nS to nY or nZ; see Fig. 11 [2]							
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	22	44	-	55	-	66	ns
		V <sub>CC</sub> = 5.0 V; V <sub>EE</sub> = 0 V; C <sub>L</sub> = 15 pF	19	-	-	-	-	-	ns
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	20	40	-	50	-	60	ns
C <sub>PD</sub>	power dissipation capacitance	per switch; $V_I = GND$ to $(V_{CC} - 1.5 V)$ [3]	14	-	-	-	-	-	pF

 $\sum ((C_L + C_{sw}) \times V_{CC}^2 \times f_o) = \text{sum of outputs};$ 


C<sub>L</sub> = output load capacitance in pF;


 $C_{sw}$  = switch capacitance in pF;

V<sub>CC</sub> = supply voltage in V.

<sup>[3]</sup>  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum ((C_L + C_{sw}) \times V_{CC}^2 \times f_o)$  where:  $f_i$  = input frequency in MHz;  $f_o$  = output frequency in MHz;

## 11.1. Waveforms and test circuit





**Table 9. Measurement points** 

Туре	V <sub>I</sub>	V <sub>M</sub>
74HCT4316-Q100	3.0 V	1.3 V




Fig. 12. Test circuit for measuring switching times

S1 = Test selection switch.

#### Table 10. Test data

10010 101	. oot aata							
Test	Input					Output	S1 position	
	Ē	nS	Switch nY (nZ)	t <sub>r</sub> , t <sub>f</sub>		Switch nZ (nY)		_
	Vı		V <sub>is</sub>	V <sub>is</sub> at f <sub>max</sub> other [1] C <sub>L</sub>		C <sub>L</sub>	R <sub>L</sub>	
t <sub>PHL</sub> , t <sub>PLH</sub>	V <sub>I</sub> = 3 V		GND to V <sub>CC</sub>	< 2 ns	6 ns	50 pF	-	open
$t_{PHZ},t_{PZH}$	V <sub>I</sub> = 3 V		V <sub>CC</sub>	< 2 ns	6 ns	50 pF, 15 pF	1 kΩ	V <sub>EE</sub>
$t_{PLZ}, t_{PZL}$	V <sub>I</sub> = 3 V		V <sub>EE</sub>	< 2 ns	6 ns	50 pF, 15 pF	1 kΩ	V <sub>CC</sub>

<sup>[1]</sup>  $t_r = t_f = 6$  ns; when measuring  $f_{max}$ , there is no constraint to  $t_r$  and  $t_f$  with 50 % duty factor.


## 11.2. Additional dynamic characteristics

#### Table 11. Additional dynamic characteristics


Recommended conditions and typical values; GND = 0 V;  $T_{amb}$  = 25 °C;  $C_L$  = 50 pF.  $V_{is}$  is the input voltage at a nY or nZ terminal, whichever is assigned as an input.  $V_{os}$  is the output voltage at a nY or nZ terminal, whichever is assigned as an output.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
THD	total harmonic	$f_i$ = 1 kHz; $R_L$ = 10 kΩ; see <u>Fig. 13</u>				
THD to di	distortion	$V_{is}$ = 4.0 V (p-p); $V_{CC}$ = 2.25 V; $V_{EE}$ = -2.25 V		0.80	-	%
		$V_{is}$ = 8.0 V (p-p); $V_{CC}$ = 4.5 V; $V_{EE}$ = -4.5 V	-	0.40	-	%
		$f_i$ = 10 kHz; $R_L$ = 10 k $\Omega$ ; see Fig. 13				
		V <sub>is</sub> = 4.0 V (p-p); V <sub>CC</sub> = 2.25 V; V <sub>EE</sub> = -2.25 V	-	2.40	-	%
		$V_{is}$ = 8.0 V (p-p); $V_{CC}$ = 4.5 V; $V_{EE}$ = -4.5 V	-	0.80 - 0.40 -	%	
f <sub>(-3dB)</sub>	-3 dB frequency	$R_L = 50 \Omega$ ; $C_L = 10 pF$ ; see <u>Fig. 14</u> [1]				
	response	V <sub>CC</sub> = 2.25 V; V <sub>EE</sub> = -2.25 V	-	150	-	MHz
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	160	-	MHz
$\alpha_{iso}$	isolation (OFF-state)	$R_L = 600 \Omega$ ; $f_i = 1 MHz$ ; see Fig. 15 [2]				
		V <sub>CC</sub> = 2.25 V; V <sub>EE</sub> = -2.25 V	-	-50	-	dB
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-50	-	dB
V <sub>ct</sub>	crosstalk voltage	between digital input and switch (peak to peak value); $R_L = 600 \ \Omega$ ; $f_i = 1 \ \text{MHz}$ ; $\overline{E}$ or nS square wave between $V_{CC}$ and GND; $t_r = t_f = 6 \ \text{ns}$ ; see Fig. 16				
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = 0 V	-	110	-	mV
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	220	-	mV
Xtalk	crosstalk	between switches; $R_L = 600 \Omega$ ; $f_i = 1 MHz$ ; see Fig. 17 [2]				
		V <sub>CC</sub> = 2.25 V; V <sub>EE</sub> = -2.25 V	-	-60	-	dB
		V <sub>CC</sub> = 4.5 V; V <sub>EE</sub> = -4.5 V	-	-60	-	dB

- Adjust input voltage  $V_{is}$  to 0 dBm level at  $V_{os}$  for 1 MHz (0 dBm = 1 mW into 50  $\Omega$ ).
- Adjust input voltage  $V_{is}$  to 0 dBm level (0 dBm = 1 mW into 600  $\Omega$ ).




11 / 18




 $V_{CC}$  = 4.5 V; GND = 0 V;  $V_{EE}$  = -4.5 V;  $R_L$  = 50  $\Omega$ ;  $R_S$  = 1 k $\Omega$ .

a. Test circuit




b. Typical -3 dB frequency response

Fig. 14. -3 dB frequency response



 $V_{CC}$  = 4.5 V; GND = 0 V;  $V_{EE}$  = -4.5 V;  $R_L$  = 600  $\Omega$ ;  $R_S$  = 1 k $\Omega$ .

a. Test circuit



b. Isolation (OFF-state) as a function of frequency

Fig. 15. Isolation (OFF-state) as a function of frequency





Fig. 16. Test circuit for measuring crosstalk voltage (between the digital input and the switch)


13 / 18



# 12. Package outline



SOT109-1



UNIT	A max.	<b>A</b> <sub>1</sub>	A <sub>2</sub>	A <sub>3</sub>	bp	С	D <sup>(1)</sup>	E <sup>(1)</sup>	е	HE	L	Lp	Q	v	w	у	Z <sup>(1)</sup>	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	10.0 9.8	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01		0.0100 0.0075	0.39 0.38	0.16 0.15	0.05	0.244 0.228	0.041	0.039 0.016	0.028 0.020	0.01	0.01	0.004	0.028 0.012	0°

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE			
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE	
SOT109-1	076E07	MS-012				<del>99-12-27</del> 03-02-19	

Fig. 18. Package outline SOT109-1 (SO16)

## 13. Abbreviations

#### **Table 12. Abbreviations**

Acronym	Description
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model
TTL	Transistor-Transistor Logic

# 14. Revision history

#### **Table 13. Revision history**

Document ID	Release date	Data sheet status	Change notice	Supersedes
74HCT4316_Q100 v.1	20231018	Product data sheet	-	-

# 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

#### Quad single-pole single-throw analog switch

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

17 / 18

## **Contents**

1.	General description	. 1
2.	Features and benefits	. 1
3.	Applications	. 1
4.	Ordering information	.1
5.	Functional diagram	2
<b>6</b> .	Pinning information	.3
6.1.	Pinning	. 3
6.2.	Pin description	. 3
<b>7.</b> I	Functional description	. 3
8.	Limiting values	. 4
9. I	Recommended operating conditions	.4
10.	Static characteristics	5
11.	Dynamic characteristics	.8
11.1	. Waveforms and test circuit	. 9
11.2	2. Additional dynamic characteristics	11
12.	Package outline	15
	Abbreviations	
14.	Revision history	16
15.	Legal information	17
	_	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 18 October 2023

<sup>©</sup> Nexperia B.V. 2023. All rights reserved