Dual supply configurable multiple function gate

Rev. 6 — 17 June 2022

Product data sheet

1. General description

The 74AXP1T57 is a dual supply configurable multiple function gate with Schmitt-trigger inputs. It features three inputs (A, B and C), an output (Y) and dual supply pins (V_{CCI} and V_{CCO}). The inputs are referenced to V_{CCI} and the output is referenced to V_{CCO}. All inputs can be connected directly to V_{CCI} or GND. V_{CCI} can be supplied at any voltage between 0.7 V and 2.75 V and V_{CCO} can be supplied at any voltage between 1.2 V and 5.5 V. This feature allows voltage level translation. The 74AXP1T57 can be configured as any of the following logic functions AND, OR, NAND, NOR, XNOR, inverter and buffer.

This device ensures very low static and dynamic power consumption across the entire supply range and is fully specified for partial power down applications using I_{OFF} . The I_{OFF} circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

2. Features and benefits

- Wide supply voltage range:
 - V_{CCI}: 0.7 V to 2.75 V
 - V_{CCO}: 1.2 V to 5.5 V
- Low input capacitance; C_I = 0.6 pF (typical)
- Low output capacitance; C_O = 1.8 pF (typical)
- Low dynamic power consumption; $C_{PD} = 0.6 \text{ pF}$ at $V_{CCI} = 1.2 \text{ V}$ (typical)
- Low dynamic power consumption; C_{PD} = 7.1 pF at V_{CCO} = 3.3 V (typical)
- Low static power consumption; I_{CCI} = 0.5 µA (85 °C maximum)
- Low static power consumption; I_{CCO} = 1.8 µA (85 °C maximum)
- High noise immunity
- Complies with JEDEC standard:
 - JESD8-12A.01 (1.1 V to 1.3 V; A, B, C inputs)
 - JESD8-11A.01 (1.4 V to 1.6 V)
 - JESD8-7A (1.65 V to 1.95 V)
 - JESD8-5A.01 (2.3 V to 2.7 V)
 - JESD8-C (2.7 V to 3.6 V; Y output)
 - JESD12-6 (4.5 V to 5.5 V; Y output)
- ESD protection:
 - HBM ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 2 kV
 - CDM JESD22-C101E exceeds 1 kV
- Latch-up performance exceeds 100 mA per JESD78D Class II
- Inputs accept voltages up to 2.75 V
- Low noise overshoot and undershoot < 10% of V_{CCO}
- I_{OFF} circuitry provides partial power-down mode operation
- Multiple package options
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

ne<mark>x</mark>peria

3. Ordering information


Table 1. Ordering	g information			
Type number	Package			
	Temperature range	Name	Description	Version
74AXP1T57DC	-40 °C to +125 °C	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	<u>SOT765-1</u>
74AXP1T57GT	-40 °C to +125 °C	plastic extremely thin small outline package; no leads; 8 terminals; body 1 × 1.95 × 0.5 mm	<u>SOT833-1</u>	
74AXP1T57GN	-40 °C to +125 °C	XSON8	extremely thin small outline package; no leads; 8 terminals; body 1.2 × 1.0 × 0.35 mm	<u>SOT1116</u>
74AXP1T57GS	-40 °C to +125 °C	XSON8	extremely thin small outline package; no leads; 8 terminals; body 1.35 × 1.0 × 0.35 mm	<u>SOT1203</u>
74AXP1T57GX	-40 °C to +125 °C	X2SON8	plastic thermal enhanced extremely thin small outline package; no leads; 8 terminals; body 1.35 × 0.8 × 0.32 mm	<u>SOT1233-2</u>

4. Marking

Table 2. Marking	
Type number	Marking code[1]
74AXP1T57DC	rD
74AXP1T57GT	rD
74AXP1T57GN	rD
74AXP1T57GS	rD
74AXP1T57GX	rD


[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

5. Functional diagram



6. Pinning information

6.1. Pinning



6.2. Pin description

Symbol	Pin	Description
V _{CCI}	1	input supply voltage
A, B, C	2, 3, 7	data input
GND[1]	4, 5	ground (0 V)
Y	6	data output
V _{CCO}	8	output supply voltage

[1] All GND pins must be connected to ground (0 V).

7. Functional description

Table 4. Function table


H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.


Supply voltage		Input			Output
V _{CCI}	V _{cco}	C	В	Α	Y
0.7 V to 2.75 V	1.2 V to 5.5 V	L	L	L	Н
0.7 V to 2.75 V	1.2 V to 5.5 V	L	L	Н	L
0.7 V to 2.75 V	1.2 V to 5.5 V	L	н	L	Н
0.7 V to 2.75 V	1.2 V to 5.5 V	L	Н	Н	L
0.7 V to 2.75 V	1.2 V to 5.5 V	Н	L	L	L
0.7 V to 2.75 V	1.2 V to 5.5 V	Н	L	Н	L
0.7 V to 2.75 V	1.2 V to 5.5 V	Н	Н	L	Н
0.7 V to 2.75 V	1.2 V to 5.5 V	Н	Н	Н	Н
GND	1.2 V to 5.5 V	Х	X	X	Z
0.7 V to 2.75 V	GND	Х	X	X	Z
GND	GND	Х	X	X	Z

7.1. Logic configurations

Table 5. Function selection table

Logic function	Figure
2-input AND	see <u>Fig. 6</u>
2-input AND with both inputs inverted	see <u>Fig. 9</u>
2-input NAND with inverted input	see <u>Fig. 7</u> and <u>Fig. 8</u>
2-input OR with inverted input	see <u>Fig. 7</u> and <u>Fig. 8</u>
2-input NOR	see <u>Fig. 9</u>
2-input NOR with both inputs inverted	see <u>Fig. 6</u>
2-input XNOR	see <u>Fig. 10</u>
Inverter	see <u>Fig. 11</u>
Buffer	see Fig. 12





8. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CCI}	input supply voltage			-0.5	+3.3	V
V _{CCO}	output supply voltage			-0.5	+6.0	V
I _{IK}	input clamping current	V _I < 0 V		-50	-	mA
VI	input voltage		[1]	-0.5	+3.3	V
I _{OK}	output clamping current	V _O < 0 V		-50	-	mA
Vo	output voltage	Active mode	[1] [2]	-0.5	V _{CCO} + 0.5	V
		Power-down or 3-state mode	[1]	-0.5	+6.0	V
I _O	output current	$V_{O} = 0 V$ to V_{CCO}		-	±25	mA
I _{CCI}	input supply current			-	50	mA
I _{CCO}	output supply current			-	50	mA
I _{GND}	ground current			-50	-	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C				
		All packages except SOT1233-2	[3]	-	250	mW
		SOT1233-2 package	[4]	-	300	mW

The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed. [1]

V_{CCO} + 0.5 V should not exceed 6.0 V. [2]

For SOT765-1 (VSSOP8) package: Ptot derates linearly with 4.9 mW/K above 99 °C. [3] For SOT833-1 (XSON8) package: Ptot derates linearly with 3.1 mW/K above 68 °C. For SOT1116 (XSON8) package: P_{tot} derates linearly with 4.2 mW/K above 90 °C. For SOT1203 (XSON8) package: P_{tot} derates linearly with 3.6 mW/K above 81 °C. For SOT1233-2 (X2SON8) package: P_{tot} derates linearly with 7.7 mW/K above 118 °C.

[4]

9. Recommended operating conditions

Table 7. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CCI}	input supply voltage		0.7	2.75	V
V _{CCO}	output supply voltage		1.2	5.5	V
VI	input voltage		0	2.75	V
Vo	output voltage	Active mode	0	V _{cco}	V
		Power-down or 3-state mode	0	5.5	V
T _{amb}	ambient temperature		-40	+125	°C

10. Static characteristics

Table 8. Static characteristics

At recommended operating conditions, unless otherwise specified; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	٦	م ^{amb} = 25 °	0	T _{amb} = -40 °	°C to +85 °C	T _{amb} = -40 °	C to +125 °C	Unit
			Min	Typ[1]	Max	Min	Max	Min	Max	
V _{T+}	positive-going	see <u>Fig. 13</u> and <u>Fig. 14</u>								
	threshold voltage	V _{CCI} = 0.75 V to 0.85 V	0.3V _{CCI}	-	0.8V _{CCI}	0.3V _{CCI}	0.8V _{CCI}	0.3V _{CCI}	0.8V _{CCI}	V
		V _{CCI} = 1.1 V to 1.95 V	0.4V _{CCI}	-	0.7V _{CCI}	0.4V _{CCI}	0.7V _{CCI}	0.4V _{CCI}	0.7V _{CCI}	V
		V _{CCI} = 2.3 V to 2.7 V	0.9	-	1.7	0.9	1.7	0.9	1.7	V
V _{T-}	negative-going	see <u>Fig. 13</u> and <u>Fig. 14</u>								
	threshold voltage	V _{CCI} = 0.75 V to 0.85 V	0.2V _{CCI}	-	0.7V _{CCI}	0.2V _{CCI}	0.7V _{CCI}	0.2V _{CCI}	0.7V _{CCI}	V
		V _{CCI} = 1.1 V to 1.95 V	0.3V _{CCI}	-	0.6V _{CCI}	0.3V _{CCI}	0.6V _{CCI}	0.3V _{CCI}	0.6V _{CCI}	V
		V _{CCI} = 2.3 V to 2.7 V	0.7	-	1.5	0.7	1.5	0.7	1.5	V
V _H	hysteresis voltage	see <u>Fig. 13</u> and <u>Fig. 14</u>								
		V _{CCI} = 0.75 V to 0.85 V	0.06V _{CCI}	-	0.5V _{CCI}	0.06V _{CCI}	0.5V _{CCI}	0.06V _{CCI}	0.5V _{CCI}	V
		V _{CCI} = 1.1 V to 1.95 V	0.1V _{CCI}	-	0.4V _{CCI}	0.1V _{CCI}	0.4V _{CCI}	0.1V _{CCI}	0.4V _{CCI}	V
		V _{CCI} = 2.3 V to 2.7 V	0.2	-	1.0	0.2	1.0	0.2	1.0	V
V _{OH}	HIGH-level output	I _O = -2 mA; V _{CCO} = 1.2 V	-	1.05	-	-	-	-	-	V
	voltage	I _O = -3 mA; V _{CCO} = 1.4 V	1.05	-	-	1.05	-	1.05	-	V
		I _O = -4.5 mA; V _{CCO} = 1.65 V	1.2	-	-	1.2	-	1.2	-	V
		I _O = -8 mA; V _{CCO} = 2.3 V	1.7	-	-	1.7	-	1.7	-	V
		I _O = -10 mA; V _{CCO} = 3.0 V	2.2	-	-	2.2	-	2.2	-	V
		I _O = -12 mA; V _{CCO} = 4.5 V	3.7	-	-	3.7	-	3.7	-	V

Dual supply configurable multiple function gate

V _{OL} I ₁ I _{OZ}	Parameter	Conditions		T _{amb} = 25 °C	;	T _{amb} = -40 °	°C to +85 °C	T _{amb} = -40	Unit	
			Min	Typ[1]	Max	Min	Max	Min	Max	
V _{OL}	LOW-level output	I _O = 2 mA; V _{CCO} = 1.2 V	-	0.18	-	-	-	-	-	V
	voltage	I _O = 3 mA; V _{CCO} = 1.4 V	-	-	0.35	-	0.35	-	0.35	V
		I _O = 4.5 mA; V _{CCO} = 1.65 V	-	-	0.45	-	0.45	-	0.45	V
		I _O = 8 mA; V _{CCO} = 2.3 V	-	-	0.7	-	0.7	-	0.7	V
		I _O = 10 mA; V _{CCO} = 3.0 V	-	-	0.8	-	0.8	-	0.8	V
		I _O = 12 mA; V _{CCO} = 4.5 V	-	-	0.8	-	0.8	-	0.8	V
l _l	input leakage current	V_{I} = 0 V to 2.75 V; V_{CCI} = 0 V to 2.75 V	-	±0.001	±0.1	-	±0.5	-	±1.0	μA
I _{OZ}	OFF-state output current	V_{O} = 0 V to 5.5 V; V_{CCO} = 1.2 V to 5.5 V	-	±0.001	±0.1	-	±0.5	-	±2.0	μA
I _{OFF}	power-off leakage current	inputs; $V_I = 0 V$ to 2.75 V; $V_{CCI} = 0 V$; $V_{CCO} = 0 V$ to 5.5 V	-	±0.01	±0.1	-	±0.5	-	±2.0	μA
		output; $V_0 = 0 V$ to 5.5 V; $V_{CCO} = 0 V$; $V_{CCI} = 0 V$ to 2.75 V; $V_I = 0 V$ to 2.75 V	-	±0.01	±0.1	-	±0.5	-	±2.0	μA
ΔI _{OFF}	I _{OFF} additional power-off i	inputs; V _I = 0 V or 2.75 V; V _{CCI} = 0 V to 0.1 V; V _{CCO} = 0 V to 5.5 V	-	±0.02	±0.1	-	±0.5	-	±2.0	μA
		output; $V_0 = 0 V \text{ or } 5.5 V$; $V_{CCO} = 0 V \text{ to } 0.1 V$; $V_{CCI} = 0 V \text{ to } 2.75 V$; $V_I = 0 V \text{ or } 2.75 V$	-	±0.02	±0.1	-	±0.5	-	±2.0	μA

[1] Typical values are measured at $V_{CCI} = V_{CCO} = 1.2$ V unless otherwise specified.




Table 9. Static characteristics supply current

At recommended operating conditions, unless otherwise specified; voltages are referenced to GND (ground = 0 V).

	Parameter	Conditions	T _{amb}	= 25 °C	T _{amb} = -40 °	°C to +85 °C	T _{amb} = -40 °C to +125 °C	Unit
			Тур	Max	Тур	Max	Max	
I _{CCI}	input supply current	$V_{I} = 0 V \text{ or } V_{CCI};$						
		V _{CCI} = 0.7 V to 1.3 V [1]	1	100	10	300	500	nA
		V _{CCI} = 1.3 V to 2.75 V [2]	1	100	20	500	1000	nA
		V _{CCI} = 2.75 V; V _{CCO} = 0 V	1	100	20	500	1000	nA
		V _{CCI} = 0 V; V _{CCO} = 5.5 V	1	100	1	100	500	nA
I _{CCO}	output supply current	$V_I = 0 V \text{ or } V_{CCI}; I_O = 0 A; \text{ see } \underline{\text{Table } 10}$						
		V _{CCO} = 1.2 V to 3.6 V [1]	0.001	1.0	0.01	1.2	1.3	μA
		V _{CCO} = 3.6 V to 5.5 V [3]	0.8	1.5	1.0	1.8	2.0	μA
		V _{CCI} = 2.75 V; V _{CCO} = 0 V	0.001	0.1	0.003	0.2	0.5	μA
		V _{CCI} = 0 V; V _{CCO} = 3.6 V	0.2	0.6	0.3	0.8	1.2	μA
		V _{CCI} = 0 V; V _{CCO} = 5.5 V	0.4	0.8	0.5	1.0	1.5	μA
ΔI _{CCI}	additional input supply current	$V_{I} = V_{CCI} - 0.5 V; V_{CCI} = 2.5 V$	2	100	14	150	200	μA

[1] Typical values are measured at $V_{CCI} = V_{CCO} = 1.2$ V unless otherwise specified.

[2] Typical values are measured at $V_{CCI} = V_{CCO} = 2.5$ V.

[3] Typical values are measured at $V_{CCI} = 1.2$ V and $V_{CCO} = 5.0$ V.

Table 10. Typical output supply current (I_{CCO})

V _{CCI}	V _{cco}							Unit
	0 V	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V	
0 V	0	1	5	20	100	200	400	nA
0.8 V	1	10	150	200	300	500	800	nA
1.2 V	1	1	5	200	300	500	800	nA
1.5 V	1	1	5	100	300	500	800	nA
1.8 V	1	1	5	100	300	500	800	nA
2.5 V	1	1	5	100	100	500	800	nA

11. Dynamic characteristics

Table 11. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for waveform, see Fig. 15; for additional propagation delay graphs see Fig. 16 to #unique_15/unique_15_Connect_42_fig_s4k_wyy_hnb; for test circuit, see Fig. 22.

Symbol	Parameter	Conditions								Vcc	o <mark>[1]</mark>								Unit
			1.2 V	1.5	5 V ± 0.	1 V	1.8	V ± 0.1	15 V	2.5 V ± 0.2 V		2 V	3.3	3 V ± 0.	3 V	5.0) V ± 0.	5 V	
			Тур	Min	Тур	Max	Min	Тур	Max	Min	Тур	Мах	Min	Тур	Max	Min	Тур	Max	1
r _{amb} = 2	5 °C	1		I	1			1	1		1			1		<u> </u>	1	·	
bd	propagation	A, B and C to Y [2]																	
	delay	V _{CCI} = 0.75 V to 0.85 V	25	4	20	76	4	18	72	3	16	72	3	16	80	3	17	92	ns
		V _{CCI} = 1.1 V to 1.3 V	16.5	3.4	10.9	21.0	3.0	8.9	17.0	2.6	7.3	12.0	2.5	6.7	10.7	2.4	6.4	10.2	ns
		V _{CCI} = 1.4 V to 1.6 V	15.5	3.1	9.9	19.0	2.6	7.9	14.0	2.3	6.2	9.9	2.1	5.6	9.0	2.1	5.3	8.5	ns
		V _{CCI} = 1.65 V to 1.95 V	15.0	2.6	9.4	18.0	2.1	7.4	12.5	1.7	5.7	9.3	1.6	5.1	8.3	1.5	4.8	7.9	ns
		V _{CCI} = 2.3 V to 2.7 V	14.5	2.7	8.9	17.5	2.2	6.9	11.7	1.9	5.2	8.7	1.8	4.6	7.7	1.7	4.3	7.2	ns
amb = -4	0 °C to +85 °C	;	1	I	1			1	1					1	1		I	-	-
bd	propagation delay	A, B and C to Y [2]																	
		V _{CCI} = 0.75 V to 0.85 V	25	3	20	151	3	18	148	2	16	167	2	16	194	2	17	225	ns
		V _{CCI} = 1.1 V to 1.3 V	16.5	3.4	10.9	21.0	3.0	8.9	17.0	2.6	7.3	12.0	2.5	6.7	10.7	2.4	6.4	10.2	ns
		V _{CCI} = 1.4 V to 1.6 V	15.5	3.1	9.9	19.0	2.6	7.9	14.0	2.3	6.2	9.9	2.1	5.6	9.0	2.1	5.3	8.5	ns
		V _{CCI} = 1.65 V to 1.95 V	15.0	2.6	9.4	18.0	2.1	7.4	12.5	1.7	5.7	9.3	1.6	5.1	8.3	1.5	4.8	7.9	ns
		V _{CCI} = 2.3 V to 2.7 V	14.5	2.7	8.9	17.5	2.2	6.9	11.7	1.9	5.2	8.7	1.8	4.6	7.7	1.7	4.3	7.2	ns
_{amb} = -4	0 °C to +125 °	C																	
bd	propagation	A, B and C to Y [2]																	
	delay	V _{CCI} = 0.75 V to 0.85 V	25	3	20	151	3	18	148	2	16	167	2	16	194	2	17	225	ns
		V _{CCI} = 1.1 V to 1.3 V	16.5	3.4	10.9	21.0	3.0	8.9	17.5	2.6	7.3	15.0	2.5	6.7	13.0	2.4	6.4	12.0	ns
		V _{CCI} = 1.4 V to 1.6 V	15.5	3.1	9.9	20.0	2.6	7.9	16.5	2.3	6.2	12.0	2.1	5.6	10.9	2.1	5.3	10.3	ns
		V _{CCI} = 1.65 V to 1.95 V	15.0	2.6	9.4	19.0	2.1	7.4	15.5	1.7	5.7	11.3	1.6	5.1	10.4	1.5	4.8	9.7	ns
		V _{CCI} = 2.3 V to 2.7 V	14.5	2.7	8.9	18.0	2.2	6.9	14.5	1.9	5.2	10.6	1.8	4.6	9.6	1.7	4.3	8.9	ns

Nexperia

74AXP1T57

Dual supply configurable multiple function gate

Symbol	Parameter	Conditions		V _{CCO} [1] Un							Unit								
			1.2 V	1.2 V 1.5 V ± 0.1 V		1.8 V ± 0.15 V 2.5 V ± 0.2 V		2 V	3.3 V ± 0.3 V		3 V	5.0 V ± 0.5 V							
			Тур	Min	Тур	Мах	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Min	Тур	Мах	
L.	transition time	$V_{CCI} = 0.75 V \text{ to } 2.7 V$ [3]	-	1.0	-	-	1.0	-	-	1.0	-	-	1.0	-	-	1.0	-	-	ns

[1] Typical values are measured at nominal supply voltages and T_{amb} = +25 °C.

[2] t_{pd} is the same as t_{PLH} and t_{PHL} . [3] t_t is the same as t_{THL} and t_{TLH} .

Table 12. Typical dynamic characteristics at T_{amb} = 25 °C

Voltages are referenced to GND (ground = 0 V); for waveform, see Fig. 15; for additional propagation delay graphs see Fig. 16 to #unique_15/unique_15_Connect_42_fig_s4k_wyy_hnb; for test circuit, see Fig. 22.

Symbol	Parameter	Conditions			V	ссо			Unit
			1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V	
C _{PD}	power dissipation	$f_i = 1 \text{ MHz}; R_L = \infty \Omega; V_I = 0 \text{ V to } V_{CCI};$ [1]]						
	capacitance	input supply [2]						
		V _{CCI} = 0.8 V	0.5	0.5	0.5	0.5	0.5	0.5	pF
		V _{CCI} = 1.2 V	0.6	0.6	0.6	0.6	0.6	0.6	pF
		V _{CCI} = 1.5 V	0.7	0.7	0.7	0.7	0.7	0.7	pF
		V _{CCI} = 1.8 V	0.8	0.8	0.8	0.8	0.8	0.8	pF
		V _{CCI} = 2.5 V	1.0	1.0	1.0	1.0	1.0	1.0	pF
		output supply [3]						
		V _{CCI} = 0.8 V	6.7	6.8	6.8	6.9	7.5	9.5	pF
		V _{CCI} = 1.2 V	6.8	6.9	7.0	7.0	7.1	7.6	pF
		V _{CCI} = 1.5 V	6.9	6.9	6.9	7.0	7.1	7.6	pF
		V _{CCI} = 1.8 V	6.9	6.9	6.9	7.0	7.2	7.6	pF
		V _{CCI} = 2.5 V	6.9	7.0	7.0	7.0	7.2	7.6	pF
CI	input capacitance	$V_{I} = 0 V \text{ or } V_{CCI}; V_{CCI} = 0 V \text{ to } 2.7 V$	0.6	0.6	0.6	0.6	0.6	0.6	pF
Co	output capacitance	V _O = 0 V; V _{CCO} = 0 V	1.8	1.8	1.8	1.8	1.8	1.8	pF

[1] C_{PD} is used to determine the dynamic power dissipation (P_D in μW).

[2] Power dissipated from input supply (V_{CCI})

 $P_D = C_{PD} \times V_{CCI}^2 \times f_i \times N$ where:

 C_{PD} = power dissipation capacitance of the input supply;

V_{CCI} = input supply voltage in V;

f_i = input frequency in MHz;

N = number of inputs switching.

[3] Power dissipated from output supply (V_{CCO})

 $P_D = (C_L + C_{PD}) \times V_{CCO}^2 \times f_o$ where:


 C_L = load capacitance in pF;

C_{PD} = power dissipation capacitance of the output supply;

V_{CCO} = output supply voltage in V;

 f_o = output frequency in MHz.

12. Waveform, graphs and test circuit




Measurement points are given in <u>Table 13</u>.


V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.


Fig. 15. Input A, B and C to output Y propagation delay times and output transition times

Table 13. Measurement points

Supply voltage		Output	Input		
V _{CCI}	V _{cco}	V _M	V _M	VI	
0.75 V to 2.7 V	1.2 V to 5.5 V	0.5V _{CCO}	0.5V _{CCI}	V _{CCI}	







74AXP1T57

All information provided in this document is subject to legal disclaimers.

0

0

30

capacitance

 $T_{amb} = 25 \text{ °C}; V_{CCO} = 1.2 \text{ V}.$

Fig. 21. Additional propagation delay versus load

60

90

120

C_L (pF)

© Nexperia B.V. 2022. All rights reserved

Dual supply configurable multiple function gate




Table 14. Test data

Supply voltage		Load		Input		
V _{CCI}	V _{cco}	CL	RL	t _r , t _f	VI	
0.75 V to 2.7 V	1.2 V to 5.5 V	5 pF	5 kΩ	≤3.0 ns	V _{CCI}	

13. Package outline




Fig. 23. Package outline SOT765-1 (VSSOP8)




Fig. 24. Package outline SOT833-1 (XSON8)

Dual supply configurable multiple function gate

XSON8: extremely thin small outline package; no leads; 8 terminals; body 1.2 x 1.0 x 0.35 mm




Fig. 25. Package outline SOT1116 (XSON8)




Fig. 26. Package outline SOT1203 (XSON8)

Dual supply configurable multiple function gate




Fig. 27. Package outline SOT1233-2 (X2SON8)

21 / 24

14. Abbreviations

Table 15. Abbreviations							
Acronym	Description						
CDM	Charged Device Model						
DUT	Device Under Test						
ESD	ElectroStatic Discharge						
НВМ	Human Body Model						

15. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74AXP1T57 v.6	20220617	Product data sheet	-	74AXP1T57 v.5
Modifications:	 Values added 	SON8) package changed to Se for T _{amb} = -40 °C to +125 °C to ting values for P _{tot} total power o	emperature range thi	oughout the data sheet.
74AXP1T57 v.5	20170703	Product data sheet	-	74AXP1T57 v.4
Modifications:	• <u>Fig. 27</u> : Packa	age outline drawing for SOT12	33 / X2SON8) has ch	anged.
74AXP1T57 v.4	20161028	Product data sheet	-	74AXP1T57 v.3
Modifications:	Added type n	umber 74AXP1T57GX (SOT12	33/X2SON8)	l
74AXP1T57 v.3	20161007	Product data sheet	-	74AXP1T57 v.2
Modifications:	Type numbers	s 74AXP1T57DP and 74AXP1	T57GD removed.	·
74AXP1T57 v.2	20151222	Product data sheet	-	74AXP1T57 v.1
Modifications:	 <u>Table 6</u>: Dera <u>Table 7</u>: Conc <u>Table 8</u>: Conc <u>Table 9</u>: Conc <u>Table 11</u>: Conc 	litions V_O corrected (errata). ting values for packages added litions V_O corrected (errata). litions I_{OZ} corrected (errata). litions ΔI_{CCI} corrected (errata). ditions t_t corrected (errata). noved "leadless packages" fror		
74AXP1T57 v.1	20150803	Product data sheet		

16. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

Dual supply configurable multiple function gate

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Marking	2
5. Functional diagram	2
6. Pinning information	3
6.1. Pinning	3
6.2. Pin description	3
7. Functional description	4
7.1. Logic configurations	4
8. Limiting values	6
9. Recommended operating conditions	6
10. Static characteristics	7
11. Dynamic characteristics	
12. Waveform, graphs and test circuit	
13. Package outline	
14. Abbreviations	
15. Revision history	
16. Legal information	
U	

© Nexperia B.V. 2022. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 17 June 2022