# 74HC1G66-Q100; 74HCT1G66-Q100

Single-pole single-throw analog switch Rev. 3 — 5 December 2023

**Product data sheet** 

## 1. General description

The 74HC1G66-Q100; 74HCT1G66-Q100 is a single-pole, single-throw analog switch with two input/output terminals (nY and nZ) and a digital enable input (nE). When nE is LOW, the analog switch is turned off. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of  $V_{CC}$ .

The HCT device features control inputs with reduced input threshold levels to allow interfacing to TTL logic levels.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

## 2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
  - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Wide supply voltage range from 2.0 V to 10.0 V
- Very low ON resistance:
  - 45  $\Omega$  (typ.) at V<sub>CC</sub> = 4.5 V
  - 30  $\Omega$  (typ.) at V<sub>CC</sub> = 6.0 V
  - 25 Ω (typ.) at V<sub>CC</sub> = 9.0 V
- High noise immunity
- CMOS low power dissipation
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
  - Complies with JEDEC standards:
    - JESD8C (2.7 V to 3.6 V)
    - JESD7A (2.0 V to 6.0)
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V

## 3. Ordering information

#### Table 1. Ordering information


Type number	Package	kage								
	Temperature range	Name	Description	Version						
74HC1G66GW-Q100	-40 °C to +125 °C	TSSOP5	plastic thin shrink small outline package;	<u>SOT353-1</u>						
74HCT1G66GW-Q100	_		5 leads; body width 1.25 mm							
74HC1G66GV-Q100	-40 °C to +125 °C	SC-74A	plastic surface-mounted package; 5 leads	<u>SOT753</u>						
74HCT1G66GV-Q100	_									

# nexperia

## 4. Marking


Type number	Marking	
74HC1G66GW-Q100	HL	-
74HCT1G66GW-Q100	TL	
74HC1G66GV-Q100	H66	
74HCT1G66GV-Q100	T66	

# 5. Functional diagram



## 6. Pinning information

## 6.1. Pinning



## 6.2. Pin description

## Table 3. Pin description

Symbol	Pin	Description
Y	1	independent input or output
Z	2	independent input or output
GND	3	ground (0 V)
E	4	enable input (active HIGH)
V <sub>CC</sub>	5	supply voltage

## 7. Functional description

#### Table 4. Function table

H = HIGH voltage level; L = LOW voltage level.

Input E	Switch
L	OFF
Н	ON

## 8. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+11.0	V
I <sub>IK</sub>	input clamping current	$V_{\rm I}$ < -0.5 V or $V_{\rm I}$ > $V_{\rm CC}$ + 0.5 V	[1]	-	±20	mA
I <sub>SK</sub>	switch clamping current	$V_{\rm I}$ < -0.5 V or $V_{\rm I}$ > $V_{\rm CC}$ + 0.5 V	[1]	-	±20	mA
I <sub>SW</sub>	switch current	$V_{SW}$ > -0.5 V or $V_{SW}$ < $V_{CC}$ + 0.5 V		-	±25	mA
I <sub>CC</sub>	supply current			-	50	mA
I <sub>GND</sub>	ground current			-50	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C	[2]	-	250	mW

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For SOT353-1 (TSSOP5) package: P<sub>tot</sub> derates linearly with 3.3 mW/K above 74 °C.

For SOT753 (SC-74A) package:  $\mathsf{P}_{tot}$  derates linearly with 3.8 mW/K above 85 °C.

## 9. Recommended operating conditions

#### Table 6. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	74HC1G66-Q100			74HCT1G66-Q100			Unit
			Min	Тур	Max	Min	Тур	Max	
V <sub>CC</sub>	supply voltage		2.0	5.0	10.0	4.5	5.0	5.5	V
VI	input voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
V <sub>SW</sub>	switch voltage	[1]	0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	-40	+25	+125	°C
Δt/ΔV	input transition rise and	V <sub>CC</sub> = 2.0 V	-	-	625	-	-	-	ns/V
	fall rate	V <sub>CC</sub> = 4.5 V	-	1.67	139	-	1.67	139	ns/V
		V <sub>CC</sub> = 6.0 V	-	-	83	-	-	-	ns/V
		V <sub>CC</sub> = 10.0 V	-	-	35	-	-	-	ns/V

[1] To avoid drawing V<sub>CC</sub> current out of pin Z, when switch current flows in pin Y, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into pin Z, no V<sub>CC</sub> current will flow out of terminal Y. In this case there is no limit for the voltage drop across the switch, but the voltage at pins Y and Z may not exceed V<sub>CC</sub> or GND.

# **10. Static characteristics**

### Table 7. Static characteristics


Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	Unit	
			Min	Typ[1]	Max	Min	Max	
74HC1G	66-Q100	-	I			1		
V <sub>IH</sub>	HIGH-level	V <sub>CC</sub> = 2.0 V	1.5	1.2	-	1.5	-	V
	input voltage	V <sub>CC</sub> = 4.5 V	3.15	2.4	-	3.15	-	V
		V <sub>CC</sub> = 6.0 V	4.2	3.2	-	4.2	-	V
		V <sub>CC</sub> = 9.0 V	6.3	4.7	-	6.3	-	V
	LOW-level input	V <sub>CC</sub> = 2.0 V	-	0.8	0.5	-	0.5	V
	voltage	V <sub>CC</sub> = 4.5 V	-	2.1	1.35	-	1.35	V
		V <sub>CC</sub> = 6.0 V	-	2.8	1.8	-	1.8	V
		V <sub>CC</sub> = 9.0 V	-	4.3	2.7	-	2.7	V
l <sub>l</sub>	input leakage current	E; V <sub>I</sub> = V <sub>CC</sub> or GND						
		V <sub>CC</sub> = 6.0 V	-	0.1	1.0	-	1.0	μA
		V <sub>CC</sub> = 10.0 V	-	0.2	2.0	-	2.0	μA
I <sub>S(OFF)</sub>	OFF-state leakage current	Y or Z; V <sub>CC</sub> = 10 V; see <u>Fig. 4</u>	-	0.1	1.0	-	1.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	Y or Z; V <sub>CC</sub> = 10 V; see <u>Fig. 5</u>	-	0.1	1.0	-	1.0	μA
I <sub>CC</sub>	supply current	E, Y or Z; V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>SW</sub> = GND or V <sub>CC</sub>						
		V <sub>CC</sub> = 6.0 V	-	1.0	10	-	20	μA
		V <sub>CC</sub> = 10.0 V	-	2.0	20	-	40	μA
CI	input capacitance		-	1.5	-	-	-	pF
C <sub>S(ON)</sub>	ON-state capacitance		-	8	-	-	-	pF

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	o +125 °C	Unit
			Min	Typ[1]	Мах	Min	Мах	
74HCT1	G66-Q100	·						
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2.0	1.6	-	2.0	-	V
V <sub>IL</sub>	LOW-level input voltage	$V_{CC}$ = 4.5 V to 5.5 V	0.1	1.2	0.8	-	0.8	V
l <sub>l</sub>	input leakage current	E; $V_I = V_{CC}$ or GND; $V_{CC} = 5.5 V$	-	0.1	1.0	-	1.0	μA
I <sub>S(OFF)</sub>	OFF-state leakage current	Y or Z; V <sub>CC</sub> = 5.5 V; see <u>Fig. 4</u>	-	0.1	1.0	-	1.0	μA
I <sub>S(ON)</sub>	ON-state leakage current	Y or Z; V <sub>CC</sub> = 5.5 V; see <u>Fig. 5</u>	-	0.1	1.0	-	1.0	μA
I <sub>CC</sub>	supply current	E, Y or Z; $V_I = V_{CC}$ or GND; $V_{SW} = GND$ or $V_{CC}$ ; $V_{CC} = 4.5$ V to 5.5 V	-	1	10	-	20	μA
ΔI <sub>CC</sub>	additional supply current	$V_{I} = V_{CC} - 2.1 V; V_{CC} = 4.5 V \text{ to } 5.5 V;$ $I_{O} = 0 A$	-	-	500	-	850	μA
CI	input capacitance		-	1.5	-	-	-	pF
C <sub>S(ON)</sub>	ON-state capacitance		-	8	-	-	-	pF

[1] Typical values are measured at  $T_{amb}$  = 25 °C.

## 10.1. Test circuits



## 10.2. ON resistance


#### Table 8. ON resistance

At recommended operating conditions; voltages are referenced to GND (ground 0 V); for graph see Fig. 7.

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C t	Unit	
			Min	Typ[1]	Мах	Min	Max	
74HC1G6	6-Q100 [2]							
R <sub>ON(peak)</sub>	ON resistance	$V_{I}$ = GND to $V_{CC}$ ; see <u>Fig. 6</u>						
	(peak)	I <sub>SW</sub> = 0.1 mA; V <sub>CC</sub> = 2.0 V	-	-	-	-	-	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	42	118	-	142	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 6.0 V	-	31	105	-	126	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 9.0 V	-	23	88	-	105	Ω
R <sub>ON(rail)</sub>	ON resistance (rail)	V <sub>I</sub> = GND; see <u>Fig. 6</u>						
		I <sub>SW</sub> = 0.1 mA; V <sub>CC</sub> = 2.0 V	-	75	-	-	-	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	29	95	-	115	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 6.0 V	-	23	82	-	100	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 9.0 V	-	18	70	-	80	Ω
		V <sub>I</sub> = V <sub>CC</sub> ; see <u>Fig. 6</u>						
		I <sub>SW</sub> = 0.1 mA; V <sub>CC</sub> = 2.0 V	-	75	-	-	-	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	35	106	-	128	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 6.0 V	-	27	94	-	113	Ω
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 9.0 V	-	21	78	-	95	Ω
74HCT1G	66-Q100		·					
R <sub>ON(peak)</sub>	ON resistance	$V_{I} = GND$ to $V_{CC}$ ; see <u>Fig. 6</u>						
	(peak)	I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	42	118	-	142	Ω
R <sub>ON(rail)</sub>	ON resistance (rail)	V <sub>I</sub> = GND; see <u>Fig. 6</u>						
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	29	95	-	115	Ω
		V <sub>I</sub> = V <sub>CC</sub> ; see <u>Fig. 6</u>						
		I <sub>SW</sub> = 1 mA; V <sub>CC</sub> = 4.5 V	-	35	106	-	128	Ω

[1]

Typical values are measured at  $T_{amb}$  = 25 °C. At supply voltages approaching 2 V, the ON resistance becomes extremely non-linear. Therefore it is recommended that these devices [2] be used to transmit digital signals only, when using this supply voltage.



## 10.3. ON resistance test circuit and graphs

# **11. Dynamic characteristics**

### **Table 9. Dynamic characteristics**

Voltages are referenced to GND (ground = 0 V);  $C_L$  = 50 pF;  $R_L$  = 1 k $\Omega$ , unless otherwise specified.

For test circuit see Fig. 10.

Symbol	Parameter	Conditions		-40	°C to +85	5 °C	-40 °C t	o +125 °C	Unit
				Min	Typ[1]	Max	Min	Max	
74HC1G	66-Q100								
t <sub>pd</sub>	propagation delay	Y to Z or Z to Y; R <sub>L</sub> = ∞ Ω; see Fig. 8	[2]						
		V <sub>CC</sub> = 2.0 V		-	8	75	-	90	ns
		V <sub>CC</sub> = 4.5 V		-	3	15	-	18	ns
		V <sub>CC</sub> = 6.0 V		-	2	13	-	15	ns
		V <sub>CC</sub> = 9.0 V		-	1	10	-	12	ns
t <sub>en</sub>	enable time	E to Y or Z; see Fig. 9	[2]						
		V <sub>CC</sub> = 2.0 V		-	50	125	-	150	ns
		V <sub>CC</sub> = 4.5 V		-	16	25	-	30	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	11	-	-	-	ns
		V <sub>CC</sub> = 6.0 V		-	13	21	-	26	ns
		V <sub>CC</sub> = 9.0 V		-	9	16	-	20	ns
t <sub>dis</sub>	disable time	E to Y or Z; see Fig. 9	[2]						
		V <sub>CC</sub> = 2.0 V		-	27	190	-	225	ns
		V <sub>CC</sub> = 4.5 V		-	16	38	-	45	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	11	-	-	-	ns
		V <sub>CC</sub> = 6.0 V		-	14	33	-	38	ns
		V <sub>CC</sub> = 9.0 V		-	12	16	-	20	ns
C <sub>PD</sub>	power dissipation capacitance	$V_I = GND$ to $V_{CC}$	[3]	-	9	-	-	-	pF
74HCT1	G66-Q100	1							
t <sub>pd</sub>	propagation delay	Y to Z or Z to Y; $R_L = ∞ Ω$ ; see Fig. 8	[2]						
		V <sub>CC</sub> = 4.5 V		-	3	15	-	18	ns
t <sub>en</sub>	enable time	E to Y or Z; see Fig. 9	[2]						
		V <sub>CC</sub> = 4.5 V		-	15	30	-	36	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	12	-	-	-	ns
t <sub>dis</sub>	disable time	E to Y or Z; see Fig. 9	[2]						
		V <sub>CC</sub> = 4.5 V		-	13	44	-	53	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	12	-	-	-	ns
C <sub>PD</sub>	power dissipation capacitance	$V_{I} = GND$ to $V_{CC} - 1.5 V$	[3]	-	9	-	-	-	pF


[1] All typical values are measured at  $T_{amb}$  = 25 °C.

 $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .  $C_{PD}$  is used to determine the dynamic power dissipation  $P_D$  ( $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i + \Sigma((C_L \times C_{SW}) \times V_{CC}^2 \times f_o)$  where: [2] [3]

 $f_i =$  input frequency in MHz;  $f_o =$  output frequency in MHz;  $C_L =$  output load capacitance in pF;  $C_{SW} =$  maximum switch capacitance in pF (see <u>Table 7</u>);

 $V_{CC}$  = supply voltage in Volt;  $\Sigma((C_L \times C_{SW}) \times V_{CC}^2 \times f_0)$  = sum of outputs.






Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.

#### Fig. 9. Enable and disable times

Table 10. Measurement points								
Туре	/pe Input Output							
	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>				
74HC1G66-Q100	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>	V <sub>OL</sub> + 10%	V <sub>OH</sub> - 10%				
74HCT1G66-Q100	1.3 V	1.3 V	V <sub>OL</sub> + 10%	V <sub>OH</sub> - 10%				



#### Table 11. Test data

Туре	Input		Load	S1 position			
	VI	t <sub>r</sub> , t <sub>f</sub> [1]	CL	RL	t <sub>PHL</sub> , t <sub>PLH</sub>	t <sub>PZH</sub> , t <sub>PHZ</sub>	t <sub>PZL</sub> , t <sub>PLZ</sub>
74HC1G66-Q100	GND to V <sub>CC</sub>	6 ns	50 pF, 15 pF	1 kΩ, ∞ Ω	open	GND	V <sub>CC</sub>
74HCT1G66-Q100	GND to 3 V	6 ns	50 pF, 15 pF	1 kΩ, ∞ Ω	open	GND	V <sub>CC</sub>

[1] There is no constraint on  $t_r$ ,  $t_f$  with a 50% duty factor when measuring  $f_{max}$ .


## **11.2.** Additional dynamic characteristics

## Table 12. Additional dynamic characteristics for 74HC1G66 and 74HCT1G66


GND = 0 V;  $t_r = t_f = 6.0 \text{ ns}$ ;  $C_L = 50 \text{ pF}$ ; unless otherwise specified. All typical values are measured at  $T_{amb} = 25 \text{ °C}$ .


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
THD	total harmonic distortion	$f_i = 1 \text{ kHz}; R_L = 10 \text{ k}\Omega; \text{ see } \frac{\text{Fig. 11}}{1}$				%
		V <sub>CC</sub> = 4.5 V; V <sub>I</sub> = 4.0 V (p-p)	-	0.04	-	%
		V <sub>CC</sub> = 9.0 V; V <sub>I</sub> = 8.0 V (p-p)	-	0.02	-	%
		$f_i$ = 10 kHz; R <sub>L</sub> = 10 kΩ; see <u>Fig. 11</u>				
		V <sub>CC</sub> = 4.5 V; V <sub>I</sub> = 4.0 V (p-p)	-	0.12	-	%
		V <sub>CC</sub> = 9.0 V; V <sub>I</sub> = 8.0 V (p-p)	-	0.06	-	%
f <sub>(-3dB)</sub>	-3 dB frequency response	$R_L = 50 \Omega$ ; $C_L = 10 pF$ ; see <u>Fig. 12</u> and <u>Fig. 13</u>				
		V <sub>CC</sub> = 4.5 V	-	180	-	MHz
		V <sub>CC</sub> = 9.0 V	-	200	-	MHz
α <sub>iso</sub>	isolation (OFF-state)	$R_L$ = 600 $\Omega$ ; f <sub>i</sub> = 1 MHz; see <u>Fig. 14</u> and <u>Fig. 15</u>				
		V <sub>CC</sub> = 4.5 V	-	-50	-	dB
		V <sub>CC</sub> = 9.0 V	-	-50	-	dB

## 11.3. Test circuits and graphs





### Fig. 11. Test circuit for measuring total harmonic distortion












# 12. Package outline



#### Fig. 16. Package outline SOT353-1 (TSSOP5)




Fig. 17. Package outline SOT753 (SC-74A)

# 13. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
ESD	ElectroStatic Discharge
HBM	Human Body Model
TTL	Transistor-Transistor Logic
DUT	Device Under Test

# 14. Revision history

# Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74HC_HCT1G66_Q100 v.3	20231205	Product data sheet	-	74HC_HCT1G66_Q100 v.2	
Modifications	• <u>Section 2</u> : ESD specification updated according to the latest JEDEC standard.				
74HC_HCT1G66_Q100 v.2	20220127	Product data sheet	-	74HC_HCT1G66_Q100 v.1	
Modifications	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li><u>Section 2</u> updated.</li> <li><u>Table 5</u>: Derating values for P<sub>tot</sub> total power dissipation updated.</li> <li><u>Fig. 16</u>: Package outline drawing for SOT353-1 (TSSOP5) has changed</li> </ul>				
74HC_HCT1G66_Q100 v.1	20130916	Product data sheet	-	-	

# 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

#### Single-pole single-throw analog switch

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Marking	2
5. Functional diagram	2
6. Pinning information	2
6.1. Pinning	2
6.2. Pin description	2
7. Functional description	3
8. Limiting values	3
9. Recommended operating conditions	3
10. Static characteristics	4
10.1. Test circuits	5
10.2. ON resistance	6
10.3. ON resistance test circuit and graphs	7
11. Dynamic characteristics	8
11.1. Waveforms and test circuit	9
11.2. Additional dynamic characteristics	11
11.3. Test circuits and graphs	11
12. Package outline	13
13. Abbreviations	15
14. Revision history	15
15. Legal information	16

© Nexperia B.V. 2023. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 5 December 2023