Dual 10 Ω single-pole double-throw analog switch Rev. 5 — 21 August 2023 Produ

**Product data sheet** 

### 1. General description

The 74LVC2G3157 is a dual low-ohmic single-pole double-throw analog switch suitable for use as an analog or digital 2:1 multiplexer/demultiplexer. Each switch has a digital select input (nS), two independent inputs/outputs (nY0 and nY1) and a common input/output (nZ).

Schmitt trigger action at the select inputs makes the circuit tolerant of slower input rise and fall times across the entire  $V_{CC}$  range from 1.65 V to 5.5 V.

### 2. Features and benefits

- Wide supply voltage range from 1.65 V to 5.5 V
- Very low ON resistance:
  - 10.4  $\Omega$  (typical) at V<sub>CC</sub> = 2.7 V
  - 7.8  $\Omega$  (typical) at V<sub>CC</sub> = 3.3 V
  - 6.2 Ω (typical) at  $V_{CC}$  = 5 V
- Switch current capability of 32 mA
- Break-before-make switching
- High noise immunity
- CMOS low power consumption
- TTL interface compatibility at 3.3 V
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Select input accepts voltages up to 5.5 V
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

### 3. Ordering information

Table 1. Ordering inform	ation			
Type number	Package			
	Temperature range	Name	Description	Version
74LVC2G3157DP	-40 °C to +125 °C	TSSOP10	plastic thin shrink small outline package; 10 leads; body width 3 mm	<u>SOT552-1</u>


### 4. Marking

Table 2. Marking codes	
Type number	Marking code[1]
74LVC2G3157DP	YJ

[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.


# ne<mark>x</mark>peria

### 5. Functional diagram



# 6. Pinning information

### 6.1. Pinning



### 6.2. Pin description

Symbol	Pin	Description
1S	1	select input
1Y1	2	independent input or output
GND	3	ground (0 V)
2Y1	4	independent input or output
2S	5	select input
2Z	6	common output or input
2Y0	7	independent input or output
V <sub>CC</sub>	8	supply voltage
1Y0	9	independent input or output
1Z	10	common output or input

74LVC2G3157

### 7. Functional description

#### Table 4. Function table

H = HIGH voltage level; L = LOW voltage level.

Input nS	Channel on
L	nY0
Н	nY1

### 8. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	supply voltage		-0.5	+6.5	V
VI	input voltage	[1]	-0.5	+6.5	V
I <sub>IK</sub>	input clamping current	V <sub>1</sub> < -0.5 V	-50	-	mA
I <sub>SK</sub>	switch clamping current	$V_{\rm I}$ < -0.5 V or $V_{\rm I}$ > $V_{\rm CC}$ + 0.5 V	-	±50	mA
V <sub>SW</sub>	switch voltage	enable and disable mode [2]	-0.5	V <sub>CC</sub> + 0.5	V
I <sub>SW</sub>	switch current	$V_{SW}$ > -0.5 V or $V_{SW}$ < $V_{CC}$ + 0.5 V	-	±50	mA
I <sub>CC</sub>	supply current		-	100	mA
I <sub>GND</sub>	ground current		-100	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb} = -40 \ ^{\circ}C \ to \ +125 \ ^{\circ}C$ [3]	-	250	mW

[1] The minimum input voltage rating may be exceeded if the input current rating is observed.

[2] The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed.

[3] For SOT552-1 (TSSOP10) packages: P<sub>tot</sub> derates linearly with 8.3 mW/K above 120 °C.

# 9. Recommended operating conditions

#### Table 6. Recommended operating conditions

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage			1.65	-	5.5	V
VI	input voltage			0	-	5.5	V
V <sub>SW</sub>	switch voltage	enable and disable mode	[1]	0	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature			-40	-	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 1.65 V to 2.7 V	[2]	-	-	20	ns/V
		V <sub>CC</sub> = 2.7 V to 5.5 V	[2]	-	-	10	ns/V

[1] To avoid sinking GND current from terminal Z when switch current flows in terminal Yn, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal Z, no GND current will flow from terminal Yn. In this case, there is no limit for the voltage drop across the switch.


[2] Applies to control signal levels.

### 10. Static characteristics

#### **Table 7. Static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground 0 V).

Symbol	Parameter	Conditions		-40	°C to +8	5 °C	-40 °C to	o +125 ℃	Unit
				Min	Typ[1]	Max	Min	Max	1
VIH	HIGH-level input	V <sub>CC</sub> = 1.65 V to 1.95 V		0.65V <sub>CC</sub>	-	-	0.65V <sub>CC</sub>	-	V
	voltage	V <sub>CC</sub> = 2.3 V to 2.7 V		1.7	-	-	1.7	-	V
		V <sub>CC</sub> = 3 V to 3.6 V		2.0	-	-	2.0	-	V
		V <sub>CC</sub> = 4.5 V to 5.5 V		0.7V <sub>CC</sub>	-	-	0.7V <sub>CC</sub>	-	V
V <sub>IL</sub>	LOW-level input	V <sub>CC</sub> = 1.65 V to 1.95 V		-	-	$0.35V_{CC}$	-	0.35V <sub>CC</sub>	V
	voltage	V <sub>CC</sub> = 2.3 V to 2.7 V		-	-	0.7	-	0.7	V
		V <sub>CC</sub> = 3 V to 3.6 V		-	-	0.8	-	0.8	V
		V <sub>CC</sub> = 4.5 V to 5.5 V		-	-	0.3V <sub>CC</sub>		0.3V <sub>CC</sub>	V
l <sub>l</sub>	input leakage current	pin nS; V <sub>I</sub> = 5.5 V or GND; V <sub>CC</sub> = 0 V to 5.5 V	[2]	-	±0.1	±1	-	±1	μA
I <sub>S(OFF)</sub>	OFF-state leakage current	V <sub>CC</sub> = 5.5 V; see <u>Fig. 4</u>	[2]	-	±0.1	±0.2	-	±0.5	μA
I <sub>S(ON)</sub>	ON-state leakage current	V <sub>CC</sub> = 5.5 V; see <u>Fig. 5</u>	[2]	-	±0.1	±1	-	±2	μA
I <sub>CC</sub>	supply current	$V_{I} = 5.5 V \text{ or GND};$ $V_{SW} = GND \text{ or } V_{CC};$ $V_{CC} = 1.65 V \text{ to } 5.5 V$	[2]	-	0.1	4	-	4	μA
ΔI <sub>CC</sub>	additional supply current	pin nS; V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; V <sub>CC</sub> = 5.5 V; V <sub>SW</sub> = GND or V <sub>CC</sub>	[2]	-	5	500	-	500	μA
CI	input capacitance			-	2.5	-	-	-	pF
C <sub>S(OFF)</sub>	OFF-state capacitance			-	6.0	-	-	-	pF
C <sub>S(ON)</sub>	ON-state capacitance			-	18	-	-	-	pF



### 10.1. Test circuits

### 10.2. ON resistance

#### Table 8. ON resistance


At recommended operating conditions; voltages are referenced to GND (ground 0 V); for graphs see Fig. 7 to Fig. 12.

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	o +125 °C	Unit
			Min	Typ[1]	Мах	Min	Max	1
R <sub>ON(peak)</sub>	ON resistance	$V_I = GND$ to $V_{CC}$ ; see <u>Fig. 6</u>						
	(peak)	$I_{SW}$ = 4 mA; $V_{CC}$ = 1.65 V to 1.95 V	-	34.0	130	-	195	Ω
		$I_{SW}$ = 8 mA; $V_{CC}$ = 2.3 V to 2.7 V	-	12.0	30	-	45	Ω
		I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	10.4	25	-	38	Ω
		$I_{SW}$ = 24 mA; $V_{CC}$ = 3.0 V to 3.6 V	-	7.8	20	-	30	Ω
		$I_{SW}$ = 32 mA; $V_{CC}$ = 4.5 V to 5.5 V	-	6.2	15	-	23	Ω
R <sub>ON(rail)</sub>	ON resistance	V <sub>I</sub> = GND; see <u>Fig. 6</u>						
	(rail)	$I_{SW}$ = 4 mA; $V_{CC}$ = 1.65 V to 1.95 V	-	8.2	18	-	27	Ω
		$I_{SW}$ = 8 mA; $V_{CC}$ = 2.3 V to 2.7 V	-	7.1	16	-	24	Ω
		I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	6.9	14	-	21	Ω
		$I_{SW}$ = 24 mA; $V_{CC}$ = 3.0 V to 3.6 V	-	6.5	12	-	18	Ω
		$I_{SW}$ = 32 mA; $V_{CC}$ = 4.5 V to 5.5 V	-	5.8	10	-	15	Ω
		$V_{I} = V_{CC}$ ; see <u>Fig. 6</u>						
		$I_{SW}$ = 4 mA; $V_{CC}$ = 1.65 V to 1.95 V	-	10.4	30	-	45	Ω
		$I_{SW}$ = 8 mA; $V_{CC}$ = 2.3 V to 2.7 V	-	7.6	20	-	30	Ω
		I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	7.0	18	-	27	Ω
		$I_{SW}$ = 24 mA; $V_{CC}$ = 3.0 V to 3.6 V	-	6.1	15	-	23	Ω
		$I_{SW}$ = 32 mA; $V_{CC}$ = 4.5 V to 5.5 V	-	4.9	10	-	15	Ω


Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	• +125 °C	Unit
			Min	Typ[1]	Max	Min	Мах	
R <sub>ON(flat)</sub>	ON resistance	$V_{I} = GND \text{ to } V_{CC}$ [2]						
	(flatness)	$I_{SW}$ = 4 mA; $V_{CC}$ = 1.65 V to 1.95 V	-	26.0	-	-	-	Ω
		$I_{SW}$ = 8 mA; $V_{CC}$ = 2.3 V to 2.7 V	-	5.0	-	-	-	Ω
		I <sub>SW</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	3.5	-	-	-	Ω
		$I_{SW}$ = 24 mA; $V_{CC}$ = 3.0 V to 3.6 V	-	2.0	-	-	-	Ω
		$I_{SW}$ = 32 mA; $V_{CC}$ = 4.5 V to 5.5 V	-	1.5	-	-	-	Ω

[1] Typical values are measured at  $T_{amb}$  = 25 °C and nominal V<sub>CC</sub>.


[2] Flatness is defined as the difference between the maximum and minimum value of ON resistance measured at identical V<sub>CC</sub> and temperature.



### 10.3. ON resistance test circuit and graphs



#### Dual 10 $\Omega$ single-pole double-throw analog switch



74LVC2G3157

© Nexperia B.V. 2023. All rights reserved

# **11. Dynamic characteristics**

#### **Table 9. Dynamic characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 16.

SymbolParametertpdpropagation delaytenenable time		Conditions		) °C to +8	5 °C	-40 °C t	o +125 °C	Unit
			Min	Typ[1]	Мах	Min	Мах	-
t <sub>pd</sub>		nYn to nZ or nZ to nYn; see Fig. 13 [2]	3]					
	delay	V <sub>CC</sub> = 1.65 V to 1.95 V	-	-	2	-	3.0	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	-	1.2	-	2.0	ns
		V <sub>CC</sub> = 2.7 V	-	-	1.0	-	1.5	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	-	-	0.8	-	1.5	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	0.6	-	1.0	ns
t <sub>en</sub>	enable time	nS to nYn; see <u>Fig. 14</u>	4]					
		V <sub>CC</sub> = 1.65 V to 1.95 V	1	8.7	24	1	26.5	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	1	5.3	14	1	15.5	ns
		V <sub>CC</sub> = 2.7 V	1	4.9	14	1	15.5	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	0.5	4	7.6	0.5	8.5	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V	0.5	3	5.7	0.5	6.6	ns
t <sub>dis</sub>	disable time	nS to nYn; see <u>Fig. 14</u>	5]					
		V <sub>CC</sub> = 1.65 V to 1.95 V	2.5	6	13	2.5	14.5	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	2	4.4	7.5	2	8.5	ns
		V <sub>CC</sub> = 2.7 V	1.5	4.2	7.5	1.5	8.5	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.5	3.6	5.3	1.5	6	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V	0.8	2.9	3.8	0.8	4.5	ns
t <sub>b-m</sub>	break-before-	$C_L$ = 35 pF; $R_L$ = 50 Ω; see <u>Fig. 15</u>	6]					
	make time	V <sub>CC</sub> = 1.65 V to 1.95 V	0.5	-	-	0.5	-	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	0.5	-	-	0.5	-	ns
		V <sub>CC</sub> = 2.7 V	0.5	-	-	0.5	-	ns
		V <sub>CC</sub> = 3 V to 3.6 V	0.5	-	-	0.5	-	ns
		V <sub>CC</sub> = 4.5 V to 5.5 V	0.5	-	-	0.5	-	ns

Typical values are measured at  $T_{amb}$  = 25 °C and nominal V<sub>CC</sub>. [1]


[2]

 $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ . Propagation delay is the calculated RC time constant of the typical ON resistance of the switch and the specified capacitance when [3] driven by an ideal voltage source (zero output impedance).

 $t_{en}$  is the same as  $t_{\text{PZH}}$  and  $t_{\text{PZL}}.$ [4]

 $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ . Break-before-make specified by design. [5]

[6]




### 11.1. Waveforms and test circuits

Measurement points are given in Table 10.

Logic levels: V<sub>OL</sub> and V<sub>OH</sub> are typical output voltage levels that occur with the output load.


#### Fig. 13. Input (nYn or nZ) to output (nZ or nYn) propagation delays




### Table 10. Measurement points

Supply voltage	Input	Output				
V <sub>cc</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>		
1.65 V to 5.5 V	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V		

#### Dual 10 $\Omega$ single-pole double-throw analog switch



#### Fig. 15. Test circuit for measuring break-before-make timing



 $C_L$  = Load capacitance including jig and probe capacitance.

 $R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator.

 $V_{EXT}$  = Test voltage for switching times.

#### Fig. 16. Test circuit for measuring switching times

Supply voltage	Input	Input		Load				
V <sub>cc</sub>	VI	t <sub>r</sub> , t <sub>f</sub>	CL	RL	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>PZH,</sub> t <sub>PHZ</sub>	t <sub>PZL,</sub> t <sub>PLZ</sub>	
1.65 V to 1.95 V	V <sub>CC</sub>	≤ 2.0 ns	50 pF	500 Ω	open	GND	2V <sub>CC</sub>	
2.3 V to 2.7 V	V <sub>CC</sub>	≤ 2.0 ns	50 pF	500 Ω	open	GND	2V <sub>CC</sub>	
2.7 V	V <sub>CC</sub>	≤ 2.5 ns	50 pF	500 Ω	open	GND	2V <sub>CC</sub>	
3 V to 3.6 V	V <sub>CC</sub>	≤ 2.5 ns	50 pF	500 Ω	open	GND	2V <sub>CC</sub>	
4.5 V to 5.5 V	V <sub>CC</sub>	≤ 2.5 ns	50 pF	500 Ω	open	GND	2V <sub>CC</sub>	


# 11.2. Additional dynamic characteristics


#### Table 12. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); T<sub>amb</sub> = 25 °C.


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
THD	total harmonic distortion	$f_i$ = 600 Hz to 20 kHz; R <sub>L</sub> = 600 Ω; C <sub>L</sub> = 50 pF; V <sub>1</sub> = 0.5 V (p-p); see <u>Fig. 17</u>				
		V <sub>CC</sub> = 1.65 V	-	0.260	-	%
		V <sub>CC</sub> = 2.3 V	-	0.078	-	%
		V <sub>CC</sub> = 3.0 V	-	0.078	-	%
		V <sub>CC</sub> = 4.5 V	-	0.078	-	%
f <sub>(-3dB)</sub>	-3 dB frequency response	R <sub>L</sub> = 50 Ω; see <u>Fig. 18</u>				
		V <sub>CC</sub> = 1.65 V	-	200	-	MHz
		V <sub>CC</sub> = 2.3 V	-	300	-	MHz
		V <sub>CC</sub> = 3.0 V	-	300	-	MHz
		V <sub>CC</sub> = 4.5 V	-	300	-	MHz
α <sub>iso</sub>	isolation (OFF-state)	$R_L$ = 50 Ω; $C_L$ = 5 pF; $f_i$ = 10 MHz; see <u>Fig. 19</u>				
		V <sub>CC</sub> = 1.65 V	-	-42	-	dB
		V <sub>CC</sub> = 2.3 V	-	-42	-	dB
		V <sub>CC</sub> = 3.0 V	-	-40	-	dB
		V <sub>CC</sub> = 4.5 V	-	-40	-	dB
Xtalk	crosstalk	between switches; f <sub>i</sub> = 10 MHz; see Fig. 20				
		V <sub>CC</sub> = 1.65 V	-	-54	-	dB
		V <sub>CC</sub> = 2.3 V	-	-54	-	dB
		V <sub>CC</sub> = 3.0 V	-	-54	-	dB
		V <sub>CC</sub> = 4.5 V	-	-54	-	dB
Q <sub>inj</sub>	charge injection	$ \begin{array}{l} C_L = 0.1 \text{ nF; } V_{gen} = 0 \text{ V; } R_{gen} = 0  \Omega;  \text{f}_\text{i} = 1 \text{ MHz;} \\ R_L = 1  M\Omega; \text{ see } \overline{\text{Fig. } 21} \end{array} $				
		V <sub>CC</sub> = 1.8 V	-	3.3	-	рС
		V <sub>CC</sub> = 2.5 V	-	4.1	-	рС
		V <sub>CC</sub> = 3.3 V	-	5.0	-	рС
		V <sub>CC</sub> = 4.5 V	-	6.4	-	рС
		V <sub>CC</sub> = 5.5 V	-	7.5	-	рС

### 11.3. Test circuits







#### Fig. 18. Test circuit for measuring the frequency response when switch is in ON-state




#### Fig. 19. Test circuit for measuring isolation (OFF-state)



#### Dual 10 $\Omega$ single-pole double-throw analog switch



# 12. Package outline



#### Fig. 22. Package outline SOT552-1 (TSSOP10)

74LVC2G3157

# 13. Abbreviations

Table 13. Abbreviations				
Acronym	Description			
CDM	Charged Device Model			
CMOS	Complementary Metal-Oxide Semiconductor			
DUT	Device Under Test			
ESD	ElectroStatic Discharge			
HBM	Human Body Model			
TTL	Transistor-Transistor Logic			

# 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes			
74LVC2G3157 v.5	20230822	Product data sheet	-	74LVC2G3157 v.4			
Modifications:	• <u>Section 2</u> : E	• <u>Section 2</u> : ESD specification updated according to the latest JEDEC standard.					
74LVC2G3157 v.4	20210512	Product data sheet	-	74LVC2G3157 v.3			
Modifications:	••	<ul> <li>Type number 74LVC2G3157GM (SOT1049-3 / XQFN10) removed.</li> <li><u>Section 8</u>: Derating values for P<sub>tot</sub> total power dissipation updated.</li> </ul>					
74LVC2G3157 v.3	20190325	Product data sheet	-	74LVC2G3157 v.2			
Modifications:	guidelines o	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> </ul>					
74LVC2G3157 v.2	20161215	Product data sheet	-	74LVC2G3157 v.1			
Modifications:	• <u>Table 7</u> : The	• <u>Table 7</u> : The maximum limits for leakage current and supply current have changed.					
74LVC2G3157 v.1	20151214	Product data sheet	-	-			

# 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

#### Dual 10 $\Omega$ single-pole double-throw analog switch

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Marking	1
5. Functional diagram	2
6. Pinning information	2
6.1. Pinning	2
6.2. Pin description	2
7. Functional description	3
8. Limiting values	3
9. Recommended operating conditions	3
10. Static characteristics	4
10.1. Test circuits	5
10.2. ON resistance	5
10.3. ON resistance test circuit and graphs	6
11. Dynamic characteristics	9
11.1. Waveforms and test circuits	.10
11.2. Additional dynamic characteristics	. 12
11.3. Test circuits	. 13
12. Package outline	. 15
13. Abbreviations	. 16
14. Revision history	.16
15. Legal information	.17

© Nexperia B.V. 2023. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 21 August 2023