# 74LVC374A-Q100

Octal D-type flip-flop; 5 V tolerant inputs/outputs; positive-edge trigger; 3-state

Rev. 3 — 1 September 2023

**Product data sheet** 

### 1. General description

The 74LVC374A-Q100 is an octal positive-edge triggered D-type flip-flop with 3-state outputs. The device features a clock (CP) and output enable  $(\overline{OE})$  inputs. The flip-flops will store the state of their individual D-inputs that meet the set-up and hold time requirements on the LOW-to-HIGH clock (CP) transition. A HIGH on  $\overline{OE}$  causes the outputs to assume a high-impedance OFF-state. Operation of the  $\overline{OE}$  input does not affect the state of the flip-flops. Inputs can be driven from either 3.3 V or 5 V devices. This feature allows the use of these devices as translators in mixed 3.3 V and 5 V environments.

Schmitt-trigger action at all inputs makes the circuit tolerant of slower input rise and fall times.

This device is fully specified for partial power down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

This product has been qualified to the Automotive Electronics Council (AEC) standard Q100 (Grade 1) and is suitable for use in automotive applications.

#### 2. Features and benefits

- Automotive product qualification in accordance with AEC-Q100 (Grade 1)
  - Specified from -40 °C to +85 °C and from -40 °C to +125 °C
- Wide supply voltage range from 1.2 V to 3.6 V
- Overvoltage tolerant inputs to 5.5 V
- CMOS low power dissipation
- · Direct interface with TTL levels
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- · 8-bit positive edge-triggered register
- Independent register and 3-state buffer operation
- Complies with JEDEC standard:
  - JESD8-7A (1.65 V to 1.95 V)
  - JESD8-5A (2.3 V to 2.7 V)
  - JESD8-C/JESD36 (2.7 V to 3.6 V)
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- DHVQFN package with Side-Wettable Flanks enabling Automatic Optical Inspection (AOI) of solder joints





# 3. Ordering information


**Table 1. Ordering information** 

Type number	Package										
	Temperature range	Name	Description	Version							
74LVC374AD-Q100	-40 °C to +125 °C	SO20	plastic small outline package; 20 leads; body width 7.5 mm	SOT163-1							
74LVC374APW-Q100	-40 °C to +125 °C	TSSOP20	plastic thin shrink small outline package; 20 leads; body width 4.4 mm	SOT360-1							
74LVC374ABQ-Q100	-40 °C to +125 °C	DHVQFN20	plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 20 terminals; body 2.5 × 4.5 × 0.85 mm	SOT764-1							

# 4. Functional diagram








### 5. Pinning information

### 5.1. Pinning



**Product data sheet** 

### 5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
ŌĒ	1	output enable input (active LOW)
Q0, Q1, Q2, Q3, Q4, Q5, Q6, Q7	2, 5, 6, 9, 12, 15, 16, 19	3-state flip-flop output
D0, D1, D2, D3, D4, D5, D6, D7	3, 4, 7, 8, 13, 14, 17, 18	data input
GND	10	ground (0 V)
CP	11	clock input (LOW-to-HIGH, edge-triggered)
V <sub>CC</sub>	20	supply voltage

### 6. Functional description

#### Table 3. Function table

H = HIGH voltage level; h = HIGH voltage level one set-up time prior to the LOW-to-HIGH CP transition;

L = LOW voltage level; I = LOW voltage level one set-up time prior to the LOW-to-HIGH CP transition;

 $Z = high-impedance \ OFF-state; \uparrow = LOW-to-HIGH \ clock \ transition.$ 

Operating mode	Input	Internal flip-flop	Output			
	ŌE CP Dn					
Load and read register	L	1	I	L	L	
	L	1	h	Н	Н	
3	Н	1	I	L	Z	
outputs	Н	1	h	Н	Z	

### 7. Limiting values

### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+6.5	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V		-50	-	mA
VI	input voltage		[1]	-0.5	+6.5	V
I <sub>OK</sub>	output clamping current	$V_O > V_{CC}$ or $V_O < 0$ V		-	±50	mA
Vo	output voltage	output HIGH or LOW state	[2]	-0.5	V <sub>CC</sub> + 0.5	V
		output 3-state	[2]	-0.5	+6.5	V
Io	output current	$V_O = 0 V \text{ to } V_{CC}$		-	±50	mA
I <sub>CC</sub>	supply current			-	100	mA
I <sub>GND</sub>	ground current			-100	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C	[3]	-	500	mW

<sup>[1]</sup> The minimum input voltage ratings may be exceeded if the input current ratings are observed.

<sup>[2]</sup> The output voltage ratings may be exceeded if the output current ratings are observed.

<sup>[3]</sup> For SOT163-1 (SO20) package: P<sub>tot</sub> derates linearly with 12.3 mW/K above 109 °C. For SOT360-1 (TSSOP20) package: P<sub>tot</sub> derates linearly with 10.0 mW/K above 100 °C. For SOT764-1 (DHVQFN20) package: P<sub>tot</sub> derates linearly with 12.9 mW/K above 111 °C.

# 8. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage		1.65	-	3.6	V
		functional	1.2	-	-	V
VI	input voltage		0	-	5.5	V
Vo	output voltage	output HIGH or LOW state	0	-	V <sub>CC</sub>	V
		output 3-state	0	-	5.5	V
T <sub>amb</sub>	ambient temperature	in free air	-40	-	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 1.65 V to 2.7 V	0	-	20	ns/V
		V <sub>CC</sub> = 2.7 V to 3.6 V	0	-	10	ns/V

### 9. Static characteristics

#### **Table 6. Static characteristics**

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	Unit	
			Min	Typ[1]	Max	Min	Max	
V <sub>IH</sub>	HIGH-level	V <sub>CC</sub> = 1.2 V	1.08	-	-	1.08	-	V
	input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	0.65V <sub>CC</sub>	-	-	0.65V <sub>CC</sub>	-	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.7	-	-	1.7	-	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	2.0	-	-	2.0	-	V
V <sub>IL</sub>	LOW-level input	V <sub>CC</sub> = 1.2 V	-	-	0.12	-	0.12	V
	voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	-	-	0.35V <sub>CC</sub>	-	0.35V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	-	0.7	-	0.7	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	0.8	-	0.8	V
V <sub>OH</sub>	HIGH-level	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>						
	output voltage	$I_O = -100 \mu A;$ $V_{CC} = 1.65 \text{ V to } 3.6 \text{ V}$	V <sub>CC</sub> - 0.2	-	-	V <sub>CC</sub> - 0.3	-	V
		I <sub>O</sub> = -4 mA; V <sub>CC</sub> = 1.65 V	1.2	-	-	1.05	-	V
		I <sub>O</sub> = -8 mA; V <sub>CC</sub> = 2.3 V	1.8	-	-	1.65	-	V
		I <sub>O</sub> = -12 mA; V <sub>CC</sub> = 2.7 V	2.2	-	-	2.05	-	V
		$I_{O}$ = -18 mA; $V_{CC}$ = 3.0 V	2.4	-	-	2.25	-	V
		$I_{O}$ = -24 mA; $V_{CC}$ = 3.0 V	2.2	-	-	2.0	-	V
V <sub>OL</sub>	LOW-level	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>						
	output voltage	$I_O = 100 \mu A;$ $V_{CC} = 1.65 \text{ V to } 3.6 \text{ V}$	-	-	0.2	-	0.3	V
		I <sub>O</sub> = 4 mA; V <sub>CC</sub> = 1.65 V	-	-	0.45	-	0.65	V
		I <sub>O</sub> = 8 mA; V <sub>CC</sub> = 2.3 V	-	-	0.6	-	0.8	V
		I <sub>O</sub> = 12 mA; V <sub>CC</sub> = 2.7 V	-	-	0.4	-	0.6	V
		I <sub>O</sub> = 24 mA; V <sub>CC</sub> = 3.0 V	-	-	0.55	-	0.8	V
l <sub>l</sub>	input leakage current	V <sub>CC</sub> = 3.6 V; V <sub>I</sub> = 5.5 V or GND	-	±0.1	±5	-	±20	μA
l <sub>OZ</sub>	OFF-state output current	$V_I = V_{IH} \text{ or } V_{IL}; V_{CC} = 3.6 \text{ V}; V_O = 5.5 \text{ V or GND};$	-	±0.1	±5	-	±20	μA

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to	+125 °C	Unit
			Min	Typ[1]	Max	Min	Max	
I <sub>OFF</sub>	power-off leakage current	$V_{CC} = 0 \text{ V}; V_{I} \text{ or } V_{O} = 5.5 \text{ V}$	-	±0.1	±10	-	±20	μΑ
I <sub>CC</sub>	supply current	$V_{CC} = 3.6 \text{ V}; V_{I} = V_{CC} \text{ or GND}; $ $I_{O} = 0 \text{ A}$	-	0.1	10	-	40	μΑ
ΔI <sub>CC</sub>	additional supply current	per input pin; $V_{CC} = 2.7 \text{ V to } 3.6 \text{ V};$ $V_I = V_{CC} - 0.6 \text{ V}; I_O = 0 \text{ A}$	-	5	500	-	5000	μΑ
Cı	input capacitance	$V_{CC}$ = 0 V to 3.6 V; $V_I$ = GND to $V_{CC}$	-	4.0	-	-	-	pF

<sup>[1]</sup> All typical values are measured at  $V_{CC}$  = 3.3 V (unless stated otherwise) and  $T_{amb}$  = 25 °C.

# 10. Dynamic characteristics

**Table 7. Dynamic characteristics** 

Voltages are referenced to GND (ground = 0 V). For test circuit see Fig. 8.


Symbol	Parameter	Conditions	-40	0 °C to +85	°C	-40 °C to	Unit	
			Min	Typ[1]	Max	Min	Max	
t <sub>pd</sub>	propagation	CP to Qn; see Fig. 5 [2]						
	delay	V <sub>CC</sub> = 1.2 V	-	16	-	-	-	ns
		V <sub>CC</sub> = 1.65 V to 1.95 V	2.2	7.4	16.3	2.2	18.8	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.5	3.9	8.4	1.5	9.7	ns
		V <sub>CC</sub> = 2.7 V	1.5	3.5	8.0	1.5	10.0	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.5	3.3	7.0	1.5	9.0	ns
t <sub>en</sub>	enable time	OE to Qn; see Fig. 6 [2]						
		V <sub>CC</sub> = 1.2 V	-	19	-	-	-	ns
		V <sub>CC</sub> = 1.65 V to 1.95 V	1.5	6.6	16.7	1.5	19.3	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.5	3.7	9.3	1.5	10.8	ns
		V <sub>CC</sub> = 2.7 V	1.5	3.8	8.5	1.5	11.0	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.5	3.0	7.5	1.5	9.5	ns
t <sub>dis</sub> disable tin	disable time	OE to Qn; see Fig. 6 [2]						
		V <sub>CC</sub> = 1.2 V	-	8.0	-	-	-	ns
		V <sub>CC</sub> = 1.65 V to 1.95 V	2.3	4.0	10.1	2.3	11.7	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.0	2.2	5.7	1.0	6.7	ns
		V <sub>CC</sub> = 2.7 V	1.5	3.1	6.5	1.5	9.0	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.5	2.9	6.0	1.5	7.5	ns
t <sub>W</sub>	pulse width	CP HIGH or LOW; see Fig. 5						
		V <sub>CC</sub> = 1.65 V to 1.95 V	5.0	-	-	5.0	-	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	4.0	-	-	4.0	-	ns
		V <sub>CC</sub> = 2.7 V	3.0	-	-	4.5	-	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	3.0	1.5	-	4.5	-	ns
t <sub>su</sub>	set-up time	Dn to CP; see Fig. 7						
		V <sub>CC</sub> = 1.65 V to 1.95 V	4.0	-	-	4.0	-	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V	3.0	-	-	3.0	-	ns
		V <sub>CC</sub> = 2.7 V	2.0	-	-	2.0	-	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V	2.0	0	-	2.0	-	ns

Symbol	Parameter	Conditions		-40	0 °C to +85	°C	-40 °C to	+125 °C	Unit
				Min	Typ[1]	Max	Min	Max	
t <sub>h</sub>	hold time	Dn to CP; see Fig. 7							
		V <sub>CC</sub> = 1.65 V to 1.95 V		3.0	-	-	3.0	-	ns
		V <sub>CC</sub> = 2.3 V to 2.7 V		2.0	-	-	2.0	-	ns
		V <sub>CC</sub> = 2.7 V		1.5	-	-	1.5	-	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V		1.5	0.6	-	1.5	-	ns
f <sub>max</sub>	maximum	see Fig. 5							
	frequency	V <sub>CC</sub> = 1.65 V to 1.95 V		100	-	-	64	-	MHz
		V <sub>CC</sub> = 2.3 V to 2.7 V		125	-	-	100	-	MHz
		V <sub>CC</sub> = 2.7 V		150	-	-	120	-	MHz
		V <sub>CC</sub> = 3.0 V to 3.6 V		150	-	-	120	-	MHz
t <sub>sk(o)</sub>	output skew time	V <sub>CC</sub> = 3.0 V to 3.6 V	[3]	-	-	1.0	-	1.5	ns
C <sub>PD</sub>	power	per flip-flop; $V_I$ = GND to $V_{CC}$	[4]						
	dissipation capacitance	V <sub>CC</sub> = 1.65 V to 1.95 V		-	11.6	-	-	-	pF
	capacitatice	V <sub>CC</sub> = 2.3 V to 2.7 V		-	13.6	-	-	-	pF
		V <sub>CC</sub> = 3.0 V to 3.6 V		-	15.4	-	-	-	pF

- Typical values are measured at T<sub>amb</sub> = 25 °C and V<sub>CC</sub> = 1.2 V, 1.8 V, 2.5 V, 2.7 V and 3.3 V respectively.
- $t_{\text{pd}}$  is the same as  $t_{\text{PLH}}$  and  $t_{\text{PHL}}.$ 
  - $t_{\text{en}}$  is the same as  $t_{\text{PZL}}$  and  $t_{\text{PZH}}$ .
- $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ . Skew between any two outputs of the same package switching in the same direction. This parameter is guaranteed by design.
- $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma (C_L \times V_{CC}^2 \times f_o)$  where:

  - f<sub>i</sub> = input frequency in MHz; f<sub>o</sub> = output frequency in MHz
  - C<sub>L</sub> = output load capacitance in pF
  - V<sub>CC</sub> = supply voltage in Volt
  - N = number of inputs switching
  - $\Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of the outputs


### 10.1. Waveforms and test circuit



Measurement points are given in Table 8.

 $V_{\text{OL}}$  and  $V_{\text{OH}}$  are typical output voltage levels that occur with the output load.


Clock (CP) to output (Qn) propagation delays, the clock pulse width, output transition times, and the Fig. 5. maximum frequency



Measurement points are given in Table 8.

 $\ensuremath{V_{\text{OL}}}$  and  $\ensuremath{V_{\text{OH}}}$  are typical output voltage levels that occur with the output load.

Fig. 6. 3-state enable and disable times



Measurement points are given in Table 8.


 $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.


The shaded areas indicate when the input is permitted to change for predicable output performance.

Fig. 7. Data set-up and hold times for the Dn input to the CP input

**Table 8. Measurement points** 

Supply voltage	Input		Output						
V <sub>CC</sub>	V <sub>I</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>				
1.2 V	V <sub>CC</sub>	0.5 x V <sub>CC</sub>	0.5 x V <sub>CC</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V				
1.65 V to 1.95 V	V <sub>CC</sub>	0.5 x V <sub>CC</sub>	0.5 x V <sub>CC</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V				
2.3 V to 2.7 V	V <sub>CC</sub>	0.5 x V <sub>CC</sub>	0.5 x V <sub>CC</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V				
2.7 V	2.7 V	1.5 V	1.5 V	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V				
3.0 V to 3.6 V	2.7 V	1.5 V	1.5 V	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V				





Test data is given in Table 9.

Definitions for test circuit:

 $R_L$  = Load resistance.

 $C_L$  = Load capacitance including jig and probe capacitance.

 $R_T$  = Termination resistance should be equal to output impedance  $Z_0$  of the pulse generator.

 $V_{\text{EXT}}$  = External voltage for measuring switching times.

Test circuit for measuring switching times Fig. 8.


Table 9. Test data

Supply voltage	Input		Load		V <sub>EXT</sub>				
V <sub>CC</sub>	VI	t <sub>r</sub> , t <sub>f</sub>	CL	R <sub>L</sub>	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>PLZ</sub> , t <sub>PZL</sub>	t <sub>PHZ</sub> , t <sub>PZH</sub>		
1.2 V	V <sub>CC</sub>	≤ 2 ns	30 pF	1 kΩ	open	2 x V <sub>CC</sub>	GND		
1.65 V to 1.95 V	V <sub>CC</sub>	≤ 2 ns	30 pF	1 kΩ	open	2 x V <sub>CC</sub>	GND		
2.3 V to 2.7 V	V <sub>CC</sub>	≤ 2 ns	30 pF	500 Ω	open	2 x V <sub>CC</sub>	GND		
2.7 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open	2 x V <sub>CC</sub>	GND		
3.0 V to 3.6 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open	2 x V <sub>CC</sub>	GND		

# 11. Package outline

#### SO20: plastic small outline package; 20 leads; body width 7.5 mm

SOT163-1



UNIT	A max.	A <sub>1</sub>	A <sub>2</sub>	A <sub>3</sub>	bp	С	D <sup>(1)</sup>	E <sup>(1)</sup>	е	HE	L	Lp	Q	v	w	у	z <sup>(1)</sup>	θ
mm	2.65	0.3 0.1	2.45 2.25	0.25	0.49 0.36	0.32 0.23	13.0 12.6	7.6 7.4	1.27	10.65 10.00	1.4	1.1 0.4	1.1 1.0	0.25	0.25	0.1	0.9 0.4	8°
inches	0.1	0.012 0.004	0.096 0.089	0.01	0.019 0.014	0.013 0.009	0.51 0.49	0.30 0.29	0.05	0.419 0.394	0.055	0.043 0.016	0.043 0.039	0.01	0.01	0.004	0.035 0.016	0°


1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE	REFERENCES			EUROPEAN	ISSUE DATE	
VERSION	IEC	JEDEC	JEITA		PROJECTION	1330E DATE
SOT163-1	075E04	MS-013				<del>99-12-27</del> 03-02-19

Package outline SOT163-1 (SO20)

TSSOP20: plastic thin shrink small outline package; 20 leads; body width 4.4 mm

SOT360-1



#### Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE	REFERENCES			EUROPEAN	ISSUE DATE	
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT360-1		MO-153				<del>99-12-27</del> 03-02-19

Fig. 10. Package outline SOT360-1 (TSSOP20)




Fig. 11. Package outline SOT764-1 (DHVQFN20)

### 12. Abbreviations

#### **Table 10. Abbreviations**

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
TTL	Transistor-Transistor Logic

# 13. Revision history

#### **Table 11. Revision history**

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74LVC374A_Q100 v.3	20230901	Product data sheet	-	74LVC374A_Q100 v.2	
Modifications:	<u>Section 2</u> : ESD specification updated according to the latest JEDEC standard.				
74LVC374A_Q100 v.2	20200824	Product data sheet	-	74LVC374A_Q100 v.1	
Modifications:	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>Section 1 and Section 2 updated.</li> <li>Table 4: Derating values for P<sub>tot</sub> total power dissipation have been updated.</li> <li>Package outline drawing of SOT764-1 (Fig. 11) updated.</li> </ul>				
74LVC374A_Q100 v.1	20121122	Product data sheet	-	-	

### 14. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use in automotive applications** — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

### **Contents**

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Functional diagram	2
5. Pinning information	4
5.1. Pinning	4
5.2. Pin description	5
6. Functional description	5
7. Limiting values	5
8. Recommended operating conditions	6
9. Static characteristics	6
10. Dynamic characteristics	7
10.1. Waveforms and test circuit	8
11. Package outline	11
12. Abbreviations	14
13. Revision history	
14. Legal information	

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 1 September 2023

**Product data sheet** 

<sup>©</sup> Nexperia B.V. 2023. All rights reserved