

# Dual supply translating transceiver; auto direction sensing; 3-state

Rev. 6 — 15 November 2023

**Product data sheet** 

# 1. General description

The NXB0102 is a 2-bit, dual supply translating transceiver with auto direction sensing, that enables bidirectional voltage level translation. It features two 2-bit input-output ports (An and Bn), one output enable input (OE) and two supply pins ( $V_{CC(A)}$  and  $V_{CC(B)}$ ).  $V_{CC(A)}$  can be supplied at any voltage between 1.2 V and 3.6 V and  $V_{CC(B)}$  can be supplied at any voltage between 1.65 V and 5.5 V, making the device suitable for translating between any of the low voltage nodes (1.2 V, 1.5 V, 1.8 V, 2.5 V, 3.3 V and 5.0 V). Pins An and OE are referenced to  $V_{CC(A)}$  and pins Bn are referenced to  $V_{CC(B)}$ . A LOW level at pin OE causes the outputs to assume a high-impedance OFF-state. This device is fully specified for partial power-down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

### 2. Features and benefits

- Wide supply voltage range:
  - V<sub>CC(A)</sub>: 1.2 V to 3.6 V and V<sub>CC(B)</sub>: 1.65 V to 5.5 V
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- Inputs accept voltages up to 5.5 V
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2500 V for A port
  - HBM: ANSI/ESDA/JEDEC JS-001 class 3B exceeds 15000 V for B port
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1500 V
- Latch-up performance exceeds 100 mA per JESD 78B Class II
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

# 3. Ordering information

**Table 1. Ordering information** 

Type number	Package								
	Temperature range	Name	Description	Version					
NXB0102DC	-40 °C to +125 °C	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	SOT765-1					
NXB0102GT	-40 °C to +125 °C	XSON8	plastic extremely thin small outline package; no leads; 8 terminals; body 1 × 1.95 × 0.5 mm	SOT833-1					
NXB0102UN	-40 °C to +125 °C	WLCSP8	wafer level chip-scale package; 8 bumps; 0.75 × 1.55 × 0.60 mm	SOT8023-1					



### Dual supply translating transceiver; auto direction sensing; 3-state


# 4. Marking

Table 2. Marking

Type number	Marking code[1]
NXB0102DC	n2
NXB0102GT	n2
NXB0102UN	n2

<sup>[1]</sup> The pin 1 indicator is located on the lower left corner of the device, below the marking code.


# 5. Functional diagram



Dual supply translating transceiver; auto direction sensing; 3-state

# 6. Pinning information

### 6.1. Pinning



# 6.2. Pin description

Table 3. Pin description

Symbol	Pin	Bump	Description
B2, B1	1, 8	A1, A2	data input or output (referenced to V <sub>CC(B)</sub> )
GND	2	B1	ground (0 V)
V <sub>CC(A)</sub>	3	C1	supply voltage A
A2, A1	4, 5	D1, D2	data input or output (referenced to V <sub>CC(A)</sub> )
OE	6	C2	output enable input (active HIGH; referenced to V <sub>CC(A)</sub> )
V <sub>CC(B)</sub>	7	B2	supply voltage B

#### Dual supply translating transceiver; auto direction sensing; 3-state

# 7. Functional description

#### **Table 4. Function table**

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

Supply voltage		Input	Input/output		
V <sub>CC(A)</sub> [1] V <sub>CC(B)</sub>		OE	An	Bn	
1.2 V to 3.6 V	1.65 V to 5.5 V	L	Z	Z	
1.2 V to 3.6 V	1.65 V to 5.5 V	Н	input or output	output or input	
GND	1.65 V to 5.5 V	X	Z	Z	
1.2 V to 3.6 V	GND	Х	Z	Z	

<sup>[1]</sup>  $V_{CC(A)}$  must be less than or equal to  $V_{CC(B)}$ .

# 8. Limiting values

#### Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC(A)</sub>	supply voltage A			-0.5	+6.5	V
$V_{CC(B)}$	supply voltage B			-0.5	+6.5	V
VI	input voltage	OE	[1]	-0.5	+6.5	V
		Power-down or 3-state mode				
		An, Bn	[1]	-0.5	+6.5	V
		Active mode				
		An, Bn	[1] [2] [3]	-0.5	V <sub>CCI</sub> + 0.5	V
Vo	output voltage	Power-down or 3-state mode				
		An, Bn	[1]	-0.5	+6.5	V
		Active mode				
		An, Bn	[1] [3] [4]	-0.5	V <sub>CCO</sub> + 0.5	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V		-50	-	mA
I <sub>OK</sub>	output clamping current	V <sub>O</sub> < 0 V		-50	-	mA
Io	output current	V <sub>O</sub> = 0 V to V <sub>CCO</sub>	[4]	-	±50	mA
I <sub>CC</sub>	supply current	I <sub>CC(A)</sub> or I <sub>CC(B)</sub>		-	100	mA
$I_{GND}$	ground current			-100	-	mΑ
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb}$ = -40 °C to +125 °C	[5]	-	250	mW

The minimum input and minimum output voltage ratings may be exceeded if the input and output current ratings are observed.

For SOT833-1 (XSON8) package: Ptot derates linearly with 3.1 mW/K above 68 °C.

For SOT8023-1 (WLCSP8) package: Ptot derates linearly with 7.2 mW/K above 115 °C.

 $V_{\text{CCI}}$  is the supply voltage associated with the input.

 $V_{\rm CCI}$  + 0.5 V or  $V_{\rm CCO)}$  + 0.5 V should not exceed 6.5 V.  $V_{\rm CCO}$  is the supply voltage associated with the output. [3]

For SOT765-1 (VSSOP8) package: Ptot derates linearly with 4.9 mW/K above 99 °C.

**Nexperia** 

Dual supply translating transceiver; auto direction sensing; 3-state

# 9. Recommended operating conditions

Table 6. Recommended operating conditions [1] [2]

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC(A)</sub>	supply voltage A		1.2	3.6	V
V <sub>CC(B)</sub>	supply voltage B		1.65	5.5	V
VI	input voltage	OE	0	5.5	V
		Power-down or 3-state mode			
		An	0	3.6	V
		Bn	0	5.5	V
		Active mode			
		An, Bn [3]	0	V <sub>CCI</sub>	V
Vo	output voltage	Power-down or 3-state mode			
		An	0	3.6	V
		Bn	0	5.5	V
		Active mode			
		An, Bn [4]	0	V <sub>cco</sub>	V
T <sub>amb</sub>	ambient temperature		-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC(A)</sub> = 1.2 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	40	ns/V

- The A and B sides of an unused I/O pair must be held in the same state, both at V<sub>CCI</sub> or both at GND.
- [2]
- $V_{CC(A)}$  must be less than or equal to  $V_{CC(B)}.$   $V_{CCI}$  is the supply voltage associated with the input.
- V<sub>CCO</sub> is the supply voltage associated with the output.

# 10. Static characteristics

#### **Table 7. Typical static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V);  $V_{CC(A)}$  must be less than or equal to  $V_{CC(B)}$ ;  $T_{amb}$  = 25 °C.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>OH</sub>	HIGH-level output voltage	A port; $V_{CC(A)} = 1.2 \text{ V}$ ; $I_O = -20 \mu\text{A}$	-	1.1	-	V
V <sub>OL</sub>	LOW-level output voltage	A port; $V_{CC(A)} = 1.2 \text{ V}$ ; $I_0 = 20 \mu\text{A}$	-	0.09	-	V
l <sub>l</sub>	input leakage current	OE input; $V_I$ = 0 V to 3.6 V; $V_{CC(A)}$ = 1.2 V to 3.6 V; $V_{CC(B)}$ = 1.65 V to 5.5 V	-	-	±1	μΑ
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_O = 0 \text{ V to } V_{CCO}$ ; $V_{CC(A)} = 1.2 \text{ V to } 3.6 \text{ V}$ ; [1] $V_{CC(B)} = 1.65 \text{ V to } 5.5 \text{ V}$	-	-	±1	μΑ
l <sub>OFF</sub>	power-off leakage current	A port; $V_1$ or $V_0 = 0$ V to 3.6 V; $V_{CC(A)} = 0$ V; $V_{CC(B)} = 0$ V to 5.5 V	-	-	±1	μΑ
		B port; $V_1$ or $V_0 = 0$ V to 5.5 V; $V_{CC(B)} = 0$ V; $V_{CC(A)} = 0$ V to 3.6 V	-	-	±1	μΑ
Cı	input capacitance	OE input; $V_{CC(A)} = 1.2 \text{ V to } 3.6 \text{ V}; V_{CC(B)} = 1.65 \text{ V to } 5.5 \text{ V}$	-	2.0	-	pF
C <sub>I/O</sub>	input/output	A port; $V_{CC(A)} = 1.2 \text{ V to } 3.6 \text{ V}; V_{CC(B)} = 1.65 \text{ V to } 5.5 \text{ V}$	-	4.0	-	pF
capacitance		B port; V <sub>CC(A)</sub> = 1.2 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	7.5	-	pF

<sup>[1]</sup>  $V_{CCO}$  is the supply voltage associated with the output.

### Dual supply translating transceiver; auto direction sensing; 3-state

Table 8. Typical supply current

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); T<sub>amb</sub> = 25 °C.

V <sub>CC(A)</sub>	V <sub>CC(B)</sub>								
	1.8	3 V	2.5	5 V		3.3 V		5.0 V	
	I <sub>CC(A)</sub>	I <sub>CC(B)</sub>							
1.2 V	10	10	10	10	10	20	10	1050	nA
1.5 V	10	10	10	10	10	10	10	650	nA
1.8 V	10	10	10	10	10	10	10	350	nA
2.5 V	-	-	10	10	10	10	10	40	nA
3.3 V	-	-	-	-	10	10	10	10	nA

#### **Table 9. Static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).[1]

Symbol	Parameter	Conditions		-40 °C to	+85 °C	-40 °C to	+125 °C	Unit
				Min	Max	Min	Max	
V <sub>IH</sub>	HIGH-level	A or B port and OE input	[2]					
	input voltage	V <sub>CC(A)</sub> = 1.2 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V		0.65V <sub>CCI</sub>	-	0.65V <sub>CCI</sub>	-	V
$V_{IL}$	LOW-level	A or B port and OE input	[2]					
input voltage		V <sub>CC(A)</sub> = 1.2 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V		-	0.35V <sub>CCI</sub>	-	0.35V <sub>CCI</sub>	V
	HIGH-level	A or B port; I <sub>O</sub> = -20 μA	[3]					
	output voltage	A port; V <sub>CC(A)</sub> = 1.4 V to 3.6 V		V <sub>CCO</sub> - 0.4	-	V <sub>CCO</sub> - 0.4	-	V
		B port; V <sub>CC(B)</sub> = 1.65 V to 5.5 V		V <sub>CCO</sub> - 0.4	-	V <sub>CCO</sub> - 0.4	-	V
V <sub>OL</sub>	LOW-level output voltage	A or B port; I <sub>O</sub> = 20 μA	[3]					
		A port; V <sub>CC(A)</sub> = 1.4 V to 3.6 V		-	0.4	-	0.4	V
		B port; V <sub>CC(B)</sub> = 1.65 V to 5.5 V		-	0.4	-	0.4	V
I	input leakage current	OE input; $V_I = 0 \text{ V to } 3.6 \text{ V};$ $V_{CC(A)} = 1.2 \text{ V to } 3.6 \text{ V};$ $V_{CC(B)} = 1.65 \text{ V to } 5.5 \text{ V}$		-	±2	-	±5	μΑ
I <sub>OZ</sub>	OFF-state output current	A or B port; $V_O = 0 \text{ V or } V_{CCO}$ ; $V_{CC(A)} = 1.2 \text{ V to } 3.6 \text{ V}$ ; $V_{CC(B)} = 1.65 \text{ V to } 5.5 \text{ V}$	[3]	-	±2	-	±10	μA
I <sub>OFF</sub>	power-off leakage	A port; $V_1$ or $V_0 = 0$ V to 3.6 V; $V_{CC(A)} = 0$ V; $V_{CC(B)} = 0$ V to 5.5 V		-	±2	-	±10	μΑ
	current	B port; $V_1$ or $V_0 = 0$ V to 5.5 V; $V_{CC(B)} = 0$ V; $V_{CC(A)} = 0$ V to 3.6 V		-	±2	-	±10	μΑ

### Dual supply translating transceiver; auto direction sensing; 3-state

Symbol	Parameter	Conditions	-40 °C t	o +85 °C	-40 °C to	+125 °C	Unit
			Min	Max	Min	Max	
I <sub>CC</sub>	supply current	$V_I = 0 \text{ V or } V_{CCI}; I_O = 0 \text{ A}$ [2]					
		I <sub>CC(A)</sub>					
		OE = LOW; V <sub>CC(A)</sub> = 1.4 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	3	-	15	μА
		OE = HIGH; V <sub>CC(A)</sub> = 1.4 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	3	-	20	μА
		V <sub>CC(A)</sub> = 3.6 V; V <sub>CC(B)</sub> = 0 V	-	2	-	15	μA
		$V_{CC(A)} = 0 \text{ V}; V_{CC(B)} = 5.5 \text{ V}$	-	-2	-	-15	μΑ
		I <sub>CC(B)</sub>					
		OE = LOW; V <sub>CC(A)</sub> = 1.4 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	3	-	15	μA
		OE = HIGH; V <sub>CC(A)</sub> = 1.4 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	3	-	20	μА
		V <sub>CC(A)</sub> = 3.6 V; V <sub>CC(B)</sub> = 0 V	-	-2	-	-15	μΑ
		$V_{CC(A)} = 0 \text{ V}; V_{CC(B)} = 5.5 \text{ V}$	-	2	-	15	μA
		$I_{CC(A)} + I_{CC(B)}$					
		V <sub>CC(A)</sub> = 1.4 V to 3.6 V; V <sub>CC(B)</sub> = 1.65 V to 5.5 V	-	8	-	40	μΑ

<sup>[1]</sup> [2]

 $V_{\text{CC}(A)}$  must be less than or equal to  $V_{\text{CC}(B)}$ .  $V_{\text{CCI}}$  is the supply voltage associated with the input.  $V_{\text{CCO}}$  is the supply voltage associated with the output. [3]

**Nexperia** 

#### Dual supply translating transceiver; auto direction sensing; 3-state

# 11. Dynamic characteristics

Table 10. Typical dynamic characteristics for temperature 25 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 5; for waveforms see Fig. 2, Fig. 3 and Fig. 4.

_	Parameter	Conditions			Vc	C(B)		Unit
[1]			1.8 V	2.5 V	3.3 V	5.0 V		
V <sub>CC(A)</sub> =	1.2 V; T <sub>amb</sub> = 25 °C		'					
t <sub>pd</sub>	propagation delay	A to B		7.5	6.0	5.5	5.2	ns
		B to A		6.6	5.6	5.1	4.9	ns
t <sub>en</sub>	enable time	OE to A, B		0.5	0.5	0.5	0.5	μs
t <sub>dis</sub>	disable time	OE to A; no external load	[2]	8.3	8.3	8.3	8.3	ns
		OE to B; no external load	[2]	10.4	9.4	9.3	8.8	ns
		OE to A		81	69	83	68	ns
		OE to B		81	69	83	68	ns
t <sub>t</sub>	transition time	A port		4.3	4.3	4.3	4.4	ns
		B port		2.7	2.1	1.8	1.5	ns
t <sub>sk(o)</sub>	output skew time	between channels	[3]	0.2	0.2	0.2	0.2	ns
t <sub>W</sub>	pulse width	data inputs		15	13	13	13	ns
f <sub>data</sub>	data rate			70	80	80	80	Mbps

 $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{t}$  is the same as  $t_{THL}$  and  $t_{TLH}$  Delay between OE going LOW and when the outputs are actually disabled.

Table 11. Dynamic characteristics for temperature range -40 °C to +85 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 5; for waveforms see Fig. 2, Fig. 3 and Fig. 4.

•	Parameter	Conditions				Vcc	(B)				Unit
[1]			1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		5.0 V ± 0.5 V		
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.5 V ± 0.1 V			•							
t <sub>pd</sub>	propagation delay	A to B	1.4	12.9	1.2	10.1	1.1	10.0	0.8	9.9	ns
		B to A	0.9	14.2	0.7	12.0	0.4	11.7	0.3	13.7	ns
t <sub>en</sub>	enable time	OE to A, B	-	1.0	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	1.0	17.9	1.0	17.9	1.0	17.9	1.0	17.9	ns
		OE to B; no external load [2]	1.0	21.0	1.0	16.6	1.0	15.1	1.0	14.4	ns
		OE to A	-	100	-	100	-	100	-	100	ns
		OE to B	-	150	-	105	-	150	-	105	ns
t <sub>t</sub>	transition time	A port	0.9	5.1	0.9	5.1	0.9	5.1	0.9	5.1	ns
		B port	0.9	4.7	0.6	3.2	0.5	2.5	0.4	2.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	0.5	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	25	-	25	-	25	-	25	-	ns
f <sub>data</sub>	data rate		-	40	-	40	-	40	-	40	Mbps

Skew between any two outputs of the same package switching in the same direction.

# Dual supply translating transceiver; auto direction sensing; 3-state

	Parameter	Conditions				Vcc	(B)				Unit
[1]			1.8 V ±	0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V	± 0.5 V	
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.8 V ± 0.15 V										
t <sub>pd</sub>	propagation	A to B	1.6	11.0	1.4	7.7	1.3	6.8	1.2	6.5	ns
	delay	B to A	1.5	12.0	1.3	8.4	1.0	7.6	0.9	7.1	ns
t <sub>en</sub>	enable time	OE to A, B	-	1.0	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	1.0	14.7	1.0	14.7	1.0	14.7	1.0	14.7	ns
		OE to B; no external load [2]	1.0	18.2	1.0	14.5	1.0	13.7	1.0	12.7	ns
		OE to A	-	120	-	120	-	120	-	120	ns
		OE to B	-	150	-	105	-	150	-	105	ns
t <sub>t</sub>	transition time	A port	0.8	4.1	0.8	4.1	0.8	4.1	0.8	4.1	ns
		B port	0.9	4.7	0.6	3.2	0.5	2.5	0.4	2.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	0.5	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	20	-	17	-	17	-	17	-	ns
f <sub>data</sub>	data rate		-	49	-	60	-	60	-	60	Mbps
V <sub>CC(A)</sub> =	2.5 V ± 0.2 V		'							,	'
t <sub>pd</sub>	propagation	A to B	-	-	1.1	6.3	1.0	5.2	0.9	4.7	ns
	delay	B to A	-	-	1.2	6.6	1.1	5.1	0.9	4.4	ns
t <sub>en</sub>	enable time	OE to A, B	-	-	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	-	-	1.0	9.7	1.0	9.7	1.0	9.7	ns
		OE to B; no external load [2]	-	-	1.0	12.9	1.0	12.0	1.0	11.0	ns
		OE to A	-	-	-	85	-	85	-	85	ns
		OE to B	-	-	-	105	-	150	-	100	ns
t <sub>t</sub>	transition time	A port	-	-	0.7	3.0	0.7	3.0	0.7	3.0	ns
		B port	-	-	0.7	3.2	0.5	2.5	0.4	2.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	-	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	-	-	12	-	10	-	10	-	ns
f <sub>data</sub>	data rate		-	-	-	85	-	100	-	100	Mbps

### Dual supply translating transceiver; auto direction sensing; 3-state

Symbol	Parameter	Conditions				Vcc	(B)				Unit
[1]			1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		5.0 V ± 0.5 V		
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	3.3 V ± 0.3 V					•	•			•	
t <sub>pd</sub>	propagation	A to B	-	-	-	-	0.9	4.7	8.0	4.0	ns
	delay	B to A	-	-	-	-	1.0	4.9	0.9	3.8	ns
t <sub>en</sub>	enable time	OE to A, B	-	-	-	-	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2	-	-	-	-	1.0	9.4	1.0	9.4	ns
		OE to B; no external load [2	-	-	-	-	1.0	11.3	1.0	10.4	ns
		OE to A	-	-	-	-	-	125	-	125	ns
		OE to B	-	-	-	-	-	150	-	100	ns
t <sub>t</sub>	transition time	A port	-	-	-	-	0.7	2.5	0.7	2.5	ns
		B port	-	-	-	-	0.5	2.5	0.4	2.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3	-	-	-	-	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	-	-	-	-	10	-	10	-	ns
f <sub>data</sub>	data rate		-	-	-	-	-	100	-	100	Mbps

 $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{t}$  is the same as  $t_{THL}$  and  $t_{TLH}$  Delay between OE going LOW and when the outputs are actually disabled.

Table 12. Dynamic characteristics for temperature range -40 °C to +125 °C

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 5; for waveforms see Fig. 2, Fig. 3 and Fig. 4.

Symbol	Parameter	Conditions	V <sub>CC(B)</sub>								
[1]			1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		5.0 V ± 0.5 V		
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.5 V ± 0.1 V										
t <sub>pd</sub>	propagation	A to B	1.4	15.9	1.2	13.1	1.1	13.0	0.8	12.9	ns
	delay	B to A	0.9	17.2	0.7	15.0	0.4	14.7	0.3	16.7	ns
t <sub>en</sub>	enable time	OE to A, B	-	1.0	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	1.0	18.3	1.0	18.3	1.0	18.3	1.0	18.3	ns
		OE to B; no external load [2]	1.0	21.8	1.0	17.7	1.0	16.1	1.0	15.2	ns
		OE to A	-	105	-	105	-	105	-	105	ns
		OE to B	-	155	-	110	-	155	-	105	ns
t <sub>t</sub>	transition time	A port	0.9	7.1	0.9	7.1	0.9	7.1	0.9	7.1	ns
		B port	0.9	6.5	0.6	5.2	0.5	4.8	0.4	4.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	0.5	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	25	-	25	-	25	-	25	-	ns
f <sub>data</sub>	data rate		-	40	-	40	-	40	-	40	Mbps

Skew between any two outputs of the same package switching in the same direction.

# Dual supply translating transceiver; auto direction sensing; 3-state

	Parameter	Conditions				Vcc	(B)				Unit
[1]			1.8 V ±	0.15 V	2.5 V :	± 0.2 V	3.3 V :	± 0.3 V	5.0 V	± 0.5 V	
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	1.8 V ± 0.15 V					•			•		
t <sub>pd</sub>	propagation	A to B	1.6	14.0	1.4	10.7	1.3	9.8	1.2	9.5	ns
delay		B to A	1.5	15.0	1.3	11.4	1.0	10.6	0.9	10.1	ns
t <sub>en</sub>	enable time	OE to A, B	-	1.0	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	1.0	15.0	1.0	15.0	1.0	15.0	1.0	15.0	ns
		OE to B; no external load [2]	1.0	19.8	1.0	15.3	1.0	14.5	1.0	13.5	ns
		OE to A	-	125	-	125	-	125	-	125	ns
		OE to B	-	150	-	105	-	150	-	105	ns
t <sub>t</sub>	transition time	A port	0.8	6.2	0.8	6.1	0.8	6.1	0.8	6.1	ns
		B port	0.9	5.8	0.6	5.2	0.5	4.8	0.4	4.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	0.5	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	22	-	19	-	19	-	19	-	ns
f <sub>data</sub>	data rate		-	45	-	55	-	55	-	55	Mbps
V <sub>CC(A)</sub> =	2.5 V ± 0.2 V		'					<b>'</b>		'	'
t <sub>pd</sub>	propagation	A to B	-	-	1.1	9.3	1.0	8.2	0.9	7.7	ns
	delay	B to A	-	-	1.2	9.6	1.1	8.1	0.9	7.4	ns
t <sub>en</sub>	enable time	OE to A, B	-	-	-	1.0	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2]	-	-	1.0	10.1	1.0	10.1	1.0	10.1	ns
		OE to B; no external load [2]	-	-	1.0	13.5	1.0	12.7	1.0	11.7	ns
		OE to A	-	-	-	85	-	85	-	85	ns
		OE to B	-	-	-	105	-	150	-	100	ns
t <sub>t</sub>	transition time	A port	-	-	0.7	5.0	0.7	5.0	0.7	5.0	ns
		B port	-	-	0.7	4.6	0.5	4.8	0.4	4.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3]	-	-	-	0.5	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	-	-	14	-	13	-	10	-	ns
f <sub>data</sub>	data rate		-	-	-	75	-	80	-	100	Mbps

**Nexperia** 

#### Dual supply translating transceiver; auto direction sensing; 3-state

Symbol	Parameter	Conditions				Vcc	(B)				Unit
[1]			1.8 V ± 0.15 V		2.5 V ± 0.2 V		3.3 V ± 0.3 V		5.0 V ± 0.5 V		
			Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>CC(A)</sub> =	3.3 V ± 0.3 V					•					
t <sub>pd</sub>	propagation	A to B	-	-	-	-	0.9	7.7	0.8	7.0	ns
	delay	B to A	-	-	-	-	1.0	7.9	0.9	6.8	ns
t <sub>en</sub>	enable time	OE to A, B	-	-	-	-	-	1.0	-	1.0	μs
t <sub>dis</sub>	disable time	OE to A; no external load [2	] -	-	-	-	1.0	9.9	1.0	9.9	ns
		OE to B; no external load [2	] -	-	-	-	1.0	12.1	1.0	10.9	ns
		OE to A	-	-	-	-	-	125	-	125	ns
		OE to B	-	-	-	-	-	150	-	100	ns
t <sub>t</sub>	transition time	A port	-	-	-	-	0.7	4.5	0.7	4.5	ns
		B port	-	-	-	-	0.5	4.1	0.4	4.7	ns
t <sub>sk(o)</sub>	output skew time	between channels [3	-	-	-	-	-	0.5	-	0.5	ns
t <sub>W</sub>	pulse width	data inputs	-	-	-	-	10	-	10	-	ns
f <sub>data</sub>	data rate		-	-	-	-	-	100	-	100	Mbps

- $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{t}$  is the same as  $t_{THL}$  and  $t_{TLH}$  Delay between OE going LOW and when the outputs are actually disabled.
- [3] Skew between any two outputs of the same package switching in the same direction.

#### Table 13. Typical power dissipation capacitance

Voltages are referenced to GND (ground = 0 V). [1] [2]

Symbol	Parameter	Conditions				V <sub>CC(A)</sub>				Unit	
			1.2 V	1.2 V	1.5 V	1.8 V	2.5 V	2.5 V	3.3 V		
						V <sub>CC(B)</sub>					
			1.8 V	5.0 V	1.8 V	1.8 V	2.5 V	5.0 V	3.3 V to 5.0 V		
$T_{amb} = 2$	5 °C										
C <sub>PD</sub>	power	outputs enabled; OE = $V_{CC(A)}$									
	dissipation capacitance	A port: (direction A to B)	6	5	6	6	6	5	5	pF	
		A port: (direction B to A)	8	8	8	8	8	8	8	pF	
		B port: (direction A to B)	26	30	26	26	27	30	30	pF	
		B port: (direction B to A)	23	28	22	22	22	26	26	pF	
		outputs disabled; OE = GND									
		A port: (direction A to B)	0.05	0.05	0.05	0.09	0.08	0.08	0.06	pF	
		A port: (direction B to A)	0.00	0.00	0.00	0.00	0.00	0.00	0.00	pF	
		B port: (direction A to B)	0.00	0.02	0.00	0.00	0.00	0.00	0.00	pF	
		B port: (direction B to A)	0.06	0.09	0.06	0.06	0.06	0.07	0.07	pF	

<sup>[1]</sup>  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu W$ ).


 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma (C_L \times V_{CC}^2 \times f_o)$  where:


 $f_i$  = input frequency in MHz;  $f_o$  = output frequency in MHz;  $C_L$  = load capacitance in pF;

 $V_{CC}$  = supply voltage in V; N = number of inputs switching;  $\Sigma(C_L \times V_{CC}^2 \times f_o)$  = sum of the outputs. [2]  $f_i$  = 10 MHz;  $V_i$  = GND to  $V_{CC}$ ;  $t_r$  =  $t_f$  = 1 ns;  $C_L$  = 0 pF;  $R_L$  =  $\infty$   $\Omega$ .


#### Dual supply translating transceiver; auto direction sensing; 3-state

#### 11.1. Waveforms and test circuit





#### Dual supply translating transceiver; auto direction sensing; 3-state



(1) The enable time  $(t_{en})$  indicates the amount of time the user must allow for one one-shot circuitry to become operational after OE is taken HIGH. See also Section 12.6

Measurement points are given in <u>Table 14</u>.

V<sub>OL</sub> is a typical output voltage level that occur with the output load.

 $\ensuremath{V_{\text{CCO}}}$  is the supply voltage associated with the output.


Fig. 4. Enable times


Table 14. Measurement points [1]

Supply voltage	Input	Output		
V <sub>cco</sub>	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>
1.2 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.1 V	V <sub>OH</sub> - 0.1 V
1.5 V ± 0.1 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.1 V	V <sub>OH</sub> - 0.1 V
1.8 V ± 0.15 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
2.5 V ± 0.2 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
3.3 V ± 0.3 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V
5.0 V ± 0.5 V	0.5V <sub>CCI</sub>	0.5V <sub>CCO</sub>	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V

[1]  $V_{CCI}$  is the supply voltage associated with the input and  $V_{CCO}$  is the supply voltage associated with the output.

#### Dual supply translating transceiver; auto direction sensing; 3-state





Test data is given in Table 15.

All input pulses are supplied by generators having the following characteristics:

PRR  $\leq$  10 MHz;  $Z_O = 50 \Omega$ ;  $dV/dt \geq 1.0 V/ns$ ;

R<sub>L</sub> = Load resistance;

C<sub>L</sub> = Load capacitance including jig and probe capacitance;

V<sub>EXT</sub> = External voltage for measuring switching times.

Fig. 5. Test circuit for measuring switching times

Table 15. Test data

Supply voltage	Input		Load		V <sub>EXT</sub>				
V <sub>CC(A)</sub>	V <sub>CC(B)</sub>	V <sub>I</sub> [1]	Δt/ΔV	CL	R <sub>L</sub> [2]	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>en</sub>	t <sub>PHZ</sub>	t <sub>PLZ</sub> [3]
1.2 V to 3.6 V	1.65 V to 5.5 V	$V_{CCI}$	≤ 1.0 ns/V	15 pF	50 kΩ, 1 MΩ	open	open	open	2V <sub>CCO</sub>


- 1] V<sub>CCI</sub> is the supply voltage associated with the input.
- [2] For measuring data rate, pulse width, propagation delay, output rise and fall time and enable time,  $R_L = 1 \text{ M}\Omega$ . For measuring disable time,  $R_L = 50 \text{ k}\Omega$ .
- [3] V<sub>CCO</sub> is the supply voltage associated with the output.

Dual supply translating transceiver; auto direction sensing; 3-state

# 12. Application information

### 12.1. Applications


Voltage level-translation applications. The NXB0102 can be used to interface between devices or systems operating at different supply voltages. See <u>Fig. 6</u> for a typical operating circuit using the NXB0102.



#### 12.2. Architecture


The architecture of the NXB0102 is shown in Fig. 7. The device does not require an extra input signal to control the direction of data flow from A to B or from B to A. In a static state, the output drivers of the NXB0102 can maintain a defined output level, but the output architecture is designed to be weak, so that they can be overdriven by an external driver when data on the bus starts flowing in the opposite direction. The output one shots detect rising or falling edges on the A or B ports. During a rising edge, the one shots turn on the PMOS transistors (T1, T3) for a short duration, accelerating the low-to-high transition. Similarly, during a falling edge, the one shots turn on the NMOS transistors (T2, T4) for a short duration, accelerating the high-to-low transition. During output transitions the typical output impedance is 70  $\Omega$  at  $V_{\rm CCO}$  = 1.2 V to 1.8 V, 50  $\Omega$  at  $V_{\rm CCO}$  = 1.8 V to 3.3 V and 40  $\Omega$  at  $V_{\rm CCO}$  = 3.3 V to 5.0 V.

#### Dual supply translating transceiver; auto direction sensing; 3-state



### 12.3. Input driver requirements

For correct operation, the device driving the data I/Os of the NXB0102 must have a minimum drive capability of ±2 mA. See Fig. 8 for a plot of typical input current versus input voltage.



#### 12.4. Output load considerations

The maximum lumped capacitive load that can be driven is dependant upon the one-shot pulse duration. In cases with very heavy capacitive loading there is a risk that the output will not reach the positive rail within the one-shot pulse duration. To avoid excessive capacitive loading and to ensure correct triggering of the one-shot it's recommended to use short trace lengths and low capacitance connectors on NXB0102 PCB layouts. To ensure low impedance termination and avoid output signal oscillations and one-shot re-triggering, the length of the PCB trace should be such that the round trip delay of any reflection is within the one-shot pulse duration.

#### Dual supply translating transceiver; auto direction sensing; 3-state

### 12.5. Power up

During operation  $V_{CC(A)}$  must never be higher than  $V_{CC(B)}$ , however during power-up  $V_{CC(A)} \ge V_{CC(B)}$  does not damage the device, so either power supply can be ramped up first. There is no special power-up sequencing required. The NXB0102 includes circuitry that disables all output ports when either  $V_{CC(A)}$  or  $V_{CC(B)}$  is switched off.

#### 12.6. Enable and disable

An output enable input (OE) is used to disable the device. Setting OE = LOW causes all I/Os to assume the high-impedance OFF-state. The disable time ( $t_{\rm dis}$  with no external load) indicates the delay between when OE goes LOW and when outputs actually become disabled. The enable time ( $t_{\rm en}$ ) indicates the amount of time the user must allow for one one-shot circuitry to become operational after OE is taken HIGH. To ensure the high-impedance OFF-state during power-up or power-down, pin OE should be tied to GND through a pull-down resistor, the minimum value of the resistor is determined by the current-sourcing capability of the driver.

### 12.7. Pull-up or pull-down resistors on I/O lines

As mentioned previously the NXB0102 is designed with low static drive strength to drive capacitive loads of up to 70 pF. To avoid output contention issues, any pull-up or pull-down resistors used must be kept higher than 50 k $\Omega$ . For this reason the NXB0102 is not recommended for use in open drain driver applications such as 1-Wire or I $^2$ C. For these applications, the NXS0102 level translator is recommended.

Dual supply translating transceiver; auto direction sensing; 3-state

# 13. Package outline




Fig. 9. Package outline SOT765-1 (VSSOP8)

#### Dual supply translating transceiver; auto direction sensing; 3-state




Fig. 10. Package outline SOT833-1 (XSON8)

#### Dual supply translating transceiver; auto direction sensing; 3-state




Fig. 11. Package outline SOT8023-1 (WLCSP8)

### Dual supply translating transceiver; auto direction sensing; 3-state

# 14. Abbreviations

#### **Table 16. Abbreviations**

Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
ESD	Electro Static Discharge
НВМ	Human Body Model
NMOS	N-channel Metal-Oxide Semiconductor
PCB	Printed Circuit Board
PMOS	P-channel Metal-Oxide Semiconductor
PRR	Pulse Rate Repetition

# 15. Revision history

### Table 17. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes				
NXB0102 v.6	20231115	Product data sheet	-	NXB0102 v.5				
Modifications:	Section 2: E	SD specification updated	according to the la	atest JEDEC standard.				
NXB0102 v.5	20210906	Product data sheet	-	NXB0102 v.4				
Modifications:	Product star supply.	tus of type number NXB01	02GT (SOT833-1/	(XSON8) is set to released for				
NXB0102 v.4	20210630	Product data sheet	-	NXB0102 v.3				
Modifications:	Type number	er NXB0102UN (SOT8023-	-1 / WLCSP8) add	led.				
NXB0102 v.3	20201113	Product data sheet	-	NXB0102 v.2				
Modifications:		: Added description for pin d <u>Table 12</u> : Disable times u	` '					
NXB0102 v.2	20200923	Product data sheet	-	NXB0102 v.1				
Modifications:	• <u>Table 7</u> : Ch	<ul> <li>Type number NXB0102GT (SOT833-1/XSON8) added.</li> <li>Table 7: Changed C<sub>1</sub> input capacitance to 2.0 pF.</li> <li>Corrected typo in Section 12.4 (Errata)</li> </ul>						
NXB0102 v.1	20191217	Product data sheet	-	-				

#### Dual supply translating transceiver; auto direction sensing; 3-state

# 16. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXB0102

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2023. All rights reserved

### Dual supply translating transceiver; auto direction sensing; 3-state

# **Contents**

1. General description	1
2. Features and benefits	1
3. Ordering information	1
4. Marking	2
5. Functional diagram	2
6. Pinning information	3
6.1. Pinning	3
6.2. Pin description	3
7. Functional description	4
8. Limiting values	4
9. Recommended operating conditions	5
10. Static characteristics	5
11. Dynamic characteristics	8
11.1. Waveforms and test circuit	13
12. Application information	16
12.1. Applications	16
12.2. Architecture	16
12.3. Input driver requirements	17
12.4. Output load considerations	17
12.5. Power up	18
12.6. Enable and disable	18
12.7. Pull-up or pull-down resistors on I/O lines	18
13. Package outline	19
14. Abbreviations	22
15. Revision history	22
16. Legal information	23

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 15 November 2023

<sup>©</sup> Nexperia B.V. 2023. All rights reserved