# **HEF4052B**

# **Dual 4-channel analog multiplexer/demultiplexer**

Rev. 11 — 15 December 2021

Product data sheet

### 1. General description

The HEF4052B is a dual single-pole quad-throw analog switch (2x SP4T) suitable for use in analog or digital 4:1 multiplexer/demultiplexer applications. Each switch features four independent inputs/outputs (nY0, nY1, nY2 and nY3) and a common input/output (nZ). A digital enable input ( $\overline{\mathbb{E}}$ ) and two digital select inputs (S1 and S2) are common to both switches. When  $\overline{\mathbb{E}}$  is HIGH, the switches are turned off. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of  $V_{DD}$ .

### 2. Features and benefits

- Wide supply voltage range from 3.0 V to 15.0 V
- CMOS low power dissipation
- · High noise immunity
- · Fully static operation
- 5 V, 10 V, and 15 V parametric ratings
- Standardized symmetrical output characteristics
- Complies with JEDEC standard JESD 13-B
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-B exceeds 200 V
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

### 3. Applications

- Analog multiplexing and demultiplexing
- Digital multiplexing and demultiplexing
- Signal gating

# 4. Ordering information


#### **Table 1. Ordering information**


Type number	Package			
	Temperature range	Name	Description	Version
HEF4052BT	-40 °C to +125 °C	SO16	plastic small outline package; 16 leads; body width 3.9 mm	SOT109-1
HEF4052BTT	-40 °C to +125 °C	TSSOP16	plastic thin shrink small outline package; 16 leads; body width 4.4 mm	SOT403-1




#### Dual 4-channel analog multiplexer/demultiplexer

# 5. Functional diagram






### **Dual 4-channel analog multiplexer/demultiplexer**




#### Dual 4-channel analog multiplexer/demultiplexer



#### **Dual 4-channel analog multiplexer/demultiplexer**

# 6. Pinning information

#### 6.1. Pinning



### 6.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
E	6	enable input (active LOW)
V <sub>EE</sub>	7	supply voltage
V <sub>SS</sub>	8	ground supply voltage
S1, S2	10, 9	select input
1Y0, 1Y1, 1Y2, 1Y3, 2Y0, 2Y1, 2Y2, 2Y3	12, 14, 15, 11, 1, 5, 2, 4	independent input or output
1Z, 2Z	13, 3	common output or input
$V_{DD}$	16	supply voltage

# 7. Function table

#### Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care.

Input			Channel on
E	S2 S1		
L	L	L	nY0 to nZ
L	L	Н	nY1 to nZ
L	Н	L	nY2 to nZ
L	Н	Н	nY3 to nZ
Н	Х	Х	switches off

#### Dual 4-channel analog multiplexer/demultiplexer

# 8. Limiting values

#### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to  $V_{SS} = 0 \text{ V}$  (ground).

Symbol	Parameter	Conditions		Min	Max	Unit
$V_{DD}$	supply voltage			-0.5	+18	V
V <sub>EE</sub>	supply voltage	referenced to V <sub>DD</sub>	[1]	-18	+0.5	V
I <sub>IK</sub>	input clamping current	pins Sn and $\overline{E}$ ; V <sub>I</sub> < -0.5 V, or V <sub>I</sub> > V <sub>DD</sub> + 0.5 V		-	±10	mA
VI	input voltage			-0.5	V <sub>DD</sub> + 0.5	V
I <sub>I/O</sub>	input/output current			-	±10	mA
I <sub>DD</sub>	supply current			-	50	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
T <sub>amb</sub>	ambient temperature			-40	+125	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C	[2]	-	500	mW
Р	power dissipation	per output		-	100	mW

<sup>[1]</sup> To avoid drawing V<sub>DD</sub> current out of terminal Z, when switch current flows into terminals Y, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal Z, no V<sub>DD</sub> current will flow out of terminals Y, and in this case there is no limit for the voltage drop across the switch, but the voltages at Y and Z may not exceed V<sub>DD</sub> or V<sub>EE</sub>.

# 9. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	eter Conditions Min		Тур	Max	Unit
$V_{DD}$	supply voltage	see Fig. 8	3	-	15	V
$V_{I}$	input voltage		0	-	$V_{DD}$	V
T <sub>amb</sub>	ambient temperature	in free air	-40	-	+125	°C
Δt/ΔV	input transition rise and fall	V <sub>DD</sub> = 5 V	-	-	3.75	μs/V
	rate	V <sub>DD</sub> = 10 V	-	-	0.5	µs/V
		V <sub>DD</sub> = 15 V	-	-	0.08	μs/V




Fig. 8. Operating area as a function of the supply voltages

**Product data sheet** 

6 / 18

<sup>[2]</sup> For SOT109-1 (SO16) package: P<sub>tot</sub> derates linearly with 12.4 mW/K above 110 °C. For SOT403-1 (TSSOP16) package: P<sub>tot</sub> derates linearly with 8.5 mW/K above 91 °C.

#### Dual 4-channel analog multiplexer/demultiplexer


# 10. Static characteristics

#### **Table 6. Static characteristics**


 $V_{SS} = V_{EE} = 0 \ V$ ;  $V_I = V_{SS} \ or \ V_{DD}$ , unless otherwise specified.

Symbol	Parameter	Conditions	$V_{DD}$	T <sub>amb</sub> =	-40 °C	T <sub>amb</sub> =	+25 °C	T <sub>amb</sub> =	+85 °C	T <sub>amb</sub> =	+125 °C	Unit
				Min	Max	Min	Max	Min	Max	Min	Max	
V <sub>IH</sub>	HIGH-level	I <sub>O</sub>   < 1 μΑ	5 V	3.5	-	3.5	-	3.5	-	3.5	-	V
	input voltage	ut voltage	10 V	7.0	-	7.0	-	7.0	-	7.0	-	V
			15 V	11.0	-	11.0	-	11.0	-	11.0	-	V
V <sub>IL</sub>	LOW-level	I <sub>O</sub>   < 1 μΑ	5 V	-	1.5	-	1.5	-	1.5	-	1.5	V
	input voltage		10 V	-	3.0	-	3.0	-	3.0	-	3.0	V
			15 V	-	4.0	-	4.0	-	4.0	-	4.0	V
I <sub>I</sub>	input leakage current		15 V	-	±0.1	-	±0.1	-	±1.0	-	±1.0	μΑ
I <sub>S(OFF)</sub>	OFF-state leakage current	Z port; all channels OFF; see Fig. 9	15 V	-	-	-	1000	-	-	-	-	nA
		Y port; per channel; see <u>Fig. 10</u>	15 V	-	-	-	200	-	-	-	-	nA
I <sub>DD</sub>	supply current	I <sub>O</sub> = 0 A	5 V	-	5	-	5	-	150	-	150	μA
		1	10 V	-	10	-	10	-	300	-	300	μA
			15 V	-	20	-	20	-	600	-	600	μΑ
Cı	input capacitance	Sn, Ē inputs	-	-	-	-	7.5	-	-	-	-	pF

#### 10.1. Test circuits



#### Dual 4-channel analog multiplexer/demultiplexer




#### 10.2. On resistance

#### Table 7. ON resistance


 $T_{amb}$  = 25 °C;  $I_{SW}$  = 200  $\mu$ A;  $V_{SS}$  =  $V_{EE}$  = 0 V.

Symbol	Parameter	Conditions	V <sub>DD</sub> - V <sub>EE</sub>	Тур	Max	Unit
R <sub>ON(peak)</sub>	ON resistance (peak)	$V_I = 0 V \text{ to } V_{DD} - V_{EE};$	5 V	350	2500	Ω
		see <u>Fig. 11</u> and <u>Fig. 12</u>	10 V	80	245	Ω
			15 V	60	175	Ω
$R_{ON(rail)}$	ON resistance (rail)	V <sub>I</sub> = 0 V;	5 V	115	340	Ω
		see <u>Fig. 11</u> and <u>Fig. 12</u>	10 V	50	160	Ω
			15 V	40	115	Ω
		$V_I = V_{DD} - V_{EE};$	5 V	120	365	Ω
		see <u>Fig. 11</u> and <u>Fig. 12</u>	10 V	65	200	Ω
			15 V	50	155	Ω
ΔR <sub>ON</sub>	ON resistance mismatch	$V_I = 0 V \text{ to } V_{DD} - V_{EE};$	5 V	25	-	Ω
	between channels	see Fig. 11	10 V	10	-	Ω
			15 V	5	-	Ω

#### 10.2.1. On resistance waveform and test circuit



#### Dual 4-channel analog multiplexer/demultiplexer



# 11. Dynamic characteristics


#### **Table 8. Dynamic characteristics**


 $T_{amb}$  = 25 °C;  $V_{SS}$  =  $V_{EE}$  = 0 V; for test circuit see Fig. 16.

Symbol	Parameter	Conditions	$V_{DD}$	Тур	Max	Unit
t <sub>PHL</sub>	HIGH to LOW propagation delay	nYn, nZ to nZ, nYn; see Fig. 13	5 V	10	20	ns
			10 V	5	10	ns
			15 V	5	10	ns
		Sn to nYn, nZ; see Fig. 14	5 V	150	305	ns
			10 V	65	135	ns
			15 V	50	100	ns
t <sub>PLH</sub>	LOW to HIGH propagation delay	Yn, nZ to nZ, nYn; see Fig. 13	5 V	10	20	ns
			10 V	5	10	ns
			15 V	5	10	ns
		Sn to nYn, nZ; see Fig. 14	5 V	150	300	ns
			10 V	75	150	ns
			15 V	50	100	ns
$t_{PHZ}$	HIGH to OFF-state propagation delay	Ē to nYn, nZ; see <u>Fig. 15</u>	5 V	95	190	ns
			10 V	90	180	ns
			15 V	85	180	ns
t <sub>PZH</sub>	OFF-state to HIGH propagation	E to nYn, nZ; see Fig. 15	5 V	130	260	ns
	delay		10 V	55	115	ns
			15 V	45	85	ns
$t_{PLZ}$	LOW to OFF-state propagation	E to nYn, nZ; see Fig. 15	5 V	100	205	ns
	delay		10 V	90	180	ns
			15 V	90	180	ns
t <sub>PZL</sub>	OFF-state to LOW propagation	E to nYn, nZ; see Fig. 15	5 V	120	240	ns
	delay		10 V	50	100	ns
			15 V	35	75	ns

#### Dual 4-channel analog multiplexer/demultiplexer

#### 11.1. Waveforms and test circuit






**Table 9. Measurement points** 

Supply voltage	Input	Output		
$V_{DD}$	V <sub>M</sub>	V <sub>M</sub>		
5 V to 15 V	0.5V <sub>DD</sub>	0.5V <sub>DD</sub>		

#### **Dual 4-channel analog multiplexer/demultiplexer**



Test data is given in Table 10.

Definitions:

 $R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator;

C<sub>L</sub> = Load capacitance including test jig and probe;

R<sub>L</sub> = Load resistance.

Fig. 16. Test circuit for measuring switching times

Table 10. Test data

Input			Load		S1 position					
nYn, nZ	Sn and <del>E</del>	t <sub>r</sub> , t <sub>f</sub>	V <sub>M</sub>	C <sub>L</sub> R <sub>L</sub>		t <sub>PHL</sub> [1]	t <sub>PLH</sub>	$t_{PZH},t_{PHZ}$	$t_{PZL}, t_{PLZ}$	other
$V_{DD}$ or $V_{EE}$	$V_{DD}$ or $V_{SS}$	≤ 20 ns	0.5V <sub>DD</sub>	50 pF	10 kΩ	$V_{DD}$ or $V_{EE}$	$V_{EE}$	$V_{EE}$	$V_{DD}$	V <sub>EE</sub>

<sup>[1]</sup> For nYn to nZ propagation delays use  $V_{EE}$ . For Sn to nYn or nZ propagation delays use  $V_{DD}$ .

### 11.2. Additional dynamic parameters

Table 11. Additional dynamic characteristics

 $V_{SS} = V_{EE} = 0 \ V; \ T_{amb} = 25 \ ^{\circ}C.$ 

Symbol	Parameter	Conditions		$V_{DD}$	Тур	Max	Unit
THD	total harmonic distortion	see <u>Fig. 17</u> ; $R_L = 10 \text{ k}\Omega$ ; $C_L = 15 \text{ pF}$ ;	[1]	5 V	0.25	-	%
		channel ON; $V_I = 0.5V_{DD}$ (p-p); $f_i = 1$ kHz		10 V	0.04	-	%
				15 V	0.04	-	%
f <sub>(-3dB)</sub>	-3 dB frequency response	see Fig. 18; $R_L = 1 \text{ k}\Omega$ ; $C_L = 5 \text{ pF}$ ;	[1]	5 V	13	-	MHz
	channel ON; V <sub>I</sub> = 0.5V <sub>DD</sub> (p-p)		10 V	40	-	MHz	
				15 V	70	-	MHz
$\alpha_{iso}$	isolation (OFF-state)	see Fig. 19; $f_i$ = 1 MHz; $R_L$ = 1 $k\Omega$ ; $C_L$ = 5 pF; channel OFF; $V_I$ = 0.5 $V_{DD}$ (p-p)	[1]	10 V	-50	-	dB
V <sub>ct</sub>	crosstalk voltage	digital inputs to switch; see Fig. 20; $R_L = 10 \text{ k}\Omega$ ; $C_L = 15 \text{ pF}$ ; E or Sn = $V_{DD}$ (square-wave)		10 V	50	-	mV
Xtalk	crosstalk	between switches; see Fig. 21; $f_i$ = 1 MHz; $R_L$ = 1 $k\Omega$ ; $V_I$ = 0.5 $V_{DD}$ (p-p)	[1]	10 V	-50	-	dB

[1]  $f_i$  is biased at 0.5  $V_{DD}$ ;  $V_I$  = 0.5 $V_{DD}$  (p-p).

**Product data sheet** 


#### Dual 4-channel analog multiplexer/demultiplexer


#### Table 12. Dynamic power dissipation

 $P_D$  can be calculated from the formulas shown;  $V_{EE} = V_{SS} = 0$  V;  $t_r = t_f \le 20$  ns;  $T_{amb} = 25$  °C.


Symbol	Parameter	$V_{DD}$	Typical formula for P <sub>D</sub> (μW)	where:
$P_D$	dynamic power	5 V	. (0 2, 22	f <sub>i</sub> = input frequency in MHz;
	dissipation	10 V	FD = 0   100 ^  ; T / 11^ ^ C  1 ^ VDD	f <sub>o</sub> = output frequency in MHz; C <sub>L</sub> = output load capacitance in pF;
		15 V	$P_D = 15600 \times f_i + \Sigma(f_o \times C_L) \times V_{DD}^2$	$V_{DD}$ = supply voltage in V; $\Sigma(C_L \times f_o)$ = sum of the outputs.


#### 11.2.1. Test circuits





#### **Dual 4-channel analog multiplexer/demultiplexer**






#### Dual 4-channel analog multiplexer/demultiplexer

# 12. Package outline

#### SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1



UNIT	A max.	A <sub>1</sub>	A <sub>2</sub>	A <sub>3</sub>	bp	С	D <sup>(1)</sup>	E <sup>(1)</sup>	е	HE	L	Lp	Q	v	w	у	Z <sup>(1)</sup>	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	10.0 9.8	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01		0.0100 0.0075	0.39 0.38	0.16 0.15	0.05	0.244 0.228	0.041	0.039 0.016	0.028 0.020	0.01	0.01	0.004	0.028 0.012	0°

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE			
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE	
SOT109-1	076E07	MS-012				<del>99-12-27</del> 03-02-19	

Fig. 22. Package outline SOT109-1 (SO16)

### **Dual 4-channel analog multiplexer/demultiplexer**

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1




Fig. 23. Package outline SOT403-1 (TSSOP16)

SOT403-1

15 / 18

03-02-18

MO-153

#### Dual 4-channel analog multiplexer/demultiplexer

## 13. Abbreviations

#### **Table 13. Abbreviations**

Acronym	Description
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model

# 14. Revision history

#### **Table 14. Revision history**

Document ID	Release date	Data sheet status	Change notice	Supersedes
HEF4052B v.11	20211215	Product data sheet	-	HEF4052B v.10
Modifications:	Nexperia.  Legal texts ha  Section 1 and	this data sheet has been redest ve been adapted to the new consection 2 updated. ing values for P <sub>tot</sub> total power of ted.	ompany name where	
HEF4052B v.10	20160325	Product data sheet	-	HEF4052B v.9
Modifications:	Type number	HEF4052BP (SOT38-4) remov	ed.	
HEF4052B v.9	20140911	Product data sheet	-	HEF4052B v.8
Modifications:	• <u>Fig. 20</u> : Test c	ircuit modified		
HEF4052B v.8	20111117	Product data sheet	-	HEF4052B v.7
Modifications:	<ul><li>Legal pages u</li><li>Changes in Se</li></ul>	pdated. ection 1, <u>Section 2</u> , and <u>Section</u>	<u>1 3</u> .	
HEF4052B v.7	20100326	Product data sheet	-	HEF4052B v.6
HEF4052B v.6	20100308	Product data sheet	-	HEF4052B v.5
HEF4052B v.5	20091127	Product data sheet	-	HEF4052B v.4
HEF4052B v.4	20090924	Product data sheet	-	HEF4052B_CNV v.3
HEF4052B_CNV v.3	19950101	Product specification	-	HEF4052B_CNV v.2
HEF4052B_CNV v.2	19950101	Product specification	-	-

### 15. Legal information

#### **Data sheet status**

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

#### Dual 4-channel analog multiplexer/demultiplexer

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

HEF4052B

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2021. All rights reserved

#### Dual 4-channel analog multiplexer/demultiplexer

# **Contents**

1. General description	1
2. Features and benefits	1
3. Applications	1
4. Ordering information	1
5. Functional diagram	2
6. Pinning information	5
6.1. Pinning	5
6.2. Pin description	5
7. Function table	5
8. Limiting values	6
9. Recommended operating conditions	6
10. Static characteristics	7
10.1. Test circuits	7
10.2. On resistance	8
10.2.1. On resistance waveform and test circuit	8
11. Dynamic characteristics	9
11.1. Waveforms and test circuit	10
11.2. Additional dynamic parameters	11
11.2.1. Test circuits	12
12. Package outline	14
13. Abbreviations	16
14. Revision history	16
15. Legal information	17

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 15 December 2021

<sup>©</sup> Nexperia B.V. 2021. All rights reserved