# XS3A4051

## Single low-ohmic 8-channel analog switch

Rev. 1 — 11 February 2022

**Product data sheet** 

### 1. General description

The XS3A4051 is a low-ohmic 8-channel analog switch, suitable for use as an analog or digital multiplexer/demultiplexer. The XS3A4051 has three digital select inputs (S1 to S3), eight independent inputs/outputs (Y0 to Y7) and a common input/output (Z). All eight switches share an enable input ( $\overline{\mathbb{E}}$ ). A HIGH on  $\overline{\mathbb{E}}$  causes all switches into the high impedance OFF-state, independent of Sn.

Schmitt trigger action at the digital inputs makes the circuit tolerant to slower input rise and fall times. Low threshold digital inputs allows this device to be driven by 1.8 V logic levels in 3.3 V applications without significant increase in supply current  $I_{CC}$ . This makes it possible for the XS3A4051 to switch 4.3 V signals with a 1.8 V digital controller, eliminating the need for logic level translation. The XS3A4051 allows signals with amplitude up to  $V_{CC}$  to be transmitted from Z to Yn or from Yn to Z. Its low ON resistance (0.5  $\Omega$ ) and flatness (0.13  $\Omega$ ) ensures minimal attenuation and distortion of transmitted signals.

### 2. Features and benefits

- Wide supply voltage range from 1.4 V to 4.3 V
- Very low ON resistance (peak):
  - 1.6 Ω (typical) at V<sub>CC</sub> = 1.4 V
  - 1.0 Ω (typical) at V<sub>CC</sub> = 1.65 V
  - 0.55 Ω (typical) at V<sub>CC</sub> = 2.3 V
  - 0.50 Ω (typical) at V<sub>CC</sub> = 2.7 V
  - 0.50 Ω (typical) at V<sub>CC</sub> = 4.3 V
- Break-before-make switching
- High noise immunity
- ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 exceeds 8000 V
  - CDM ANSI/ESDA/JEDEC JS-002 exceeds 1000 V
  - IEC61000-4-2 contact discharge exceeds 8000 V for switch ports
- CMOS low-power consumption
- Latch-up performance exceeds 100 mA per JESD78 Class II Level A
- Low-switching threshold levels
- · Control input accepts voltages above supply voltage
- Very low supply current, even when input is below V<sub>CC</sub>
- High current handling capability (350 mA continuous current under 3.3 V supply)
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

## 3. Applications

- Appliances
- · Communication Systems
- Medical Equipment
- Analog Sensor Monitoring
- Audio Routing/Switching
- · Test and Measurement




### Single low-ohmic 8-channel analog switch


## 4. Ordering information

**Table 1. Ordering information** 

| Type number | Package           |         |  |          |  |  |  |  |  |  |
|-------------|-------------------|---------|--|----------|--|--|--|--|--|--|
|             | Temperature range | Name    | Description  | Version  |  |  |  |  |  |  |
| XS3A4051PW  | -40 °C to +125 °C | TSSOP16 | plastic thin shrink small outline package; 16 leads; body width 4.4 mm | SOT403-1 |  |  |  |  |  |  |

## 5. Functional diagram






Single low-ohmic 8-channel analog switch

## 6. Pinning information

### 6.1. Pinning



### 6.2. Pin description

Table 2. Pin description

| Symbol                         | Pin                        | Description                 |
|--------------------------------|----------------------------|-----------------------------|
| Ē                              | 6                          | enable input (active LOW)   |
| n.c.                           | 7                          | not connected               |
| GND                            | 8                          | ground supply voltage       |
| S1, S2, S3                     | 11, 10, 9                  | select input                |
| Y0, Y1, Y2, Y3, Y4, Y5, Y6, Y7 | 13, 14, 15, 12, 1, 5, 2, 4 | independent input or output |
| Z                              | 3                          | common output or input      |
| Vcc                            | 16                         | supply voltage              |

### Single low-ohmic 8-channel analog switch

## 7. Functional description

#### Table 3. Function table

 $H = HIGH \ voltage \ level; \ L = LOW \ voltage \ level; \ X = don't \ care.$ 

| Input |    |    |    | Channel ON   |
|-------|----|----|----|--------------|
| E     | S3 | S2 | S1 |              |
| L     | L  | L  | L  | Y0 to Z      |
| L     | L  | L  | Н  | Y1 to Z      |
| L     | L  | Н  | L  | Y2 to Z      |
| L     | L  | Н  | Н  | Y3 to Z      |
| L     | Н  | L  | L  | Y4 to Z      |
| L     | Н  | L  | Н  | Y5 to Z      |
| L     | Н  | Н  | L  | Y6 to Z      |
| L     | Н  | Н  | Н  | Y7 to Z      |
| Н     | Х  | Х  | X  | switches off |

## 8. Limiting values

#### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol           | Parameter               | Conditions   |     | Min  | Max                   | Unit |
|------------------|-------------------------|--|-----|------|-----------------------|------|
| V <sub>CC</sub>  | supply voltage          |  |     | -0.5 | +4.6                  | V    |
| V <sub>I</sub>   | input voltage           | Sn and Ē inputs  | [1] | -0.5 | +4.6                  | V    |
| V <sub>SW</sub>  | switch voltage          |  | [2] | -0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>  | input clamping current  | V <sub>I</sub> < -0.5 V  |     | -50  | -                     | mA   |
| I <sub>SK</sub>  | switch clamping current | $V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$  |     | -    | ±50                   | mA   |
| I <sub>SW</sub>  | switch current          | $V_{SW}$ > -0.5 V or $V_{SW}$ < $V_{CC}$ + 0.5 V; source or sink current   |     | -    | ±350                  | mA   |
|                  |                         | $V_{SW}$ > -0.5 V or $V_{SW}$ < $V_{CC}$ + 0.5 V;<br>pulsed at 1 ms duration, < 10 % duty cycle;<br>peak current |     | -    | ±500                  | mA   |
| T <sub>stg</sub> | storage temperature     |  |     | -65  | +150                  | °C   |
| P <sub>tot</sub> | total power dissipation | T <sub>amb</sub> = -40 °C to +125 °C   | [3] | -    | 500                   | mW   |

<sup>[1]</sup> The minimum input voltage rating may be exceeded if the input current rating is observed.

<sup>[2]</sup> The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed but may not exceed 4.6 V.

<sup>[3]</sup> For SOT403-1 (TSSOP16) package:  $P_{tot}$  derates linearly with 8.5 mW/K above 91 °C.

#### Single low-ohmic 8-channel analog switch

## 9. Recommended operating conditions

Table 5. Recommended operating conditions

| Symbol           | Parameter                           | Conditions  |     | Min | Max             | Unit |
|------------------|-------------------------------------|---|-----|-----|-----------------|------|
| V <sub>CC</sub>  | supply voltage                      |   |     | 1.4 | 4.3             | V    |
| VI               | input voltage                       | Sn and E inputs                                   |     | 0   | 4.3             | V    |
| $V_{SW}$         | switch voltage                      |   | [1] | 0   | V <sub>CC</sub> | V    |
| T <sub>amb</sub> | ambient temperature                 |   |     | -40 | +125            | °C   |
| Δt/ΔV            | input transition rise and fall rate | Sn and E inputs; V <sub>CC</sub> = 1.4 V to 4.3 V | [2] | -   | 200             | ns/V |

<sup>[1]</sup> To avoid sinking GND current from terminal Z when switch current flows in terminal Yn, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal Z, no GND current will flow from terminal Yn. In this case, there is no limit for the voltage drop across the switch.

### 10. Static characteristics

**Table 6. Static characteristics** 

At recommended operating conditions; voltages are referenced to GND (ground 0 V).

| Symbol              | Parameter                | Conditions   | Tan | <sub>nb</sub> = 25 | S°C | T <sub>amb</sub> = -40 °C to +85 °C |      | T <sub>amb</sub> = -40 °C to +125 °C |       | Unit |
|---------------------|--------------------------|--|-----|--------------------|-----|-------------------------------------|------|--------------------------------------|-------|------|
|                     |                          |  | Min | Тур                | Max | Min                                 | Max  | Min                                  | Max   |      |
| V <sub>IH</sub>     | HIGH-level               | V <sub>CC</sub> = 1.4 V to 1.6 V   | 0.9 | -                  | -   | 0.9                                 | -    | 0.9                                  | -     | V    |
|                     | input voltage            | V <sub>CC</sub> = 1.65 V to 1.95 V   | 0.9 | -                  | -   | 0.9                                 | -    | 0.9                                  | -     | V    |
|                     |                          | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.1 | -                  | -   | 1.1                                 | -    | 1.1                                  | -     | V    |
|                     |                          | V <sub>CC</sub> = 2.7 V to 3.6 V   | 1.3 | -                  | -   | 1.3                                 | -    | 1.3                                  | -     | V    |
|                     |                          | V <sub>CC</sub> = 3.6 V to 4.3 V   | 1.4 | -                  | -   | 1.4                                 | -    | 1.4                                  | -     | V    |
| V <sub>IL</sub>     | LOW-level                | V <sub>CC</sub> = 1.4 V to 1.6 V   | -   | -                  | 0.3 | -                                   | 0.3  | -                                    | 0.3   | V    |
|                     | input voltage            | V <sub>CC</sub> = 1.65 V to 1.95 V   | -   | -                  | 0.4 | -                                   | 0.4  | -                                    | 0.3   | V    |
|                     |                          | V <sub>CC</sub> = 2.3 V to 2.7 V   | -   | -                  | 0.4 | -                                   | 0.4  | -                                    | 0.4   | V    |
|                     |                          | V <sub>CC</sub> = 2.7 V to 3.6 V   | -   | -                  | 0.5 | -                                   | 0.5  | -                                    | 0.5   | V    |
|                     |                          | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | -                  | 0.6 | -                                   | 0.6  | -                                    | 0.6   | V    |
| I <sub>I</sub>      | input leakage<br>current | Sn and $\overline{E}$ input;<br>$V_I = GND$ to 4.3 V;<br>$V_{CC} = 1.4$ V to 4.3 V | -   | -                  | -   | -                                   | ±0.5 | -                                    | ±1    | μА   |
| I <sub>S(OFF)</sub> | OFF-state                | Y1 and Y2 port; see Fig. 5   |     |                    |     |                                     |      |                                      |       |      |
|                     | leakage<br>current       | V <sub>CC</sub> = 1.4 V to 3.6 V   | -   | -                  | ±5  | -                                   | ±50  | -                                    | ±500  | nA   |
|                     | Current                  | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | -                  | ±10 | -                                   | ±50  | -                                    | ±500  | nA   |
| I <sub>S(ON)</sub>  | ON-state                 | Z port; see Fig. 6   |     |                    |     |                                     |      |                                      |       |      |
|                     | leakage<br>current       | V <sub>CC</sub> = 1.4 V to 3.6 V   | -   | -                  | ±15 | -                                   | ±150 | -                                    | ±1500 | nA   |
|                     | Current                  | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | -                  | ±20 | -                                   | ±150 | -                                    | ±1500 | nA   |
| I <sub>CC</sub>     | supply current           | $V_I = V_{CC}$ or GND;<br>$V_{SW} = GND$ or $V_{CC}$                               |     |                    |     |                                     |      |                                      |       |      |
|                     |                          | V <sub>CC</sub> = 3.6 V  | -   | -                  | 100 | -                                   | 690  | -                                    | 6000  | nA   |
|                     |                          | V <sub>CC</sub> = 4.3 V  | -   | -                  | 150 | -                                   | 800  | -                                    | 7000  | nA   |

<sup>[2]</sup> Applies to control signal levels.

### Single low-ohmic 8-channel analog switch

| Symbol              | Parameter                                       | Conditions                                      | T <sub>amb</sub> = 25 °C |     |      | <sub>nb</sub> =<br>o +85 °C | T <sub>amb</sub> = -40 °C to +125 °C |     | Unit |    |
|---------------------|---|---|--------------------------|-----|------|-----------------------------|--------------------------------------|-----|------|----|
|                     |   |   | Min                      | Тур | Max  | Min                         | Max                                  | Min | Max  |    |
| $\Delta I_{CC}$     | additional                                      | V <sub>SW</sub> = GND or V <sub>CC</sub>        |                          |     |      |                             |                                      |     |      |    |
|                     | supply current                                  | V <sub>I</sub> = 2.6 V; V <sub>CC</sub> = 4.3 V | -                        | 2.0 | 4.0  | -                           | 7                                    | -   | 7    | μΑ |
|                     | V <sub>I</sub> = 2.6 V; V <sub>CC</sub> = 3.6 V | -   | 0.35                     | 0.7 | -    | 1                           | -                                    | 1   | μΑ   |    |
|                     |   | V <sub>I</sub> = 1.8 V; V <sub>CC</sub> = 4.3 V | -                        | 7.0 | 10.0 | -                           | 15                                   | -   | 15   | μΑ |
|                     |   | V <sub>I</sub> = 1.8 V; V <sub>CC</sub> = 3.6 V | -                        | 2.5 | 4.0  | -                           | 5                                    | -   | 5    | μΑ |
|                     |   | V <sub>I</sub> = 1.8 V; V <sub>CC</sub> = 2.5 V | -                        | 50  | 200  | -                           | 300                                  | -   | 500  | nA |
| C <sub>I</sub>      | input<br>capacitance                            | Sn and Ē input                                  | -                        | 1.0 | -    | -                           | -                                    | -   | -    | pF |
| C <sub>S(OFF)</sub> | OFF-state capacitance                           |   | -                        | 35  | -    | -                           | -                                    | -   | -    | pF |
| C <sub>S(ON)</sub>  | ON-state capacitance                            |   | -                        | 350 | -    | -                           | -                                    | -   | -    | pF |

#### Table 7. ON resistance

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for graphs see Fig. 8 to Fig. 14.

| Symbol                | Parameter                | Conditions  | T <sub>amb</sub> = | -40 °C to | +85 °C | T <sub>amb</sub> = -40 ° | C to +125 °C | Unit |
|-----------------------|--------------------------|---|--------------------|-----------|--------|--------------------------|--------------|------|
|                       |                          |   | Min                | Typ[1]    | Max    | Min                      | Max          |      |
| R <sub>ON(peak)</sub> | ON resistance<br>(peak)  | $V_I$ = GND to $V_{CC}$ ;<br>$I_{SW}$ = 100 mA; see <u>Fig. 7</u> |                    |           |        |                          |              |      |
|                       |                          | V <sub>CC</sub> = 1.4 V   | -                  | 1.6       | 3.7    | -                        | 4.1          | Ω    |
|                       |                          | V <sub>CC</sub> = 1.65 V  | -                  | 1.0       | 1.6    | -                        | 1.7          | Ω    |
|                       |                          | V <sub>CC</sub> = 2.3 V   | -                  | 0.55      | 0.8    | -                        | 0.9          | Ω    |
|                       | V <sub>CC</sub> = 2.7 V  | -   | 0.5                | 0.75      | -      | 0.9                      | Ω            |      |
|                       |                          | V <sub>CC</sub> = 4.3 V   | -                  | 0.5       | 0.75   | -                        | 0.9          | Ω    |
| ΔR <sub>ON</sub>      | mismatch                 | $V_I = GND \text{ to } V_{CC};$ [2]<br>$I_{SW} = 100 \text{ mA}$  |                    |           |        |                          |              |      |
|                       | between<br>channels      | V <sub>CC</sub> = 1.4 V; V <sub>SW</sub> = 0.4 V                  | -                  | 0.07      | 0.30   | -                        | 0.30         | Ω    |
|                       | Gramicis                 | V <sub>CC</sub> = 1.65 V; V <sub>SW</sub> = 0.5 V                 | -                  | 0.07      | 0.20   | -                        | 0.30         | Ω    |
|                       |                          | $V_{CC} = 2.3 \text{ V}; V_{SW} = 0.7 \text{ V}$                  | -                  | 0.05      | 0.10   | -                        | 0.13         | Ω    |
|                       |                          | $V_{CC} = 2.7 \text{ V}; V_{SW} = 0.8 \text{ V}$                  | -                  | 0.05      | 0.10   | -                        | 0.13         | Ω    |
|                       |                          | $V_{CC} = 4.3 \text{ V}; V_{SW} = 0.8 \text{ V}$                  | -                  | 0.05      | 0.10   | -                        | 0.13         | Ω    |
| R <sub>ON(flat)</sub> | ON resistance (flatness) | $V_I = GND \text{ to } V_{CC};$ [3]<br>$I_{SW} = 100 \text{ mA}$  |                    |           |        |                          |              |      |
|                       |                          | V <sub>CC</sub> = 1.4 V   | -                  | 1.0       | 3.3    | -                        | 3.6          | Ω    |
|                       |                          | V <sub>CC</sub> = 1.65 V  | -                  | 0.5       | 1.2    | -                        | 1.3          | Ω    |
|                       |                          | V <sub>CC</sub> = 2.3 V   | -                  | 0.15      | 0.3    | -                        | 0.35         | Ω    |
|                       |                          | V <sub>CC</sub> = 2.7 V   | -                  | 0.13      | 0.3    | -                        | 0.35         | Ω    |
|                       |                          | V <sub>CC</sub> = 4.3 V   | -                  | 0.2       | 0.4    | -                        | 0.45         | Ω    |

Typical values are measured at  $T_{amb}$  = 25 °C.

Measured at identical  $V_{CC}$ , temperature and input voltage. Flatness is defined as the difference between the maximum and minimum value of ON resistance measured at identical  $V_{CC}$  and temperature.

### Single low-ohmic 8-channel analog switch

## 10.1. Test circuits and graphs





Fig. 5. Test circuit for measuring OFF-state leakage current



 $V_I$  = 0.3 V or  $V_{CC}$  - 0.3 V;  $V_O$  =  $V_{CC}$  - 0.3 V or 0.3 V

Fig. 6. Test circuit for measuring ON-state leakage current

### Single low-ohmic 8-channel analog switch






Fig. 7. Test circuit for measuring ON resistance



- (1) T<sub>amb</sub> = 125 °C
- (2) T<sub>amb</sub> = 85 °C
- (3)  $T_{amb} = 25 \, ^{\circ}C$
- (4)  $T_{amb} = -40 \, ^{\circ}C$


Fig. 9. ON resistance as a function of input voltage;  $V_{CC} = 1.5 \text{ V}$ 



- (1)  $V_{CC} = 1.5 V$
- $(2) V_{CC} = 1.8 V$
- (3)  $V_{CC} = 2.5 \text{ V}$
- $(4) V_{CC} = 2.7 V$
- $(5) V_{CC} = 3.3 V$
- (6)  $V_{CC} = 4.3 \text{ V}$


Measured at T<sub>amb</sub> = 25 °C

Fig. 8. Typical ON resistance as a function of input voltage




- (1)  $T_{amb} = 125 \, ^{\circ}C$
- (2)  $T_{amb} = 85 \, ^{\circ}C$
- (3)  $T_{amb} = 25 \, ^{\circ}C$
- (4)  $T_{amb}$  = -40 °C

Fig. 10. ON resistance as a function of input voltage;  $V_{CC} = 1.8 \text{ V}$ 




- (1)  $T_{amb} = 125 \, ^{\circ}C$
- (2)  $T_{amb}$  = 85 °C
- (3)  $T_{amb} = 25 \, ^{\circ}C$
- (4)  $T_{amb} = -40 \, ^{\circ}C$

Fig. 11. ON resistance as a function of input voltage;  $V_{CC} = 2.5 \text{ V}$ 




- (1)  $T_{amb} = 125 \, ^{\circ}C$
- (2)  $T_{amb}$  = 85 °C
- (3)  $T_{amb} = 25 \, ^{\circ}C$
- (4)  $T_{amb} = -40 \, ^{\circ}C$

Fig. 12. ON resistance as a function of input voltage;  $V_{CC} = 2.7 \text{ V}$ 



- (1)  $T_{amb}$  = 125 °C
- (2)  $T_{amb}$  = 85 °C
- (3)  $T_{amb}$  = 25 °C
- (4)  $T_{amb} = -40 \, ^{\circ}C$





- (1)  $T_{amb} = 125 \, ^{\circ}C$
- (2)  $T_{amb}$  = 85 °C
- (3)  $T_{amb} = 25 \, ^{\circ}C$
- (4) T<sub>amb</sub> = -40 °C

Fig. 14. ON resistance as a function of input voltage;  $V_{CC} = 4.3 \text{ V}$ 

Single low-ohmic 8-channel analog switch

## 11. Dynamic characteristics


**Table 8. Dynamic characteristics** 

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 17.

| Symbol           | Parameter        | Conditions                         | T   | <sub>amb</sub> = 25 ° | C   | T <sub>amb</sub> = -40 °C<br>to +85 °C |     | T <sub>amb</sub> = -40 °C<br>to +125 °C |     | Unit |
|------------------|------------------|------------------------------------|-----|-----------------------|-----|--|-----|---|-----|------|
|                  |                  |                                    | Min | Typ[1]                | Max | Min                                    | Max | Min                                     | Max |      |
| t <sub>en</sub>  | enable time      | E, Sn to Z or Yn;<br>see Fig. 15   |     |                       |     |  |     |   |     |      |
|                  |                  | V <sub>CC</sub> = 1.4 V to 1.6 V   | -   | 50                    | 110 | -                                      | 120 | -                                       | 120 | ns   |
|                  |                  | V <sub>CC</sub> = 1.65 V to 1.95 V | -   | 36                    | 70  | -                                      | 80  | -                                       | 90  | ns   |
|                  |                  | V <sub>CC</sub> = 2.3 V to 2.7 V   | -   | 24                    | 45  | -                                      | 50  | -                                       | 55  | ns   |
|                  |                  | V <sub>CC</sub> = 2.7 V to 3.6 V   | -   | 22                    | 40  | -                                      | 45  | -                                       | 50  | ns   |
|                  |                  | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | 22                    | 40  | -                                      | 45  | -                                       | 50  | ns   |
| t <sub>dis</sub> | disable time     | E, Sn or Yn; see Fig. 15           |     |                       |     |  |     |   |     |      |
|                  |                  | V <sub>CC</sub> = 1.4 V to 1.6 V   | -   | 32                    | 90  | -                                      | 90  | -                                       | 90  | ns   |
|                  |                  | V <sub>CC</sub> = 1.65 V to 1.95 V | -   | 20                    | 55  | -                                      | 60  | -                                       | 65  | ns   |
|                  |                  | V <sub>CC</sub> = 2.3 V to 2.7 V   | -   | 12                    | 25  | -                                      | 30  | -                                       | 35  | ns   |
|                  |                  | V <sub>CC</sub> = 2.7 V to 3.6 V   | -   | 10                    | 20  | -                                      | 25  | -                                       | 30  | ns   |
|                  |                  | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | 10                    | 20  | -                                      | 25  | -                                       | 30  | ns   |
| t <sub>b-m</sub> | break-           | see <u>Fig. 16</u> [2]             |     |                       |     |  |     |   |     |      |
|                  | before-make time | V <sub>CC</sub> = 1.4 V to 1.6 V   | -   | 19                    | -   | 9                                      | -   | 9                                       | -   | ns   |
|                  | unic             | V <sub>CC</sub> = 1.65 V to 1.95 V | -   | 17                    | -   | 7                                      | -   | 7                                       | -   | ns   |
|                  |                  | V <sub>CC</sub> = 2.3 V to 2.7 V   | -   | 13                    | -   | 4                                      | -   | 4                                       | -   | ns   |
|                  |                  | V <sub>CC</sub> = 2.7 V to 3.6 V   | -   | 10                    | -   | 3                                      | -   | 3                                       | -   | ns   |
|                  |                  | V <sub>CC</sub> = 3.6 V to 4.3 V   | -   | 10                    | -   | 2                                      | -   | 2                                       | -   | ns   |

<sup>[1]</sup> Typical values are measured at  $T_{amb}$  = 25 °C and  $V_{CC}$  = 1.5 V, 1.8 V, 2.5 V, 3.3 V and 4.3 V respectively.

### 11.1. Waveforms and test circuit



<sup>[2]</sup> Break-before-make guaranteed by design.

### Single low-ohmic 8-channel analog switch

**Table 9. Measurement points** 

| Supply voltage  | Input              | Output             |
|-----------------|--------------------|--------------------|
| V <sub>CC</sub> | V <sub>M</sub>     | V <sub>X</sub>     |
| 1.4 V to 4.3 V  | 0.5V <sub>CC</sub> | 0.9V <sub>OH</sub> |





Fig. 16. Test circuit for measuring break-before-make times



Test data is given in Table 10.

Definitions test circuit:

R<sub>L</sub> = Load resistance.

C<sub>L</sub> = Load capacitance including jig and probe capacitance.

 $V_{\mathsf{EXT}}$  = External voltage for measuring switching times.

Fig. 17. Test circuit for measuring switching times

Table 10. Test data

| Supply voltage  | Input L         |                                 | Load  |                |  |
|-----------------|-----------------|---------------------------------|-------|----------------|--|
| V <sub>CC</sub> | VI              | t <sub>r</sub> , t <sub>f</sub> | CL    | R <sub>L</sub> |  |
| 1.4 V to 4.3 V  | V <sub>CC</sub> | ≤ 2.5 ns                        | 35 pF | 50 Ω           |  |

Single low-ohmic 8-channel analog switch

## 11.2. Additional dynamic characteristics

### **Table 11. Additional dynamic characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V);  $V_I = GND$  or  $V_{CC}$  (unless otherwise specified);  $t_r = t_f \le 2.5$  ns.

| Symbol                | Parameter             | Conditions  |     |     | T <sub>amb</sub> = 25 ° | С   | Unit |
|-----------------------|-----------------------|---|-----|-----|-------------------------|-----|------|
|                       |                       |   |     | Min | Тур                     | Max |      |
| THD                   | total harmonic        | $f_i$ = 20 Hz to 20 kHz; $R_L$ = 32 Ω; see Fig. 18  | [1] |     |                         |     |      |
|                       | distortion            | V <sub>CC</sub> = 1.4 V; V <sub>I</sub> = 1 V (p-p)   |     | -   | 0.17                    | -   | %    |
|                       |                       | V <sub>CC</sub> = 1.65 V; V <sub>I</sub> = 1.2 V (p-p)  |     | -   | 0.10                    | -   | %    |
|                       |                       | V <sub>CC</sub> = 2.3 V; V <sub>I</sub> = 1.5 V (p-p)   |     | -   | 0.05                    | -   | %    |
|                       |                       | V <sub>CC</sub> = 2.7 V; V <sub>I</sub> = 2 V (p-p)   |     | -   | 0.04                    | -   | %    |
|                       |                       | V <sub>CC</sub> = 4.3 V; V <sub>I</sub> = 2 V (p-p)   |     | -   | 0.01                    | -   | %    |
| f <sub>(-3dB)</sub>   | -3 dB frequency       | R <sub>L</sub> = 50 Ω; see <u>Fig. 19</u>   | [1] |     |                         |     |      |
|                       | response              | V <sub>CC</sub> = 1.4 V to 4.3 V  |     | -   | 15                      | -   | MHz  |
| $\alpha_{\text{iso}}$ | isolation (OFF-state) | f <sub>i</sub> = 100 kHz; R <sub>L</sub> = 50 Ω; see <u>Fig. 20</u>   | [1] |     |                         |     |      |
|                       |                       | V <sub>CC</sub> = 1.4 V to 4.3 V  |     | -   | -90                     | -   | dB   |
| V <sub>ct</sub>       | crosstalk voltage     | between digital inputs and switch; $f_i$ = 1 MHz; $C_L$ = 50 pF; $R_L$ = 50 $\Omega$ ; see Fig. 21          | [1] |     |                         |     |      |
|                       |                       | V <sub>CC</sub> = 1.4 V to 3.6 V  |     | -   | 0.2                     | -   | V    |
|                       |                       | V <sub>CC</sub> = 3.6 V to 4.3 V  |     | -   | 0.3                     | -   | V    |
| Xtalk                 | crosstalk             | between switches; $f_i$ = 100 kHz; $R_L$ = 50 $\Omega$ ; see Fig. 22  | [1] |     |                         |     |      |
|                       |                       | V <sub>CC</sub> = 1.4 V to 4.3 V  |     | -   | -90                     | -   | dB   |
| Q <sub>inj</sub>      | charge injection      | $f_i$ = 1 MHz; $C_L$ = 0.1 nF; $R_L$ = 1 M $\Omega$ ; $V_{gen}$ = 0 V; $R_{gen}$ = 0 $\Omega$ ; see Fig. 23 | [1] |     |                         |     |      |
|                       |                       | V <sub>CC</sub> = 1.5 V   |     | -   | 3                       | -   | рС   |
|                       |                       | V <sub>CC</sub> = 1.8 V   |     | -   | 4                       | -   | рС   |
|                       |                       | V <sub>CC</sub> = 2.5 V   |     | -   | 6                       | -   | рС   |
|                       |                       | V <sub>CC</sub> = 3.3 V   |     | -   | 9                       | -   | рС   |
|                       |                       | V <sub>CC</sub> = 4.3 V   |     | -   | 15                      | -   | рС   |

<sup>[1]</sup>  $f_i$  is biased at  $0.5V_{CC}$ .

### Single low-ohmic 8-channel analog switch

### 11.3. Additional test circuits






Fig. 18. Test circuit for measuring total harmonic distortion




Adjust  $f_i$  voltage to obtain 0 dBm level at output. Increase  $f_i$  frequency until dB meter reads -3 dB.  $R_S = R_L = 50 \ \Omega$  (standard  $50 \ \Omega$  system).


Fig. 19. Test circuit for measuring the frequency response when channel is in ON-state




Adjust fi voltage to obtain 0 dBm level at input.

Fig. 20. Test circuit for measuring isolation (OFF-state)








### Single low-ohmic 8-channel analog switch

## 12. Package outline

### TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1



| UNIT | A<br>max. | A <sub>1</sub> | A <sub>2</sub> | A <sub>3</sub> | b <sub>p</sub> | С          | D <sup>(1)</sup> | E <sup>(2)</sup> | е    | HE         | L | Lp           | Q          | v   | w    | у   | Z <sup>(1)</sup> | θ        |
|------|-----------|----------------|----------------|----------------|----------------|------------|------------------|------------------|------|------------|---|--------------|------------|-----|------|-----|------------------|----------|
| mm   | 1.1       | 0.15<br>0.05   | 0.95<br>0.80   | 0.25           | 0.30<br>0.19   | 0.2<br>0.1 | 5.1<br>4.9       | 4.5<br>4.3       | 0.65 | 6.6<br>6.2 | 1 | 0.75<br>0.50 | 0.4<br>0.3 | 0.2 | 0.13 | 0.1 | 0.40<br>0.06     | 8°<br>0° |

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

| OUTLINE  |     | REFER  | EUROPEAN | ISSUE DATE |            |                                 |  |
|----------|-----|--------|----------|------------|------------|---------------------------------|--|
| VERSION  | IEC | JEDEC  | JEITA    |            | PROJECTION | ISSUE DATE                      |  |
| SOT403-1 |     | MO-153 |          |            |            | <del>99-12-27</del><br>03-02-18 |  |

Fig. 24. Package outline SOT403-1 (TSSOP16)

### Single low-ohmic 8-channel analog switch

## 13. Abbreviations

### **Table 12. Abbreviations**

| Acronym | Description                             |
|---------|---|
| CDM     | Charged Device Model                    |
| CMOS    | Complementary Metal-Oxide Semiconductor |
| ESD     | ElectroStatic Discharge                 |
| HBM     | Human Body Model                        |

## 14. Revision history

### Table 13. Revision history

| Document ID  | Release date | Data sheet status  | Change notice | Supersedes |
|--------------|--------------|--------------------|---------------|------------|
| XS3A4051 v.1 | 20220211     | Product data sheet | -             | -          |

## 15. Legal information

#### Data sheet status

| Document status [1][2]         | Product<br>status [3] | Definition  |
|--------------------------------|-----------------------|---|
| Objective [short] data sheet   | Development           | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification         | This document contains data from the preliminary specification.                       |
| Product [short]<br>data sheet  | Production            | This document contains the product specification.                                     |

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <a href="https://www.nexperia.com">https://www.nexperia.com</a>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

#### Single low-ohmic 8-channel analog switch

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nexperia.com/profile/terms">http://www.nexperia.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by sustained.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

XS3A4051

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2022. All rights reserved

### Single low-ohmic 8-channel analog switch

## **Contents**

| 1. General description                   | 1  |
|--|----|
| 2. Features and benefits                 | 1  |
| 3. Applications                          | 1  |
| 4. Ordering information                  |    |
| 5. Functional diagram                    |    |
| 6. Pinning information                   |    |
| 6.1. Pinning                             |    |
| 6.2. Pin description                     |    |
| 7. Functional description                |    |
| 8. Limiting values                       |    |
| 9. Recommended operating conditions      |    |
| 10. Static characteristics               |    |
| 10.1. Test circuits and graphs           |    |
|  |    |
| 11. Dynamic characteristics              |    |
| 11.1. Waveforms and test circuit         |    |
| 11.2. Additional dynamic characteristics | 13 |
| 11.3. Additional test circuits           | 14 |
| 12. Package outline                      | 17 |
| 13. Abbreviations                        | 18 |
| 14. Revision history                     | 18 |
| 15. Legal information                    | 19 |
| -  |    |

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 11 February 2022

<sup>©</sup> Nexperia B.V. 2022. All rights reserved