

Quarterly Reliability Monitoring Results

Quarters: Q3/2021 to Q4/2022

Based on structural similarity

Supplier Nexperia B.V. Name of Laboratory Assembly reliability labs Based on AEC-Q101 Test		User Part Number						
		PRTR5V0U2AX-Q						
		Part Description						
		Nexperia DHAM Protection Bipolar						
		SMD package						
		Test Conditions	Duration	# Lots	# Quantity	# Rejects		
	TEST							
	Pre- and Post-Stress							
# E1	Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below		
		JESD22-A113						
	PC	Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85%	24 hours 168 hours					
# A1	Preconditioning	Reflow soldering	3 cycles	438	24630	0		
# AI		MIL-STD-750-1	- 0,0.00	730	24030	U		
	HTRB	M1038 Method A						
		Tj = Tjmax, Vr = 100% of max. datasheet						
# B1	Bias	reverse voltage	1000 hours	34	2000	0		
	тс	JESD22-A104						
# A4	Temperature Cycling	-65 °C to Tjmax, not to exceed 150°C	1000 cycles	131	7760	0		
	UHAST	JESD22-A118						
# A3 or	Unbiased HAST	Tamb = 130 °C, RH = 85 %	— 96 hours	131	7760	0		
		JESD22-A102						
	AC	Tamb = 121 °C, RH = 100 %						
# A3 alt	Autoclave	Pressure = 205 kPa (29.7 psia)						
	H3TRB	JESD22-A101						
	High Humidity High	Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage ^[1]				_		
# A2 alt	Temperature Reverse Bias		1000 hours	131	7760	0		
	IOL	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔT_j =						
# A5	Intermittent Operating Life		1000 hours	n.a.	n.a.	n.a.		
# AJ	End operating the		1000 110015	11.0.	11.0.	11.0.		
	RSH	JESD22-A111						
# C8	Resistance to Solder Heat	260 °C ± 5 °C	10 s	45	1350	0		
	SD							
# C10	Solderability	J-STD-002		111	1110	0		

^[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia					
DHAM	Protection Bipolar	2000	0	2,12	4,71E+08

^{© 2023} Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com